

SPECIFICATION CONTROL DRAWING


55/1112

TITLE ONE CONDUCTOR CABLE, SHIELDED, JACKETED, OUTER SPACE, 600 VOLT

Date 6-25-13

Revision F

This specification sheet forms a part of the latest issue of Raychem Specification 55/.



CABLE CONSTRUCTION DETAILS							
PART NUMBER ^{1/}	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT (lbs/1000 ft.)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55/1112-26-*	26	38	.006	.008	.065	.070	4.7
55/1112-24-*	24	38	.006	.008	.070	.076	5.7
55/1112-22-*	22	38	.006	.008	.076	.082	6.9
55/1112-20-*	20	38	.006	.008	.083	.089	8.9
55/1112-18-*	18	38	.006	.008	.093	.100	11.9
55/1112-16-*	16	38	.006	.008	.101	.108	14.3
55/1112-14-*	14	38	.006	.008	.118	.126	20.2
55/1112-12-*	12	38	.006	.008	.136	.144	28.2

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature
 VOLTAGE RATING: 600 volts (rms) at sea level
 CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour
 DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz
 JACKET COLOR: White preferred
 JACKET ELONGATION: 50% (minimum)
 JACKET FLAWS:

Spark Test, 1000 volts (rms)
 Impulse Dielectric Test, 6.0 kV (peak)

NOTE: Nominal values are for information only.
 Nominal values are not requirements.

RADIATION RESISTANCE: 500 megarads

SHIELD COVERAGE: 85% (minimum)
 VACUUM STABILITY:
 Total Mass Loss (TML), 1.00% (maximum)
 Volatile Condensable Material (VCM), 0.10% (maximum)
 VOLTAGE WITHSTAND (Post Environmental):
 1500 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a dash separating the component wire color from the jacket color.

^{1/} Example: AWG 20, white component wire; white jacket:
 55/1112-20-9-9

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
 Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

^{1/} COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902.." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 1	Raychem, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks.		Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297
	DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.		
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55/1112-24-9-9](#) [55/1112-24-9-5](#) [55/1112-22-9-9](#)