

SPECIFICATION CONTROL DRAWING

55/1144

TITLE FOUR CONDUCTOR CABLE, SHIELDED, JACKETED, OUTER SPACE, 600 VOLT


Date 7-2-07

Revision C

This specification sheet forms a part of the latest issue of Raychem Specification 55/.

COMPONENT WIRES - 55/0114

SHIELD - TIN-COATED COPPER

JACKET - RADIATION-CROSSLINKED,
MODIFIED ETFE

CABLE CONSTRUCTION DETAILS

PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT (lbs/1000 ft.)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55/1144-30-*	30	38	.006	.008	.091	.104	7.7
55/1144-28-*	28	38	.006	.008	.098	.113	9.3
55/1144-26-*	26	38	.006	.008	.110	.127	12.1
55/1144-24-*	24	38	.006	.008	.123	.141	15.4
55/1144-22-*	22	38	.006	.008	.137	.159	20.1
55/1144-20-*	20	38	.006	.008	.154	.179	27.4

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

JACKET COLOR: White preferred

JACKET ELONGATION: 50% (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms)

Impulse Dielectric Test, 6.0 kV (peak)

RADIATION RESISTANCE: 500 megarads

SHIELD COVERAGE: 85% (minimum)

VACUUM STABILITY:

Total Mass Loss (TML), 1.00% (maximum)

Volatile Condensable Material, 0.10% (maximum)

VOLTAGE WITHSTAND TEST (Post Environmental):

1500 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.

NOTE: Nominal values are for information only.

Nominal values are not requirements.

1/ Example: AWG 24, black, brown, red and orange component wires;
white jacket: 55/1144-24-0/1/2/3-9

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx"). OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 1

RAYCHEM is a trademark of Tyco Electronics Corporation.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable
501 Oaks Avenue
Redwood City, CA 94063-3800
Phone: 1-800-227-8816
Fax: 1-650-361-6297

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55/1144-24-9/93/95/96-5](#) [55/1144-24-9/93/95/96-9](#) [55/1144-26-9/93/95/96-9](#)