


SPECIFICATION CONTROL DRAWING			55/2334	
TITLE	THREE CONDUCTOR CABLE, FLAT BRAID SHIELDED, JACKETED, OUTER SPACE, 600 VOLT	Date	8-19-11	Revision C
This specification sheet forms a part of the latest issue of Raychem Specification 55/.				



CABLE CONSTRUCTION DETAILS							
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD STRAND THICKNESS (± .0004 inch)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT (lbs/1000 ft.)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55/2334-28-*	28	.0015	.0040	.0050	.067	.071	4.78
55/2334-26-*	26	.0015	.0040	.0050	.077	.081	6.48
55/2334-24-*	24	.0015	.0040	.0050	.085	.089	8.11
55/2334-22-*	22	.0015	.0040	.0050	.102	.106	12.08

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature
VOLTAGE RATING: 600 volts (rms) at sea level
CROSSLINKED VERIFICATION: 300 ± 3°C for 1 hour
DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz
JACKET COLOR: White preferred
JACKET ELONGATION: 50% (minimum)
JACKET FLAWS:
Spark Test, 1000 volts (rms)
Impulse Dielectric Test, 6.0 kV (peak)

NOTE: Nominal values are for information only.
Nominal values are not requirements.


RADIATION RESISTANCE: 500 megarads

SHIELD COVERAGE: 90% (minimum)
VACUUM STABILITY:
Total Mass Loss (TML), 1.00% (maximum)
Volatile Condensable Material (VCM), 0.10% (maximum)
VOLTAGE WITHSTAND (Post Environmental):
1500 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.

1/ Example: AWG 24, black, brown and red component wires;
white jacket: 55/2334-24-0/1/2-9

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.		
1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.		
Page 1 of 1	Raychem, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks.	
	DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.	
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.	
		Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55/2334-26-9/93/96-9](#)