



























































THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - By -		ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AT1	REVISED PER ECO-16-004223	19JUL2016	NK	MZ
	AT2	REVISED PER ECO-17-008715	16JUN2017	RS	MZ



- ① BRASS PER ASTM B-36.
- ② $2.54\mu\text{m} [.000100]$ MIN TIN-LEAD OVER $1.27\mu\text{m} [.000050]$ MIN NICKEL.
- ③ $0.76\mu\text{m} [.000030]$ MIN PRECIOUS METAL PLATING CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS), OVER $1.27\mu\text{m} [.000050]$ MIN NICKEL.
- ④ $0.76\mu\text{m} [.000030]$ MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF 5.08 [.200] MIN OVER $1.27\mu\text{m} [.000050]$ MIN NICKEL PLATE. GOLD FLASH ALL OVER. CONFORMS TO THE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01A (CONTROLLED ENVIRONMENT APPLICATIONS).
- ⑤ SELECTIVELY PLATED $0.51\mu\text{m} [.000020]$ MIN GOLD, FOR A DISTANCE OF 5.08 [.200] FROM MATING END, GOLD FLASH ON REMAINDER, ALL OVER $0.76\mu\text{m} [.000030]$ MIN NICKEL.
- ⑥ POST WILL ACCEPT (SEE TABLE) TERMINATIONS.
- ⑦ POST PLATING .000100 MIN TIN OVER .000050 MIN NICKEL.
- ⑧ .0001000 TIN OVER .000050 NICKEL.

			3	46.08 [1.814]	25.91 [1.020]	6-66460-6	
			1	35.97 [1.416]	15.80 [.622]	6-66460-5	
			3	46.08 [1.814]	25.91 [1.020]	6-66460-4	
			2	41.28 [1.625]	21.11 [.831]	6-66460-3	
			1	35.97 [1.416]	15.80 [.622]	6-66460-2	
OBSOLETE			SPECIAL	33.40 [1.315]	13.23 [.521]	6-66460-1	
			SPECIAL	65.61 [2.583]	45.44 [1.789]	5-66460-0	
			SPECIAL	57.73 [2.273]	37.57 [1.479]	4-66460-9	
			SPECIAL	49.86 [1.963]	29.69 [1.169]	4-66460-8	
			SPECIAL	68.60 [2.701]	48.44 [1.907]	3-66460-0	
			SPECIAL	59.71 [2.351]	39.55 [1.557]	2-66460-9	
			SPECIAL	50.82 [2.001]	30.66 [1.207]	2-66460-8	
OBSOLETE			1	34.80 [1.370]	14.63 [.576]	2-66460-1	
			-	34.77 [1.369]	14.63 [.576]	2-66460-0	
OBSOLETE			SPECIAL	52.78 [2.078]	32.61 [1.284]	1-66460-9	
			2	41.28 [1.625]	21.11 [.831]	1-66460-8	
			2	41.28 [1.625]	21.11 [.831]	1-66460-1	
			SPECIAL	33.40 [1.315]	13.23 [.521]	1-66460-0	
			3	46.08 [1.814]	25.91 [1.020]	66460-9	
			2	41.28 [1.625]	21.11 [.831]	66460-8	
			1	35.97 [1.416]	15.80 [.622]	66460-7	
	OBSOLETE			3	46.08 [1.814]	25.91 [1.020]	66460-6
				2	41.28 [1.625]	21.11 [.831]	66460-5
Y 66460-8			1	35.97 [1.416]	15.80 [.622]	66460-4	
			3	46.08 [1.814]	25.91 [1.020]	66460-3	
			2	41.28 [1.625]	21.11 [.831]	66460-2	
			1	35.97 [1.416]	15.80 [.622]	66460-1	
		FINISH	BODY FINISH	NO OF TERM	B	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 06 JUN 96 C. REIFSNYDER CHK 27 JUN 96 R. STONE		 TE Connectivity	
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PIN CONTACT, CRIMPED, .062, .025 X .025 POSST, M SERIES	
		APD 23 JUL 96 G. STEINHAUER PRODUCT SPEC —			
0 PLC ± — 1 PLC ± — 2 PLC ± 0.25 [.010] 3 PLC ± — 4 PLC ± — ANGLES ± —		APPLICATION SPEC —			
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS			
		WEIGHT		SIZE A2	
				CAGE CODE 00779	
				DRAWING NO C-66460	
				RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE 4:1	
				SHEET 1 of 2	
				REV AT2	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

7

4

SPECIAL

33.40
[1.315]

13.23
[.521]

6-66460-8

7

8

2

41.28
[1.625]

21.11
[.831]

6-66460-7

POST
FINISH

BODY
FINISH

NO OF
TERM

B

A

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM [INCHES]

MATERIAL
SEE CALLOUTS

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.25 [.010]

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH
SEE CALLOUTS

DWN
C.REIFSNYDER
06 JUN 96

CHK
R.STONE
27 JUN 96

APVD
G.A.STEINHAUER
23 JUL 96

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT

CUSTOMER DRAWING

TE Connectivity

PIN CONTACT, CRIMPED,
.062, .025 X .025 POSST,
M SERIES

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=66460

RESTRICTED TO
—

SCALE
4:1

SHEET
2 of 2

REV
AT2

1471-9 (1/15)

66460

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-66460-9](#)