DEUTSCH* Field Service Crimp Tool HDT-1561 Crimping Instructions

This racheting crimp tool is designed to crimp Deutsch solid pin and socket contacts as listed on *Chart A* below:

Chart A

Contact Size	Contact Type	Deutsch Part Number	Wire AWG Range	Crimp Nest	Recommended Strip Length
20	Pin	0460-202-20141	20	Front	.156"218"
20	Socket	0462-201-20141	20	Front	.156"218"
16	Pin	0460-202-16141	16-18	Middle	.250"312"
16	Socket	0462-201-16141	16-18	Middle	.250"312"
16	Pin	0460-215-16141	14	Middle	.250"312"
16	Socket	0462-209-16141	14	Middle	.250"312"
12	Pin	0460-204-12141	12-14	Rear	.222"284"
12	Socket	0462-203-12141	12-14	Rear	.222"284"

Illustration A



Assembly Instructions:

- Cycle the tool to open position by completely closing handle grips.
- 2. Refer to Chart A to select the appropriate crimp nest.
- 3. Grasp crimp barrel end of contact (short end with bleed hole). Place contact through front of tool (*Illustration A*). Align contact shoulder with locating slot (*Illustration B*). Close tool slightly, holding contact in place.
- Insert properly stripped wire (refer to Chart A) into the crimp barrel of contact. Hold wire in place while completely closing handle grips.
- 5. Remove crimped contact. Inspect for quality; a) copper strands should be visible in bleed hole of crimp and b) no copper strands should be loose outside the crimp barrel.

Illustration B (Locating Slot)




Chart B (Crimp Height/Width)




Chart C (Current Ratings)

Wire AWG Range	Current Rating	Tensile Strength
20	7.5 amps	20 lbs.
16-18	13 amps	25 lbs.
14	13 amps	25 lbs.
12-14	25 amps	70 lbs.
	20 16-18 14	Wire AWG Current Range 7.5 amps 16-18 13 amps 14 13 amps

Maximum

010407

Crimn

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity: