


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—		B	REVISED	11MAY2011	M.M	N.Y



注)

- 1.一般公差： $\pm 0.25$
- 2.材料：2材料：銅合金全面Niめっき  $1.3\mu\text{m}$  以上  
接点部金めっき  $0.38\mu\text{m}$  以上めっき
- 3.適用電線：AWG#14-#12(被覆外径  $\phi 2.9 \sim \phi 4.1$ )

NOTES)

- 1.GENERAL TOLERANCE: $\pm 0.25$
- 2..MATERIAL:COPPER ALLOY,FINISH:OVER NI PLATING  $1.3\mu\text{m}$  MIN.  
(CONTACT AREA)  $0.38\mu\text{m}$  MIN GOLD PLATING
- 3.APPLICABLE WIRE:AWG#14-#12 (INS DIA  $\phi 2.9 \sim \phi 4.1$ )

L SIZE


## DIMENSIONS:

mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

SEE NOTE

0 PLC	$\pm$	—
1 PLC	$\pm$	—
2 PLC	$\pm$	—
3 PLC	$\pm$	—
4 PLC	$\pm$	—
ANGLES	$\pm$	—



DWN	T.KUDO	26AUG2004
CHK	D.MITSUGI	26AUG2004
APVD	D.MITSUGI	26AUG2004
PRODUCT SPEC	108-78182	
APPLICATION SPEC	114-5369	
WEIGHT	—	

MATERIAL	COPPER ALLOY	FINISH	SEE NOTE
TE Connectivity			
NAME DYNAMIC D-4200 TAB CONTACT L SIZE LOOSE PIECE			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A4	00779	C-1747500	—

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 of 1

REV B

MAY, 2011.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

COPYRIGHT 2011 By Tyco Electronics Japan G.K.

THIS DRAWING IS UNPUBLISHED.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1747500-2](#)