

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.




LOC

DIST


REVISIONS

変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	24SEP2008	H.U	T.K
	B	REVISED	18DEC2008	H.U	T.K
	C	REVISED	11MAY2010	H.U	T.M



-2; 本図  
-2; AS SHOWN



材料; 黄銅。



仕上げ; 全面ニッケル下地めっき。  
接触部及び圧着部に0.2μm以上の金めっき。



AWG#26, AWG#28対応;  
対応電線: UL1508 AWG#26  
素線数/素線径: 7/0.16mm<sup>2</sup>  
絶縁被覆径: φ0.73-φ0.82

対応電線: UL1508 AWG#28  
素線数/素線径: 7/0.127mm<sup>2</sup>  
絶縁被覆径: φ0.64-φ0.68

4. 使用ハウジング: 2040974-\*



MATERIAL; Brass.



FINISH; Ni UNDER PLATING ALL SURFACE.  
CONTACT AND CRIMP AREA; Au PLATING 0.2μm MIN.



WIRE SIZE AWG#26, AWG#28;  
APPLICABLE WIRES: UL1508 AWG#26  
NUMBER OF CONDUCTORS/  
DIAMETER OF A CONDUCTOR: 7/0.16mm<sup>2</sup>  
INSULATION DIAMETER: φ0.73-φ0.82

APPLICABLE WIRES: UL1508 AWG#28  
NUMBER OF CONDUCTORS/  
DIAMETER OF A CONDUCTOR: 7/0.127mm<sup>2</sup>  
INSULATION DIAMETER: φ0.64-φ0.68

4. USE HOUSING P/N: 2040974-\*

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION.  
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: 単位: 毫 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
一般公差	±0.2
0 PLC	±
1 PLC	±0.3
2 PLC	±0.1
3 PLC	±0.001
4 PLC	±0.0001
ANGLES	±3°
MATERIAL 材料	FINISH 仕上
1	2

DWN H. URUSHIBATA	24SEP2008
CHK T. KUDO	24SEP2008
APVD S. MANABE	24SEP2008
PRODUCT SPEC 製品規格	108-78573
APPLICATION SPEC 取付適用規格	114-5441
WEIGHT	-
CUSTOMER DRAWING	

WIRE RANGE 総合電線断面積	0.089mm <sup>2</sup> ~0.141mm <sup>2</sup>	INSULATION DIA 被覆外径	3
Tyco Electronics Corporation Kawasaki, Japan			
NAME 名称 POST CONTACT 1.0VP REMODEL			
SIZE 寸法	CAGE CODE 番号	DRAWING NO 図番	RESTRICTED TO
A3	00779	C-2040973	-
SCALE 尺度		SHEET 枚数	REV 改訂
20:1		1 OF 1	C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2040973-2](#)