









MATING CROSS SECTION
(30:1)



Ni UNDER PL; 0.65um Sn PL.; 2~5um	COPPER ALLOY	PLUG PEG	3
Ni UNDER PL; 0.65um Au PL.(CONTACT AREA); 0.1um MIN. Au PL.(TINE AREA); 0.05um MIN.	COPPER ALLOY	PLUG CONTACT	2
	LCP,UL94V-0,BLACK	PLUG HOUSING	1
△ FINISH	△ MATERIAL	NAME	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.HIKAGE 02AUG2012		TE Connectivity	
DIMENSIONS: mm		CHK A.KUBO 02AUG2012			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T.KUSUHARA 02AUG2012		NAME	
0 PLC ± 0.1 1 PLC ± 0.1 2 PLC ± 0.1 3 PLC ± 0.1 4 PLC ± 0.1 ANGLES ± 3°		PRODUCT SPEC 108-78916		0.4mm PITCH STACKING CONNECTOR PLUG ASSEMBLY 0.98mm HEIGHT	
MATERIAL △		APPLICATION SPEC 411-78379		SIZE A3	
FINISH △		WEIGHT		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-2201196	
				RESTRICTED TO —	
				SCALE 20:1	
				SHEET 1 OF 3	
				REV A	

LOC J	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



△6 REFERENCE PCB LAYOUT
(VIEWED FROM MOUNTING SIDE)

- NOTE
- △1 MATERIAL REFER TO THE TABLE.
 - △2 FINISH REFER TO THE TABLE.
 - 3. MATING CONNECTOR : P/N: *-2201197-*
 - △4 LASER MARKING; XXXXX
DATE CODE MACHINE CODE
(YWW)
 - △5 PICK UP THE CONNECTOR AT CENTER
 - △6 RECOMMENDED METAL MASK; THICKNESS 0.1mm
 - △7 Ni DAM AREA

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.1
1 PLC ± 0.1
2 PLC ± 0.1
3 PLC ± 0.1
4 PLC ± 0.1
ANGLES ± 3°
FINISH

DWN
—
CHK
—
APVD
—
PRODUCT SPEC
—
APPLICATION SPEC
—
WEIGHT
—

TE Connectivity

NAME
0.4mm PITCH STACKING CONNECTOR
PLUG ASSEMBLY 0.98mm HEIGHT

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2201196

RESTRICTED TO

CUSTOMER DRAWING

SCALE
NTS

SHEET
2 of 3

REV
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2201196-0](#)