

RMW
Heat-Shrinkable, Medium Wall, Polyolefin Tubing




Table 1: Dimensions

Size	Minimum Expanded I.D. (D)		Maximum Expanded I.D. (d)		Nominal Recovered Jacket Wall (W minus W1)		Nominal Recovered Adhesive Wall (W1)	
	in.	mm.	in.	mm.	in.	mm.	in.	mm.
10/3	.394	10	.118	3	.039	1.0	.010	.25
16/5	.630	16	.197	5	.055	1.4	.012	.30
25/8	.984	25	.315	8	.079	2.0	.014	.35
35/12	1.378	35	.472	12	.079	2.0	.014	.35
50/16	1.968	50	.630	16	.079	2.0	.014	.35
63/19	2.480	63	.748	19	.095	2.4	.016	.40
75/22	2.953	75	.866	22	.106	2.7	.016	.40
85/25	3.346	85	.984	25	.110	2.8	.016	.40
95/29	3.740	95	1.142	29	.122	3.1	.018	.45
115/34	4.527	115	1.339	34	.122	3.1	.018	.45
140/42	5.512	140	1.654	42	.122	3.1	.018	.45
160/50	6.300	160	1.968	50	.126	3.2	.020	.50
180/60	7.087	180	2.362	60	.126	3.2	.020	.50
245/80*	9.646	245	3.150	80	.095	2.4	N/A	N/A
285/135*	11.220	285	5.315	135	.055	1.4	N/A	N/A

* Uncoated Only

Material: The tubing shall be fabricated from a modified irradiated polyolefin compounded to produce a homogeneous, uniform product whose outside surface is essentially free from flaws, defects, pinholes, seams, cracks, or inclusions.


Color: Black

Note: Available with adhesive coating as well as uncoated. Sizes indicated with * in Table 1 are available only as uncoated.

Raychem Tubing

© 2013 Tyco Electronics Corporation. All rights reserved.

CUSTOMER DRAWING

		TE Connectivity 305 Constitution Drive Menlo Park, CA 94025 USA		Title: RMW Heat-Shrinkable, Medium Wall, Polyolefin Tubing			
		TE Connectivity reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for the application		Document No : RMW			
Cage Code: 06090	Scale: None	Size: A	Rev. Date: 30-Apr-13	Rev.:	D	Sheet: 1 of 2	

If this document is printed it becomes uncontrolled. Check for the latest revision.

CUSTOMER DRAWING

Table 2: Properties

Property	Unit	Requirement	Test Method
Dimensions	Inch (mm)	Table 1	ASTM D2671
Tensile Strength	psi (MPa)	1750 minimum (12)	ASTM D2671
Ultimate Elongation	Percent	350 minimum	ASTM D2671
Longitudinal Change	Percent	+5 to -15 maximum	ASTM D2671
Specific Gravity		1.2 maximum	ASTM D792
Hardness	Shore D	40 - 60	ASTM D2240
Low Temperature Flexibility 4 hrs @ -40°C		No cracking	ASTM D2671
Heat Resistance 168 h @150°C followed by Ultimate Elongation	Percent	350 minimum	ASTM D2671
Fungus Growth		Rating of 1 or less	ASTM G21
ELECTRICAL			
Dielectric Strength	V/mil (kV/cm)	300 minimum (120)	ASTM D149
Volume Resistivity	Ohm-cm	1 X 10 ¹² minimum	ASTM D257
CHEMICAL			
Fluid Resistance 168 hrs @ 23°C Immersion in VDE 0370 oil followed by tests for:			
Tensile Strength	psi	1450 minimum (10)	ASTM D2671
Ultimate Elongation	Percent	300 minimum	
Corrosive Effect 16 hrs @ 150°C		Noncorrosive	ASTM D2671, Proc. A
Water Absorption 24 hrs @ 23°C	Percent	0.50 maximum	ASTM D570

Rev. Date: 30-Apr-13	Rev.: D	Document No. RMW	Sheet: 2 of 2
-------------------------	------------	----------------------------	------------------

If this document is printed it becomes uncontrolled. Check for the latest revision.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[RMW-16/5-1200/ADH-0](#)