




Passive Components > Resistors > Chassis Mount Resistors > Power Wirewound Resistor: Mineral, CFH



Resistor Type: **Power Resistor**

Passive Component Dimensions: **320 x 95 x 30 mm**

Number of Terminations: **2**

Packaging Method: **Loose Piece - Box**

Passive Component Tolerance: **5 %**

[All Power Wirewound Resistor: Mineral, CFH \(17\)](#)

Features

Product Type Features

| | |
|---------------|----------------|
| Resistor Type | Power Resistor |
| Element Type | Wire Wound |

Configuration Features

| | |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

| | |
|-----------------------------|-----------|
| Passive Component Tolerance | 5 % |
| Resistance Class | Up to 1kΩ |
| Resistance Value | 22 Ω |
| Power Rating | 2200 W |

Termination Features

| | |
|---|--------------------|
| Number of Terminations | 2 |
| Chassis Mount Resistor Termination Type | Custom Termination |

Mechanical Attachment

| | |
|------------------------------------|---------------|
| Chassis Mount Resistor Mount Style | Chassis Mount |
|------------------------------------|---------------|

Dimensions

| | |
|------------------------------|------------------|
| Passive Component Dimensions | 320 x 95 x 30 mm |
|------------------------------|------------------|



Packaging Features

| | |
|------------------|-------------------|
| Packaging Method | Loose Piece - Box |
|------------------|-------------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-C339-C339
Power Wirewound Resistor: Mineral, CFH

TE Part # 2-1623821-8
CFH 1100 120R 5% 300MM LEADS

TE Part # 2-1623821-7
CFH350 620R 5% 1000MM LEADS

Also in the Series | CGS CFH




Chassis Mount Resistors(17)

Customers Also Bought




TE Part #1-1623821-0
CFH 1100 1R6 5% 300mm Leads




TE Part #580133-5
THREADED, PWR PIN, PLTD & LUBE



TE Part #104352-5
10 MODII HDR DRST B/A W/HD



TE Part #792325-000
322A123-25/86-0



TE Part #531138-7
3ROW BOX REC 210P 100CL UNSEAL



TE Part #5406552-7
INV MJ,1X4,PNL GRD,LED (OG/OG)

Documents

Product Drawings

CFH 1100 22R 5% 300MM LEADS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1623821-5_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1623821-5_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1623821-5_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



[Datasheets & Catalog Pages](#)
[Aluminium Housed Power Resistors - Type CFH Series](#)
English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1623821-5](#)