



Relays, Contactors & Switches > Relays > Protective Relays



Protective Relay Contact Arrangement: 1 N.C & 1 N.O

Protective Relay Contact Current Rating: 5 A

Protective Relay Input Voltage: 230 VAC

Time Delay: Without

Protective Relay Mounting Type: Flanged

Features

Product Type Features

Relay Type	Protective Relay
Product Type	Relay
Protection Function	Over/Undervoltage
Time Delay	Without
Phase	Single

Electrical Characteristics

Actuating System	AC
Protective Relay Input Voltage	230 VAC

Contact Features

Contact Arrangement (Additional Output)	1 Form B, SPST-NC, 1 N/C
Protective Relay Contact Arrangement	1 N.C & 1 N.O
Protective Relay Contact Current Rating	5 A

Mechanical Attachment

Protective Relay Mounting Type	Flanged
--------------------------------	---------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1618071-6
250-1X=WILMAR OVER
/UNDervOLTAG

Customers Also Bought



TE Part #YACT26JE35HBV00100
STRAIGHT PLUG



TE Part #455188-000
D-500-0255-021-02



TE Part #6-1617540-4
J1MAP-6XL=M39016/7-016L



TE Part #696469-1
AMPPOWER,2,3/8,TIN,90,30 DEG BL



TE Part #9-1617541-0
JMAC-30XP=M39016/9-063P

TE Part #624046-000
D-105-36

TE Part #279316-000
D-500-04-C23-072

TE Part #7477570003
S02-10-R-9CS927

TE Part #8-1617805-8
TD231-2001P=TDAR .2-2 SEC

TE Part #830023-000
TXR21AB00-2416AI

Documents

Product Drawings
253-5X=WILMAR OVER/UNDERVOLTAG
English

Datasheets & Catalog Pages
5-1773450-5_sec11_250
English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[253-5X](#)