



Wire Protection & Management > Heat Shrink Molded Shapes > Heat Shrink Boots > Low Profile Heat Shrink Boots: Poly Molded, Lipped, Straight



Molded Part Angle: 180 °
Molded Part Shape Code: 202
Lipped: Yes
Material Code: 3
Heat Shrink Boot Material Systems Code: 10

[All Low Profile Heat Shrink Boots: Poly Molded, Lipped, Straight \(223\)](#)

Features

Product Type Features

Molded Part Angle	180 °
-------------------	-------

Configuration Features

Lipped	Yes
--------	-----

Body Features

Material Code	3
Heat Shrink Boot Material Systems Code	10
Adhesive Pre-Coat	No
Material	Semi-Rigid Modified Polyolefin

Dimensions

Wire/Cable Outside Diameter	.43 in, .47 in, .55 in, .63 in, .71 in, 11 mm, 12 mm, 14 mm, 16 mm, 18 mm
Connector or Backshell Outside Diameter	1.26 in, 1.34 in, 1.42 in, 1.5 in, 32 mm, 34 mm, 36 mm, 38 mm

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Industry Standards

Approved Standards	BS-G-198-5-DA, DEF Std 59-97 Issue 3
--------------------	--------------------------------------



Type DA, SAE AS I 81765/1, Type I, UL 224, File E85381

Other

Molded Part Shape Code	202
Fluid & Chemical Resistance	Occasional Fluid Exposure

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 890060-000
S1017-1.0X50



TE Part # CJ2087-000
HL2010E-KIT-120V



Customers Also Bought

 TE Part #2343522-5 SFP56 STACKED 2X2 RECEPTACLE ASSEMBLY	 TE Part #806894-000 202D232-25-22-0	 TE Part #808492-000 202A063-3-0	 TE Part #1-1532171-9 M83513/04-A03C, MCKS-C2-B-9S6G9-18.0
 TE Part #1-1879749-8 LED ENCODER 12MM HORIZ SW GR /RD	 TE Part #1-1617125-2 JMAW-6XL = M39016/9-014L	 TE Part #1879270-8 RP 2A 51R1 0.1% 15PPM 1K RL	 TE Part #5-1879270-6 RP 2A 75R 0.1% 15PPM 1K RL

Documents

Product Drawings

202D253-3-2

English

Datasheets & Catalog Pages

1654025_Sec4_-3

English

1654025_Sec4_202D211to299

English

Raychem Molded Parts Visual Guide

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

Safety Datasheet

English

Safety Datasheet

French

Safety Datasheet

German

Safety Datasheet

Safety Datasheet

Safety Datasheet



[Safety Datasheet](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202D253-3-2](#)