

Type TJT Series

Key Features


Excellent Heat transfer and small dimensions

Good
Electrical
Stability,
reliability and
mechanically
very rigid

Wide Range of Resistance values available

Custom Terminations, Mounting Arrangements possible

Non Inductive version available



The TJT series is a range of high quality, high stability Aluminium housed low profile Power resistors designed for direct heat sink attachment.

A wide range of resistance values is available in 150W to 500W when fitted to a standard heatsink


Ideal for custom terminations and mounting arrangements, the TJT series is RoHS compliant


Characteristics - Electrical

Parameter	Test	Change in R value if applicable
Tolerance		±5%
Temperature Co-efficient		< ± 260 PPM/°C
Insulation Resistance	Dry/Normal	> 500 MΩ
Change in Resistance		
- Short time overload	5x rated voltage for 5 secs	< ± (1% + 0.05Ω)
- Load Life	Rated Power (1.5Hr ON – 1.5Hr	< ± 1%
	OFF) for 1000 hours	
Operating Temperature	From -25°C to 250°C	
Derating	Linearly from 100% at 25°C to 0 at	
	260°C	

ALUMINIUM ENCLOSED POWER RESISTORS

Surface Temperature Vs Power





Series	Power rating	Power	Resistance	Dielectric	L max	P1	P2
	on Std Heat	rating in	Range (Ω)	Strength	(mm)	(mm)	(mm)
	sink (W)	free air (W)		(V)			
TJT150	150	75	1R0 - 1K0	1500	120	100	N/A
TJT250	250	125	1R0 - 1K5	1500	180	160	N/A
TJT300	300	150	1R0 – 1K7	1500	210	190	85
TJT500	500	250	1R0 – 3K0	1500	330	310	155

How To Order

TJT	150	1R0 J

Common Part	Power Rating	Resistance Value	Tolerance
ТЈТ	150 – 150W 250 – 250W 300 – 300W 500 – 500W	1 ohm 1R0 1K ohm 1000 ohms 1K0	J – 5%

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

TJT1501R0J TJT250100RJ TJT3004R7J TJT150470RJ TJT30022RJ TJT250680RJ TJT25047RJ TJT1501R5J
TJT500470RJ TJT300220RJ TJT250220RJ TJT1501K0J TJT250150RJ TJT50047RJ TJT1506R8J TJT30010RJ
TJT15010RJ TJT5002K2J TJT300100RJ TJT150100RJ TJT2504R7J TJT2501R5J TJT30033RJ TJT50033RJ
TJT1503R3J TJT300680RJ TJT50010RJ TJT3003R3J TJT500100RJ TJT15033RJ TJT15015RJ TJT250470RJ
TJT3001K5J TJT50015RJ TJT25015RJ TJT25033RJ TJT500680RJ TJT15068RJ TJT3001R5J TJT15047RJ
TJT30047RJ TJT2506R8J TJT5001K0J TJT30015RJ TJT50022RJ TJT2501K0J TJT25010RJ TJT5001K5J
TJT500150RJ TJT150150RJ TJT300150RJ TJT300150RJ TJT15022RJ TJT5004R7J TJT50022RJ TJT300470RJ TJT5003R3J
TJT25022RJ TJT300330RJ TJT5006R8J TJT3002R2J TJT1504R7J TJT2503R3J TJT30068RJ TJT150220RJ
TJT25068RJ TJT150330RJ TJT50068RJ
TJT250330RJ TJT50068RJ