





D



RECOMMENDED HOLE LAYOUT

C



SECTION X—X

B

- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 2 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING
- 3 POSTS:.000015 GOLD IN CONTACT AREA, .000100—.000200 MATTE TIN—LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- 4 POSTS:.000015 GOLD IN CONTACT AREA, .000100—.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

A

OBSOLETE	4	3.032	2.900	29	60	7-102055-8
	4	2.732	2.600	26	54	7-102055-5
	4	2.532	2.400	24	50	7-102055-3
	4	2.032	1.900	19	40	6-102055-8
	4	1.732	1.600	16	34	6-102055-5
	4	1.532	1.400	14	30	6-102055-3
	4	1.232	1.100	11	24	6-102055-0
	4	.932	.800	8	18	5-102055-8
	4	.832	.700	7	16	5-102055-7
	4	.732	.600	6	14	5-102055-6
OBSOLETE	4	.632	.500	5	12	5-102055-5
	4	.532	.400	4	10	5-102055-4
	4	.432	.300	3	8	5-102055-3
	4	.332	.200	2	6	5-102055-2
	4	1.032	.900	9	20	5-102055-1
	3	3.732	3.600	36	74	3-102055-5
	3	3.632	3.500	35	72	3-102055-4
	3	3.532	3.400	34	70	3-102055-3
	3	3.432	3.300	33	68	3-102055-2
	3	3.332	3.200	32	66	3-102055-1
OBSOLETE	3	3.232	3.100	31	64	3-102055-0
	3	3.132	3.000	30	62	2-102055-9
	3	3.032	2.900	29	60	2-102055-8
	3	2.932	2.800	28	58	2-102055-7
	3	2.832	2.700	27	56	2-102055-6
	3	2.732	2.600	26	54	2-102055-5
	3	2.632	2.500	25	52	2-102055-4
	3	2.532	2.400	24	50	2-102055-3
	3	2.432	2.300	23	48	2-102055-2
	3	2.332	2.200	22	46	2-102055-1
OBSOLETE	3	2.332	2.200	22	46	2-102055-1
	3	2.232	2.100	21	44	2-102055-0
	3	2.132	2.000	20	42	1-102055-9
	3	2.032	1.900	19	40	1-102055-8
	3	1.932	1.800	18	38	1-102055-7
	3	1.832	1.700	17	36	1-102055-6
	3	1.732	1.600	16	34	1-102055-5
	3	1.632	1.500	15	32	1-102055-4
	3	1.532	1.400	14	30	1-102055-3
	3	1.432	1.300	13	28	1-102055-2
OBSOLETE	3	1.332	1.200	12	26	1-102055-1
	3	1.232	1.100	11	24	1-102055-0
	3	1.132	1.000	10	22	102055-9
	3	.932	.800	8	18	102055-8
	3	.832	.700	7	16	102055-7
	3	.732	.600	6	14	102055-6
	3	.632	.500	5	12	102055-5
	3	.532	.400	4	10	102055-4
	3	.432	.300	3	8	102055-3
	3	.332	.200	2	6	102055-2
OBSOLETE	3	1.032	.900	9	20	102055-1
	3	.932	.800	8	18	102055-8
	3	.832	.700	7	16	102055-7
	3	.732	.600	6	14	102055-6
	3	.632	.500	5	12	102055-5
	3	.532	.400	4	10	102055-4
	3	.432	.300	3	8	102055-3
	3	.332	.200	2	6	102055-2
	3	1.032	.900	9	20	102055-1
	3	1.032	.900	9	20	102055-1

SUPERCEDED BY 1-103164-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL:

HOUSING:
FLAME RETARDANT
COLOR: Y. BLACK
POSTS:PHOS BRONZE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

FINISH

SEE TABLE

DWN
H. MOLL
16NOV87

CHK
R. FEIDT
16NOV87

APVD
R. FLICKER
16NOV87

NAME

SIZE
A1

CAGE CODE
00779

DRAWING NO.
102055

RESTRICTED TO

—

TE Connectivity

HEADER ASSY, MOD II, DBL ROW,
.100X.100 C/L, RIGHT ANGLE,
(3) SIDED SHROUD

CUSTOMER DRAWING

SCALE
4:1

SHEET
1

OF
1

REV
K2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-102055-3](#)