



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	W1	PART STATUS UPDATED IN PART LIST TABLE	07FEB2018	SD	PS



- 1 STAGGERS: UP TO 9 POS—(2 REQD) ON THE OUTSIDE ENDS OF THE HOUSING 10 TO 19 POS—(3 REQD) TWO ON THE OUTSIDE ENDS AND ONE CENTERED ON THE HOUSING. 19 POS AND LARGER—(4 REQD) TWO ON THE OUTSIDE ENDS AND TWO SPACED EVENLY WITHIN THE REMAINING LENGTH OF THE HOUSING.
 - 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
 - 3 FOR 3 POS (3—4 & 3—9 ONLY) ONE SLOT, .215 WIDE.
 - 4 INDICATED PARTS ARE PACKAGED IN "GANG-OF-TUBES".
 - 5 RECESSED DATE CODE
 - 6 INDICATED PARTS ARE PACKAGED IN "SINGLE TUBES".
 - 7 .000015 GOLD ON THE CONTACT AREA, .000100—.000200 MATTE TIN—LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL.
 - 8 .000015 GOLD ON THE CONTACT AREA, .000100—.000200 MATTE TIN ON THE SOLDER TAIL, ALL OVER .000050 NICKEL.
 - 9 PRELIMINARY PART
 - 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

SECTION X-X



RECOMMENDED HOLE LAYOUT FOR MANUAL INSERTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.RINGLY	11JUN85	 TE Connectivity Ltd.			
		CHK D.DUPLER	11JUN85				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, MOD II,HEADER,SINGLE ROW .100 C/L, RIGHT ANGLE,WITH .025 SQ POST —			
		APVD —					
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL RETARDANT THERMOPLASTIC, COLOR—BLACK — POSTS—PHOS. BRONZE		FINISH SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C-102203	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 2	REV W1	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

	.820	.740	.600	6	7	8-102203-6	OBSOLETE
	.420	.340	.200	2	 3	8-102203-4	
	2.620	2.540	2.400	24	25	7-102203-2	OBSOLETE 
	2.520	2.440	2.300	23	24	7-102203-1	OBSOLETE 
	2.420	2.340	2.200	22	23	7-102203-0	OBSOLETE 
	2.320	2.240	2.100	21	22	6-102203-9	
	2.220	2.140	2.000	20	21	6-102203-8	OBSOLETE 
	2.120	2.040	1.900	19	20	6-102203-7	
	2.020	1.940	1.800	18	19	6-102203-6	OBSOLETE 
	1.920	1.840	1.700	17	18	6-102203-5	
	1.820	1.740	1.600	16	17	6-102203-4	OBSOLETE 
	1.720	1.640	1.500	15	16	6-102203-3	
	1.620	1.540	1.400	14	15	6-102203-2	
	1.520	1.440	1.300	13	14	6-102203-1	
	1.420	1.340	1.200	12	13	6-102203-0	
	1.320	1.240	1.100	11	12	5-102203-9	
	1.220	1.140	1.000	10	11	5-102203-8	
	1.120	1.040	.900	9	10	5-102203-7	
	1.020	.940	.800	8	9	5-102203-6	OBSOLETE 
	.920	.840	.700	7	8	5-102203-5	
	.820	.740	.600	6	7	5-102203-4	
	.720	.640	.500	5	6	5-102203-3	
	.620	.540	.400	4	5	5-102203-2	
	.520	.440	.300	3	4	5-102203-1	
PLATING	D	C	B	A	NO OF POS	ASSEMBLY PART NUMBER	

		910 OBSOLETE	8	1.720	1.640	1.500	15	16	4-102203-0
SUPERSEDED BY 8-102203-4			8	.420	.340	.200	2	3 3	3-102203-9
	910	OBSOLETE	8	1.020	.940	.800	8	9	3-102203-8
SUPERSEDED BY 5-102203-1			8	.520	.440	.300	3	4	3-102203-7
	610	OBSOLETE	7	.820	.740	.600	6	7	3-102203-6
SUPERSEDED BY 103361-8			7	1.120	1.040	.900	9	4 10	3-102203-5
			7	.420	.340	.200	2	3 3	3-102203-4
		OBSOLETE	7	3.720	3.640	3.500	35	36	3-102203-3
		OBSOLETE	7	3.620	3.540	3.400	34	35	3-102203-2
		OBSOLETE	7	3.520	3.440	3.300	33	34	3-102203-1
		OBSOLETE	7	3.420	3.340	3.200	32	33	3-102203-0
		OBSOLETE	7	3.320	3.240	3.100	31	32	2-102203-9
		OBSOLETE	7	3.220	3.140	3.000	30	31	2-102203-8
		OBSOLETE	7	3.120	3.040	2.900	29	30	2-102203-7
		OBSOLETE	7	3.020	2.940	2.800	28	29	2-102203-6
		OBSOLETE	7	2.920	2.840	2.700	27	28	2-102203-5
		OBSOLETE	7	2.820	2.740	2.600	26	27	2-102203-4
		OBSOLETE	7	2.720	2.640	2.500	25	26	2-102203-3
	10	OBSOLETE	7	2.620	2.540	2.400	24	25	2-102203-2
			7	2.520	2.440	2.300	23	24	2-102203-1
	10	OBSOLETE	7	2.420	2.340	2.200	22	23	2-102203-0
	10		7	2.320	2.240	2.100	21	22	1-102203-9
	10	OBSOLETE	7	2.220	2.140	2.000	20	21	1-102203-8
	10		7	2.120	2.040	1.900	19	20	1-102203-7
	10	OBSOLETE	7	2.020	1.940	1.800	18	19	1-102203-6
			7	1.920	1.840	1.700	17	18	1-102203-5
	10	OBSOLETE	7	1.820	1.740	1.600	16	17	1-102203-4
			7	1.720	1.640	1.500	15	16	1-102203-3
			7	1.620	1.540	1.400	14	15	1-102203-2
			7	1.520	1.440	1.300	13	14	1-102203-1
			7	1.420	1.340	1.200	12	13	1-102203-0
			7	1.320	1.240	1.100	11	12	102203-9
			7	1.220	1.140	1.000	10	11	102203-8
			7	1.120	1.040	.900	9	10	102203-7
	10		7	1.020	.940	.800	8	9	102203-6
			7	.920	.840	.700	7	8	102203-5
			7	.820	.740	.600	6	7	102203-4
			7	.720	.640	.500	5	6	102203-3
			7	.620	.540	.400	4	5	102203-2
			7	.520	.440	.300	3	4	102203-1
			FINISH	D	C	B	A	NO OF POS	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.RINGLY 11JUN85		 TE Connectivity Ltd.						
		CHK D.DUPLER 11JUN85								
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, MOD II,HEADER,SINGLE ROW .100 C/L, RIGHT ANGLE,WITH .025 SQ POST —						
		APVD —								
		PRODUCT SPEC —								
		APPLICATION SPEC —		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO		
MATERIAL —		FINISH SEE TABLE		WEIGHT —	A2	00779	C-102203	—		
CUSTOMER DRAWING				SCALE	1:1		SHEET	2 OF 2	REV	W1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-102203-2](#)