





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	W1	PART STATUS UPDATED IN PART LIST TABLE	07FEB2018	SD	PS

D


C

B

A



RECOMMENDED HOLE LAYOUT
FOR MANUAL INSERTION



SECTION X-X



STANDOFFS: UP TO 9 POS-(2 REQD) ON THE OUTSIDE ENDS OF THE HOUSING
10 TO 19 POS-(3 REQD) TWO ON THE OUTSIDE ENDS AND ONE CENTERED
ON THE HOUSING. 19 POS AND LARGER-(4 REQD) TWO ON THE OUTSIDE ENDS
AND TWO SPACED EVENLY WITHIN THE REMAINING LENGTH OF THE HOUSING.



POINT OF MEASUREMENT FOR PLATING THICKNESS.



FOR 3 POS (3--4 & 3--9 ONLY) ONE SLOT, .215 WIDE.



INDICATED PARTS ARE PACKAGED IN "GANG-OF-TUBES".



RECESSED DATE CODE



INDICATED PARTS ARE PACKAGED IN "SINGLE TUBES".



.000015 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN-LEAD
ON THE SOLDER TAIL, ALL OVER .000050 NICKEL.



.000015 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN
ON THE SOLDER TAIL, ALL OVER .000050 NICKEL.



PRELIMINARY PART



OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

D

C

B

A

102203

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.RINGLY 11JUN85	TE Connectivity Ltd.		
		CHK D.DUPLER 11JUN85			
DIMENSIONS: INCHES		APVD —	NAME		
		PRODUCT SPEC	ASSEMBLY, MOD II, HEADER, SINGLE ROW .100 C/L, RIGHT ANGLE, WITH .025 SQ POST		
		APPLICATION SPEC			
MATERIAL RETARDANT THERMOPLASTIC, COLOR-BLACK POSTS-PHOS BRONZE		WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-102203
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 of 2	REV W1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-102203-4](#)