

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION






ALL RIGHTS RESERVED

© COPYRIGHT

 $\Theta_f =$

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APR
	L3	PART STATUS UPATED IN PART LIST TABLE	09FEB2018	SD	PS



RECOMENDED HOLE LAYOUT

- | | |
|---|---|
| 1 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING |
| 2 | POINT OF MEASUREMENT FOR PLATING THICKNESS |
| 3 | FINISH: POSTS: .000015 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL |
| 4 | FINISH: POSTS: .000015 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL |
| 5 | MATERIALS: HOUSING- FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK
POSTS- PHOS BRONZE |
| 6 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |

OBSOLETE	△	3.506	.106	3.732	3.600	36	74	8-102618-5	
	△	3.406	.106	3.632	3.500	35	72	8-102618-4	
	△	3.306	.106	3.532	3.400	34	70	8-102618-3	
	△	3.206	.106	3.432	3.300	33	68	8-102618-2	
	△	3.106	.106	3.332	3.200	32	66	8-102618-1	
	△	3.006	.106	3.232	3.100	31	64	8-102618-0	
OBSOLETE	△	2.906	.106	3.132	3.000	30	62	7-102618-9	
	△	2.806	.106	3.032	2.900	29	60	7-102618-8	
	△	2.706	.106	2.932	2.800	28	58	7-102618-7	
	△	2.606	.106	2.832	2.700	27	56	7-102618-6	
OBSOLETE	△	2.506	.106	2.732	2.600	26	54	7-102618-5	
	△	2.406	.106	2.632	2.500	25	52	7-102618-4	
	△	2.306	.106	2.532	2.400	24	50	7-102618-3	
OBSOLETE	△	2.206	.106	2.432	2.300	23	48	7-102618-2	
	△	2.106	.106	2.332	2.200	22	46	7-102618-1	
	△	2.006	.106	2.232	2.100	21	44	7-102618-0	
OBSOLETE	△	1.906	.106	2.132	2.000	20	42	6-102618-9	
	△	1.806	.106	2.032	1.900	19	40	6-102618-8	
	△	1.706	.106	1.932	1.800	18	38	6-102618-7	
	△	1.606	.106	1.832	1.700	17	36	6-102618-6	
OBSOLETE	△	1.506	.106	1.732	1.600	16	34	6-102618-5	
	△	1.406	.106	1.632	1.500	15	32	6-102618-4	
△ OBSOLETE	△	1.306	.106	1.532	1.400	14	30	6-102618-3	
	△	1.206	.106	1.432	1.300	13	28	6-102618-2	
	△	1.106	.106	1.332	1.200	12	26	6-102618-1	
	△	1.006	.106	1.232	1.100	11	24	6-102618-0	
	△	.906	.106	1.132	1.000	10	22	5-102618-9	
	△	.806	.106	1.032	.900	9	20	5-102618-8	
	△	—	.406	.932	.800	8	18	5-102618-7	
	△	—	.306	.832	.700	7	16	5-102618-6	
	△	—	.306	.732	.600	6	14	5-102618-5	
	△	—	.206	.632	.500	5	12	5-102618-4	
	△	—	.206	.532	.400	4	10	5-102618-3	
	△	—	.106	.432	.300	3	8	5-102618-2	
	△	—	.106	.332	.200	2	6	5-102618-1	
	OBSOLETE	△	3.506	.106	3.732	3.600	36	74	3-102618-5
		△	3.406	.106	3.632	3.500	35	72	3-102618-4
△		3.306	.106	3.532	3.400	34	70	3-102618-3	
△		3.206	.106	3.432	3.300	33	68	3-102618-2	
△		3.106	.106	3.332	3.200	32	66	3-102618-1	
△		3.006	.106	3.232	3.100	31	64	3-102618-0	
OBSOLETE	△	2.906	.106	3.132	3.000	30	62	2-102618-9	
	△	2.806	.106	3.032	2.900	29	60	2-102618-8	
	△	2.706	.106	2.932	2.800	28	58	2-102618-7	
	△	2.606	.106	2.832	2.700	27	56	2-102618-6	
OBSOLETE	△	2.506	.106	2.732	2.600	26	54	2-102618-5	
	△	2.406	.106	2.632	2.500	25	52	2-102618-4	
	△	2.306	.106	2.532	2.400	24	50	2-102618-3	
OBSOLETE	△	2.206	.106	2.432	2.300	23	48	2-102618-2	
	△	2.106	.106	2.332	2.200	22	46	2-102618-1	
	△	2.006	.106	2.232	2.100	21	44	2-102618-0	
OBSOLETE	△	1.906	.106	2.132	2.000	20	42	1-102618-9	
	△	1.806	.106	2.032	1.900	19	40	1-102618-8	
	△	1.706	.106	1.932	1.800	18	38	1-102618-7	
	△	1.606	.106	1.832	1.700	17	36	1-102618-6	
5-102618-9	△	1.506	.106	1.732	1.600	16	34	1-102618-5	
	△	1.406	.106	1.632	1.500	15	32	1-102618-4	
	△	1.306	.106	1.532	1.400	14	30	1-102618-3	
	△	1.206	.106	1.432	1.300	13	28	1-102618-2	
	△	1.106	.106	1.332	1.200	12	26	1-102618-1	
	△	1.006	.106	1.232	1.100	11	24	1-102618-0	
	△	.906	.106	1.132	1.000	10	22	—102618-9	
	△	.806	.106	1.032	.900	9	20	102618-8	
	△	—	.406	.932	.800	8	18	102618-7	
	△	—	.306	.832	.700	7	16	102618-6	
	△	—	.306	.732	.600	6	14	102618-5	
	△	—	.206	.632	.500	5	12	102618-4	
	△	—	.206	.532	.400	4	10	102618-3	
	△	—	.106	.432	.300	3	8	102618-2	
	△	—	.106	.332	.200	2	6	102618-1	
	PLATING	E	D	C	B	A	NO. OF POSN	ASSEMBLY PART NUMBER	

SUP BY 5-102618-9

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN H. MOLL 4-9-87	 TE Connectivity		
		CHK LA. MAYER 4-9-87			
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, HEADER, MOD II, .025 SQ POST, DBL ROW, .100 X .100 C/L WITH DETENTS	
INCHES		APVD R. FEJDT 4-9-87			
	0 PLC ± —	PRODUCT SPEC			
	1 PLC ± —	—			
	2 PLC ± —	—			
	3 PLC ± .005	APPLICATION SPEC			
		4 PLC ± —	—		
MATERIAL 		ANGLES FINISH	—		
SEE TABLE		WEIGHT	—		
		CUSTOMER DRAWING			
		SIZE	CAGE CODE	DRAWING NO	RESTRICTED
		A1	00779	①-102618	—
		SCALE	4:1	SHEET	1 OF 1
		REV			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-102618-7](#)