





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		G	ECO-05-007262	09JAN06	BSV	MM




SECTION D-D



SECTION A-A



SECTION B-B



SECTION C-C
INSULATION RANGE - .020-.040 DIA

- 1

.000030 ON CONTACT AREA, .000100-.000200 93/7 TIN LEAD IN CRIMP AREA "Z", ALL OVER .000050 NICKEL.
- 2

REELED FOR MINI APPLICATOR.
- 3

SHEARED EDGES PERMITTED TO BE UNPLATED.
- 4


.000015 GOLD IN AREA "K", .000100-.000200 BRIGHT TIN-LEAD IN AREA "Z", ALL OVER .000050 NICKEL.
- 5

.000015 GOLD IN CONTACT AREA, .000050 NICKEL ENTIRE CONTACT.
- 6

POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 7

.000030 ON CONTACT AREA, .000100-.000200 MATTE TIN IN CRIMP AREA "Z", ALL OVER .000050 NICKEL.

	LOOSE PIECE	3 7	5-102920-2
	—	3 7	5-102920-1
OBSOLETE	LOOSE PIECE	3 5	102920-8
OBSOLETE	—	3 5	102920-7
OBSOLETE	LOOSE PIECE	3 4	102920-5
OBSOLETE	—	3 4	102920-4
	LOOSE PIECE	3 1	102920-2
	—	3 1	102920-1
	REMARKS	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KATE HELM 03MAY89	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608				
DIMENSIONS: INCHES		CHK C. OBERMAN 02JUN89	NAME CONTACT, MOD IV 1/2, RECEPTACLE, CRIMP SNAP-IN				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. GESFORD 02JUN89					
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± ± - FINISH	PRODUCT SPEC 108-25021 APPLICATION SPEC 114-25003					
MATERIAL CU-SN-P ALLOY 521 .008 THK COML		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=102920	RESTRICTED TO -	
SEE TABLE		CUSTOMER DRAWING			SCALE 10:1	SHEET 1 OF 1	REV G

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-102920-2](#)