



LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	APVD
		G		REVISED PER ECO-14-000068	23APR2014	NK

- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 4 BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

OBSOLETE	3.984	3.900	39	40	4-102978-0
	3.884	3.800	38	39	3-102978-9
OBSOLETE	3.784	3.700	37	38	3-102978-8
	3.684	3.600	36	37	3-102978-7
OBSOLETE	3.584	3.500	35	36	3-102978-6
	3.484	3.400	34	35	3-102978-5
OBSOLETE	3.384	3.300	33	34	3-102978-4
	3.284	3.200	32	33	3-102978-3
OBSOLETE	3.184	3.100	31	32	3-102978-2
	3.084	3.000	30	31	3-102978-1
OBSOLETE	2.984	2.900	29	30	3-102978-0
	2.884	2.800	28	29	2-102978-9
OBSOLETE	2.784	2.700	27	28	2-102978-8
	2.684	2.600	26	27	2-102978-7
OBSOLETE	2.584	2.500	25	26	2-102978-6
	2.484	2.400	24	25	2-102978-5
OBSOLETE	2.384	2.300	23	24	2-102978-4
	2.284	2.200	22	23	2-102978-3
OBSOLETE	2.184	2.100	21	22	2-102978-2
	2.084	2.000	20	21	2-102978-1
OBSOLETE	1.984	1.900	19	20	2-102978-0
	1.884	1.800	18	19	1-102978-9
OBSOLETE	1.784	1.700	17	18	1-102978-8
	1.684	1.600	16	17	1-102978-7
OBSOLETE	1.584	1.500	15	16	1-102978-6
	1.484	1.400	14	15	1-102978-5
OBSOLETE	1.384	1.300	13	14	1-102978-4
	1.284	1.200	12	13	1-102978-3
OBSOLETE	1.184	1.100	11	12	1-102978-2
	1.084	1.000	10	11	1-102978-1
OBSOLETE	.984	.900	9	10	1-102978-0
	.884	.800	8	9	1-102978-9
OBSOLETE	.784	.700	7	8	1-102978-8
	.684	.600	6	7	1-102978-7
OBSOLETE	.584	.500	5	6	1-102978-6
	.484	.400	4	5	1-102978-5
OBSOLETE	.384	.300	3	4	1-102978-4
	.284	.200	2	3	1-102978-3
OBSOLETE	.184	.100	1	2	1-102978-2
	.084	—	—	1	1-102978-1
OBSOLETE	C	B	A	NO OF POSN	PART NUMBER
	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL	15OCT87	 TE Connectivity				
DIMENSIONS: INCHES		CHK T. CLARK	20OCT87					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	APVD T. CLARK	20OCT87	NAME HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100 CL, RIGHT ANGLE, W/ .025 SQ POSTS				
		PRODUCT SPEC —						
			APPLICATION SPEC —		SIZE A2	CAGE CODE 00779	DRAWING NO C=102978	RESTRICTED TO —
		MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK POSTS: COPPER ALLOY	FINISH POSTS .000030 GOLD ON CONTACT AREA .00010- .000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL	WEIGHT —	CUSTOMER DRAWING			
			SCALE 4:1	SHEET 1 of 1	REV G			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-102978-5](#)