

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-15-010494	14JUL2015	DW	CW
	B	ECR-15-013292	24SEP2015	DL	CW
	B1	ECR-15-017530	02DEC2015	GY	CW
	B2	ECR-16-015492	08NOV2016	QY	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:

INSULATION MATERIAL: PC

RATED VOLTAGE: 250 V

RATED CURRENT: 10 A

INSULATION RESISTANCE: $\geq 400M\Omega$

RATED IMPULSE VOLTAGE: 4 KV

POLLUTION DEGREE: 3

FLAMMABILITY: UL94V-0

MATING CYCLES: 500 CYCLES

WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)

CONTACT TYPE: CRIMP CONTACT

2. CONTACT NEED TO BE ORDERED SEPARATELY.

(ORDER No. REFER TO DRAWING: T20200X10XX000)

注释:

1. 技术参数:

绝缘材料: PC

额定电压: 250V

额定电流: 10A

绝缘电阻: $\geq 400M\Omega$

额定脉冲电压: 4 KV

污染等级: 3

阻燃等级: UL94V-0



插拔次数: 500次

接线范围: 0.14-2.5 mm² (26-14 AWG)




接线类型: 冷压接

2. 端子需要单独订购.


(订货号参考图面: T20200X10XX000)



M4 SCREW RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4 螺丝, 推荐锁紧力矩 1.2Nm



4X M3 SCREW RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐锁紧力矩 0.5Nm



PANEL CUT OUT FOR INSERTS FOR USE
WITHOUT HOODS/HOUSINGS
不用防护外壳时芯件的安装开孔图

TYPE-1, T2020402101-000, TE LOGO
类型-1, T2020402101-000, TE LOGO

TYPE-2, T2020402101-001, STAINLESS STEEL SCREW, TE LOGO
类型-2, T2020402101-001, 不锈钢螺丝, TE LOGO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 16DEC2014

RAGHAVENDRA H M

CHK 16DEC2014

CHRIS WANG

APVD 16DEC2014

XU XIANG

PRODUCT SPEC

108-137042

APPLICATION SPEC

114-137042

WEIGHT -

Customer Drawing

TE

TE Connectivity

NAME

HD-040-M

SIZE

A3

CAGE CODE

DRAWING NO

00779

T2020402101000

RESTRICTED TO

-

SCALE

1:1





SHEET

1 OF 2

REV

B2


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



NOTE:
SEE SHEET 1


注释:
见页 1

TYPE-3, T2020402101-002, STAINLESS STEEL SCREW, NO LOGO
类型-3, T2020402101-002, 不锈钢螺丝, 无LOGO



ALL DIMENSIONS ARE SAME AS TYPE 1,
EXCEPT THOSE DEFINED IN THIS TYPE.
除了在本类型中定义的尺寸外, 其它尺寸同类型 1

T2020402101-002	HD-040-M	HD-040 MALE INSERT, STAINLESS STEEL SCREW, NO LOGO HD-040 公插, 不锈钢螺丝, 无LOGO	TYPE-3 类 型-3
T2020402101-001	HD-040-M	HD-040 MALE INSERT, STAINLESS STEEL SCREW HD-040 公插, 不锈钢螺丝	TYPE-2 类 型-2
T2020402101-000	HD-040-M	HD-040 MALE INSERT HD-040 公插	TYPE-1 类 型-1
PART NUMBER 料 号	PART DESCRIPTION 描 述		TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16DEC2014 RAGHAVENDRA H M	 TE Connectivity		
		CHK 16DEC2014 CHRIS WANG			
DIMENSIONS: mm		APVD 16DEC2014 XU XIANG	NAME HD-040-M		
		PRODUCT SPEC 108-137042			
		APPLICATION SPEC 114-137042	SIZE CAGE CODE DRAWING NO RESTRICTED TO A300779 C-T2020402101000 -		
MATERIAL -	FINISH -	WEIGHT -			
		Customer Drawing	SCALE 1:1	SHEET 2 OF 2	REV B2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HD-040-M](#)