






REVISIONS				
P	LTR	DESCRIPTION	DATE	APPD
K3		PART STATUS UPDATED IN PART LIST TABLE	19FEB2018	SD PS

- 1 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 PACKAGED IN SINGLE TUBES
- 4 POSTS: .000030 GOLD IN CONTACT AREA .000100-.000200 MATTE TIN LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 5 POSTS: .000030 GOLD IN CONTACT AREA .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

PLATING	E	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER
6	3	6	6	6	6	2	8-103166-6
6	6	6	6	6	6	36	8-103166-5
6	6	6	6	6	6	35	8-103166-4
6	6	6	6	6	6	34	8-103166-3
6	6	6	6	6	6	33	8-103166-2
6	6	6	6	6	6	32	8-103166-1
6	6	6	6	6	6	31	8-103166-0
6	6	6	6	6	6	30	7-103166-9
6	6	6	6	6	6	29	7-103166-8
6	6	6	6	6	6	28	7-103166-7
6	6	6	6	6	6	27	7-103166-6
6	6	6	6	6	6	26	7-103166-5
6	6	6	6	6	6	25	7-103166-4
6	6	6	6	6	6	24	7-103166-3
6	6	6	6	6	6	23	7-103166-2
6	6	6	6	6	6	22	7-103166-1
6	6	6	6	6	6	21	7-103166-0
6	6	6	6	6	6	20	6-103166-9
6	6	6	6	6	6	19	6-103166-8
6	6	6	6	6	6	18	6-103166-7
6	6	6	6	6	6	17	6-103166-6
6	6	6	6	6	6	16	6-103166-5
6	6	6	6	6	6	15	6-103166-4
6	6	6	6	6	6	14	6-103166-3
6	6	6	6	6	6	13	6-103166-2
6	6	6	6	6	6	12	6-103166-1
6	6	6	6	6	6	11	6-103166-0
6	6	6	6	6	6	10	5-103166-9
6	6	6	6	6	6	9	5-103166-8
6	6	6	6	6	6	8	5-103166-7
6	6	6	6	6	6	7	5-103166-6
6	6	6	6	6	6	6	5-103166-5
6	6	6	6	6	6	5	5-103166-4
6	6	6	6	6	6	4	5-103166-3
6	6	6	6	6	6	3	5-103166-2
6	6	6	6	6	6	2	5-103166-1
6	3	6	6	6	6	2	3-103166-6
6	6	6	6	6	6	36	3-103166-5
6	6	6	6	6	6	35	3-103166-4
6	6	6	6	6	6	34	3-103166-3
6	6	6	6	6	6	33	3-103166-2
6	6	6	6	6	6	32	3-103166-1
6	6	6	6	6	6	31	3-103166-0
6	6	6	6	6	6	30	2-103166-9
6	6	6	6	6	6	29	2-103166-8
6	6	6	6	6	6	28	2-103166-7
6	6	6	6	6	6	27	2-103166-6
6	6	6	6	6	6	26	2-103166-5
6	6	6	6	6	6	25	2-103166-4
6	6	6	6	6	6	24	2-103166-3
6	6	6	6	6	6	23	2-103166-2
6	6	6	6	6	6	22	2-103166-1
6	6	6	6	6	6	21	2-103166-0
6	6	6	6	6	6	20	1-103166-9
6	6	6	6	6	6	19	1-103166-8
6	6	6	6	6	6	18	1-103166-7
6	6	6	6	6	6	17	1-103166-6
6	6	6	6	6	6	16	1-103166-5
6	6	6	6	6	6	15	1-103166-4
6	6	6	6	6	6	14	1-103166-3
6	6	6	6	6	6	13	1-103166-2
6	6	6	6	6	6	12	1-103166-1
6	6	6	6	6	6	11	1-103166-0
6	6	6	6	6	6	10	103166-9
6	6	6	6	6	6	9	103166-8
6	6	6	6	6	6	8	103166-7
6	6	6	6	6	6	7	103166-6
6	6	6	6	6	6	6	103166-5
6	6	6	6	6	6	5	103166-4
6	6	6	6	6	6	4	103166-3
6	6	6	6	6	6	3	103166-2
6	6	6	6	6	6	2	103166-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DRAWN: H MOLL 27AUG87	DATE: 27AUG87
INCHES:	0 PLC ± .005	CHK: R FEIDT 28AUG87	DATE: 28AUG87
	1 PLC ± .005	APVD: R FLICKER 29AUG87	DATE: 29AUG87
	2 PLC ± .005	NAME: R FLICKER	
	3 PLC ± .005	PRODUCT SPEC:	
	4 PLC ± .005	APPLICATION SPEC:	
	ANGLES ± .005	SIZE: A1	CAGE CODE: 100779
		DRAWING NO: 103166	RESTRICTED TO:
MATERIAL: HOUSING: PLATE RETARDANT THERMOPLASTIC; COLOR: BLACK; POSTS: PHOS BRONZE	FINISH: SEE TABLE	WEIGHT: -	CUSTOMER DRAWING

STE TE Connectivity

HDR ASSY, MOD II, SHROUDED, 4 SIDES, DBL ROW, .100X.100 WITH .025 SQ POSTS

SCALE: 4:1 SHEET: 1 OF 1 REV: K3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-103166-3](#)