



|   |            |   |          |      |       |       |       |       |            |    |            |
|---|------------|---|----------|------|-------|-------|-------|-------|------------|----|------------|
| 5 | OBSELETE   | 4 | 3.490    | .190 | 3.800 | 3.500 | 35    | 72    | 8-103167-3 |    |            |
|   | OBSELETE   |   | 3.390    | .190 | 3.700 | 3.400 | 34    | 70    | 8-103167-2 |    |            |
| 5 | OBSELETE   | 4 | 3.290    | .190 | 3.600 | 3.300 | 33    | 68    | 8-103167-1 |    |            |
|   |            | 4 | 3.190    | .190 | 3.500 | 3.200 | 32    | 66    | 8-103167-0 |    |            |
| 5 | OBSELETE   | 4 | 3.090    | .190 | 3.400 | 3.100 | 31    | 64    | 7-103167-9 |    |            |
| 5 | OBSELETE   | 4 | 2.990    | .190 | 3.300 | 3.000 | 30    | 62    | 7-103167-8 |    |            |
| 5 | OBSELETE   | 4 | 2.890    | .190 | 3.200 | 2.900 | 29    | 60    | 7-103167-7 |    |            |
|   |            | 4 | 2.790    | .190 | 3.100 | 2.800 | 28    | 58    | 7-103167-6 |    |            |
| 5 | OBSELETE   | 4 | 2.690    | .190 | 3.000 | 2.700 | 27    | 56    | 7-103167-5 |    |            |
| 5 | OBSELETE   | 4 | 2.590    | .190 | 2.900 | 2.600 | 26    | 54    | 7-103167-4 |    |            |
| 5 | OBSELETE   | 4 | 2.490    | .190 | 2.800 | 2.500 | 25    | 52    | 7-103167-3 |    |            |
| 5 | OBSELETE   | 4 | 2.390    | .190 | 2.700 | 2.400 | 24    | 50    | 7-103167-2 |    |            |
| 5 | OBSELETE   | 4 | 2.290    | .190 | 2.600 | 2.300 | 23    | 48    | 7-103167-1 |    |            |
| 5 | OBSELETE   | 4 | 2.190    | .190 | 2.500 | 2.200 | 22    | 46    | 7-103167-0 |    |            |
| 5 | OBSELETE   | 4 | 2.090    | .190 | 2.400 | 2.100 | 21    | 44    | 6-103167-9 |    |            |
| 5 | OBSELETE   | 4 | 1.990    | .190 | 2.300 | 2.000 | 20    | 42    | 6-103167-8 |    |            |
| 5 | OBSELETE   | 4 | 1.890    | .190 | 2.200 | 1.900 | 19    | 40    | 6-103167-7 |    |            |
|   |            | 4 | 1.790    | .190 | 2.100 | 1.800 | 18    | 38    | 6-103167-6 |    |            |
| 5 | OBSELETE   | 4 | 1.690    | .190 | 2.000 | 1.700 | 17    | 36    | 6-103167-5 |    |            |
| 5 | OBSELETE   | 4 | 1.590    | .190 | 1.900 | 1.600 | 16    | 34    | 6-103167-4 |    |            |
| 5 | OBSELETE   | 4 | 1.490    | .190 | 1.800 | 1.500 | 15    | 32    | 6-103167-3 |    |            |
| 5 | OBSELETE   | 4 | 1.390    | .190 | 1.700 | 1.400 | 14    | 30    | 6-103167-2 |    |            |
|   |            | 4 | 1.290    | .190 | 1.600 | 1.300 | 13    | 28    | 6-103167-1 |    |            |
| 5 | OBSELETE   | 4 | 1.190    | .190 | 1.500 | 1.200 | 12    | 26    | 6-103167-0 |    |            |
|   |            | 4 | 1.090    | .190 | 1.400 | 1.100 | 11    | 24    | 5-103167-9 |    |            |
|   |            | 4 | .990     | .190 | 1.300 | 1.000 | 10    | 22    | 5-103167-8 |    |            |
|   |            | 4 | .890     | .190 | 1.200 | .900  | 9     | 20    | 5-103167-7 |    |            |
|   |            | 4 | —        | .490 | 1.100 | .800  | 8     | 18    | 5-103167-6 |    |            |
|   |            | 4 | —        | .390 | 1.000 | .700  | 7     | 16    | 5-103167-5 |    |            |
|   |            | 4 | —        | .390 | .900  | .600  | 6     | 14    | 5-103167-4 |    |            |
|   |            | 4 | —        | .290 | .800  | .500  | 5     | 12    | 5-103167-3 |    |            |
|   |            | 4 | —        | .290 | .700  | .400  | 4     | 10    | 5-103167-2 |    |            |
|   |            | 4 | —        | .190 | .600  | .300  | 3     | 8     | 5-103167-1 |    |            |
|   |            | 5 | OBSELETE | 3    | 3.490 | .190  | 3.800 | 3.500 | 35         | 72 | 3-103167-3 |
|   |            | 5 | OBSELETE | 3    | 3.390 | .190  | 3.700 | 3.400 | 34         | 70 | 3-103167-2 |
| 5 | OBSELETE   | 3 | 3.290    | .190 | 3.600 | 3.300 | 33    | 68    | 3-103167-1 |    |            |
|   |            | 3 | 3.190    | .190 | 3.500 | 3.200 | 32    | 66    | 3-103167-0 |    |            |
| 5 | OBSELETE   | 3 | 3.090    | .190 | 3.400 | 3.100 | 31    | 64    | 2-103167-9 |    |            |
| 5 | OBSELETE   | 3 | 2.990    | .190 | 3.300 | 3.000 | 30    | 62    | 2-103167-8 |    |            |
| 5 | OBSELETE   | 3 | 2.890    | .190 | 3.200 | 2.900 | 29    | 60    | 2-103167-7 |    |            |
|   |            | 3 | 2.790    | .190 | 3.100 | 2.800 | 28    | 58    | 2-103167-6 |    |            |
| 5 | OBSELETE   | 3 | 2.690    | .190 | 3.000 | 2.700 | 27    | 56    | 2-103167-5 |    |            |
| 5 | OBSELETE   | 3 | 2.590    | .190 | 2.900 | 2.600 | 26    | 54    | 2-103167-4 |    |            |
| 5 | OBSELETE   | 3 | 2.490    | .190 | 2.800 | 2.500 | 25    | 52    | 2-103167-3 |    |            |
| 5 | OBSELETE   | 3 | 2.390    | .190 | 2.700 | 2.400 | 24    | 50    | 2-103167-2 |    |            |
|   |            | 3 | 2.290    | .190 | 2.600 | 2.300 | 23    | 48    | 2-103167-1 |    |            |
| 5 | OBSELETE   | 3 | 2.190    | .190 | 2.500 | 2.200 | 22    | 46    | 2-103167-0 |    |            |
| 5 | OBSELETE   | 3 | 2.090    | .190 | 2.400 | 2.100 | 21    | 44    | 1-103167-9 |    |            |
| 5 | OBSELETE   | 3 | 1.990    | .190 | 2.300 | 2.000 | 20    | 42    | 1-103167-8 |    |            |
| 5 | OBSELETE   | 3 | 1.890    | .190 | 2.200 | 1.900 | 19    | 40    | 1-103167-7 |    |            |
|   |            | 3 | 1.790    | .190 | 2.100 | 1.800 | 18    | 38    | 1-103167-6 |    |            |
| 5 | OBSELETE   | 3 | 1.690    | .190 | 2.000 | 1.700 | 17    | 36    | 1-103167-5 |    |            |
| 5 | OBSELETE   | 3 | 1.590    | .190 | 1.900 | 1.600 | 16    | 34    | 1-103167-4 |    |            |
|   |            | 3 | 1.490    | .190 | 1.800 | 1.500 | 15    | 32    | 1-103167-3 |    |            |
| 5 | OBSELETE   | 3 | 1.390    | .190 | 1.700 | 1.400 | 14    | 30    | 1-103167-2 |    |            |
|   |            | 3 | 1.290    | .190 | 1.600 | 1.300 | 13    | 28    | 1-103167-1 |    |            |
| 5 | SUPERSEDED | 3 | 1.190    | .190 | 1.500 | 1.200 | 12    | 26    | 1-103167-0 |    |            |
|   |            | 3 | 1.090    | .190 | 1.400 | 1.100 | 11    | 24    | 103167-9   |    |            |
|   |            | 3 | .990     | .190 | 1.300 | 1.000 | 10    | 22    | 103167-8   |    |            |
|   |            | 3 | .890     | .190 | 1.200 | .900  | 9     | 20    | 103167-7   |    |            |
|   |            | 3 | —        | .490 | 1.100 | .800  | 8     | 18    | 103167-6   |    |            |
|   |            | 3 | —        | .390 | 1.000 | .700  | 7     | 16    | 103167-5   |    |            |
|   |            | 3 | —        | .390 | .900  | .600  | 6     | 14    | 103167-4   |    |            |
|   |            | 3 | —        | .290 | .800  | .500  | 5     | 12    | 103167-3   |    |            |
|   |            | 3 | —        | .290 | .700  | .400  | 4     | 10    | 103167-2   |    |            |
|   |            | 3 | —        | .190 | .600  | .300  | 3     | 8     | 103167-1   |    |            |



|  |  |  |  |   |  |
|--|--|--|--|---|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.   |  | DWN: H MOLL 27JUL87<br>CHK: R FEIDT 28JUL87  |  |  TE Connectivity |  |
| DIMENSIONS:<br>INCHES<br> |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ± —<br>1 PLC ± —<br>2 PLC ± —<br>3 PLC ± .005<br>4 PLC ± —<br>ANGLES ± — |  | NAME<br>HDR ASSY, MOD II, SHROUDED,<br>4 SIDES, DBL ROW, .100X.100<br>RIGHT ANGLE, W/ .025 SQ POSTS   |  |
| MATERIAL: HOUSING: UL94V-0<br>THERMOPLASTIC POLYESTER<br>COLOR: BLACK<br>POSTS: PHOS BRONZE                    |  | FINISH<br>SEE TABLE  |  | SIZE: A1<br>CAGE CODE: 00779<br>DRAWING NO: 103167<br>RESTRICTED TO: —                                |  |
| WEIGHT: —  |  |  |  | SCALE: 4:1<br>SHEET: 1 OF 1<br>REV: N4  |  |
| CUSTOMER DRAWING   |  |  |  |   |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103167-2](#)