




LOC	DIST	REVISONS				
		REV	LTR	DESCRIPTION	DATE	OWN
GP	00	N1	REVISED	PER ECO-11-004835	11MAR11	RK



- 1 DOUBLE BAR POLARIZATION
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 3 POSTS: GOLD FLASH OVER PALLADIUM-NICKEL PLATE, .000030 MIN TOTAL ON THE MATING SUFACES, .000100 MIN TIN-LEAD PLATE ON THE SOLDER-TAILS, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
-OR-
.000030 MIN GOLD PLATE ON THE MATING SURFACES, .000100 MIN TIN-LEAD PLATE ON THE SOLDER-TAILS, .000050 MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
- 4 CENTER POLARIZATION SLOT
- 5 FOR 10 POSN ASSEMBLY, SLOT OMITTED WHERE INDICATED
- 6 OPTIONAL AMP IDENTIFICATION NUMBER (DATE CODE). LOCATION APPROXIMATELY WHERE SHOWN.
- 7 PACKAGED IN GANG OF TUBES.
- 8 NUMBER 1 POSITION.



RECOMMENDED HOLE LAYOUT
FOR MANUAL INSERTION

1	OBSELETE	2.800	2.400	24	50	1-103309-8
2	OBSELETE	1.500	1.100	11	24	1-103309-7
3	OBSELETE	1.600	1.200	12	26	1-103309-4
4	OBSELETE	1.300	.900	9	20	1-103309-3
5	OBSELETE	3.300	2.900	29	60	1-103309-2
6	OBSELETE	3.100	2.700	27	56	1-103309-1
7	OBSELETE	2.800	2.400	24	50	1-103309-0
8	OBSELETE	2.500	2.100	21	44	103309-9
9		2.300	1.900	19	40	103309-8
10		2.000	1.600	16	34	103309-7
11		1.600	1.200	12	26	103309-6
12		1.300	.900	9	20	103309-5
13	OBSELETE	1.200	.800	8	18	103309-4
14		1.100	.700	7	16	103309-3
15		1.000	.600	6	14	103309-2
16		.800	.400	4	10	103309-1
17		C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN H. MOLL 8-27-87
CHK L. MEYER 9-03-87
APVD R. FEIDT 9-03-87

TE Connectivity

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -
FINISH

MATERIAL: GLASS FILLED NYLON
OR PBT, BLACK
UL 94V-0 RATED
POSTS: BRASS

PRODUCT SPEC
108-40018

APPLICATION SPEC

SIZE: A1
CAGE CODE: 00779
DRAWING NO: 103309

RESTRICTED TO: -

CUSTOMER DRAWING

SCALE: 4:1

SHEET: 1 OF 1

REV: N1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103309-7](#)