

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

—

© COPYRIGHT

By -

ALL RIGHTS RESERVED

LOC

DIST

REVISIONS

P

LIR

DESCRIPTION

DA

DWRN

	APV
--	-----

RD/IS



REFERENCES

FCO 14 000068


26A9

4	NI
---	----

	MM
--	----




- | | |
|---|---|
| 1 | TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD |
| 2 | ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS |
| 3 | .000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL. |
| 4 | .000100-.000200 BRIGHT TIN OVER .000050 NICKEL. |
| 5 | PRELIMINARY PART - NOT RELEASED FOR PRODUCTION. |
| 6 | HOUSING MATERIAL: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK. |
| 7 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |



RECOMMENDED HOLE LAYOUT

		5	4	1.684	1.600	16	34	4-103322-7
		5	4	1.184	1.100	11	24	4-103322-6
		5	4	.584	.500	5	12	4-103322-5
	OBSOLETE		4	.284	.200	2	6	4-103322-4
		5	4	.084	—	—	2	4-103322-3
			4	3.984	3.900	39	80	4-103322-2
		5	4	.484	.400	4	10	4-103322-1
			4	3.984	3.900	39	80	4-103322-0
	OBSOLETE	7	4	3.884	3.800	38	78	3-103322-9
	OBSOLETE	7	4	3.784	3.700	37	76	3-103322-8
	OBSOLETE	7	4	3.684	3.600	36	74	3-103322-7
△	SUPERSEDED BY 8-146250-6		4	3.584	3.500	35	72	3-103322-6
	OBSOLETE	7	4	3.484	3.400	34	70	3-103322-5
	OBSOLETE	7	4	3.384	3.300	33	68	3-103322-4
	OBSOLETE	7	4	3.284	3.200	32	66	3-103322-3
	OBSOLETE	7	4	3.184	3.100	31	64	3-103322-2
	OBSOLETE	7	4	3.084	3.000	30	62	3-103322-1
	OBSOLETE	7	4	2.984	2.900	29	60	3-103322-0
	OBSOLETE	7	4	2.884	2.800	28	58	2-103322-9
	OBSOLETE	7	4	2.784	2.700	27	56	2-103322-8
	OBSOLETE	7	4	2.684	2.600	26	54	2-103322-7
	OBSOLETE	7	4	2.584	2.500	25	52	2-103322-6
			4	2.484	2.400	24	50	2-103322-5
	OBSOLETE	7	4	2.384	2.300	23	48	2-103322-4
	OBSOLETE	7	4	2.284	2.200	22	46	2-103322-3
	OBSOLETE	7	4	2.184	2.100	21	44	2-103322-2
	OBSOLETE	7	4	2.084	2.000	20	42	2-103322-1
△	SUPERSEDED BY 7-146250-0		4	1.984	1.900	19	40	2-103322-0
	OBSOLETE	7	4	1.884	1.800	18	38	1-103322-9
	OBSOLETE	7	4	1.784	1.700	17	36	1-103322-8
	OBSOLETE	7	4	1.684	1.600	16	34	1-103322-7
	OBSOLETE	7	4	1.584	1.500	15	32	1-103322-6
	OBSOLETE	7	4	1.484	1.400	14	30	1-103322-5
	OBSOLETE	7	4	1.384	1.300	13	28	1-103322-4
	OBSOLETE	7	4	1.284	1.200	12	26	1-103322-3
	OBSOLETE	7	4	1.184	1.100	11	24	1-103322-2
	OBSOLETE	7	4	1.084	1.000	10	22	1-103322-1
△	SUPERSEDED BY 6-146250-0		4	.984	.900	9	20	1-103322-0
	OBSOLETE	7	4	.884	.800	8	18	103322-9
	OBSOLETE	7	4	.784	.700	7	16	103322-8
			4	.684	.600	6	14	103322-7
			4	.584	.500	5	12	103322-6
			4	.484	.400	4	10	103322-5
			4	.384	.300	3	8	103322-4
			4	.284	.200	2	6	103322-3
			4	.184	.100	1	4	103322-2
△	SUPERSEDED BY 5-146250-1		4	.084	—	—	2	103322-1

		PLATING	C	B	A	NO OF POSN	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MARTINELLI	150CT92		 TE Connectivity		
DIMENSIONS:		OK JOHN KNITTLE		23NOV92	ASSEMBLY, HEADER, BREAKAWAY, MOD II, DOUBLE ROW, .100 X .100 C/L, VERTICAL WITH .025 SQUARE POSTS		
INCHES		APVD B. FLINCHBAUGH		23NOV92			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		—			
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — — ANGLES		APPLICATION SPEC		—			
		WEIGHT		—	SIZE CASE CODE DRAWING NO A1 00779 C-103322		RESTRICTED
MATERIAL POST: COPPER ALLOY		SEE TABLE		SCALE 4:1 SHEET 1 OF 1 REV			
		CUSTOMER DRAWING					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-103322-5](#)