



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J1	REVISED PER ECO-21-000268	13JAN2021	RK	JO



RECOMMENDED HOLE LAYOUT

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- POINT OF MEASUREMENT FOR PLATING THICKNESS
- SINGLE TUBING PACKAGING
- BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- FINISH: POSTS- .000015 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL
- FINISH: POSTS- .000015 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL
- HIGH TEMPERATURE CONFIGURATION

6	7	4	.384	.300	3	4	9-103325-1
6	7		3.984	3.900	39	40	9-103325-0
6	7		3.884	3.800	38	39	8-103325-9
6	7		3.784	3.700	37	38	8-103325-8
6	7		3.684	3.600	36	37	8-103325-7
6	7		3.584	3.500	35	36	8-103325-6
6	7		3.484	3.400	34	35	8-103325-5
6	7		3.384	3.300	33	34	8-103325-4
6	7		3.284	3.200	32	33	8-103325-3
6	7		3.184	3.100	31	32	8-103325-2
6	7		3.084	3.000	30	31	8-103325-1
6	7		2.984	2.900	29	30	8-103325-0
6	7		2.884	2.800	28	29	7-103325-9
6	7		2.784	2.700	27	28	7-103325-8
6	7		2.684	2.600	26	27	7-103325-7
6	7		2.584	2.500	25	26	7-103325-6
6	7		2.484	2.400	24	25	7-103325-5
6	7		2.384	2.300	23	24	7-103325-4
6	7		2.284	2.200	22	23	7-103325-3
6	7		2.184	2.100	21	22	7-103325-2
6	7		2.084	2.000	20	21	7-103325-1
6	7		1.984	1.900	19	20	7-103325-0
6	7		1.884	1.800	18	19	6-103325-9
6	7		1.784	1.700	17	18	6-103325-8
6	7		1.684	1.600	16	17	6-103325-7
6	7		1.584	1.500	15	16	6-103325-6
6	7		1.484	1.400	14	15	6-103325-5
6	7		1.384	1.300	13	14	6-103325-4
6	7		1.284	1.200	12	13	6-103325-3
6	7		1.184	1.100	11	12	6-103325-2
6	7		1.084	1.000	10	11	6-103325-1
6	7		.984	.900	9	10	6-103325-0
6	7		.884	.800	8	9	5-103325-9
6	7		.784	.700	7	8	5-103325-8
6	7		.684	.600	6	7	5-103325-7
6	7		.584	.500	5	6	5-103325-6
6	7		.484	.400	4	5	5-103325-5
6	7		.384	.300	3	4	5-103325-4
6	7		.284	.200	2	3	5-103325-3
6	7		.184	.100	1	2	5-103325-2
6	7		.084	—	—	1	5-103325-1

REMARKS	PLATING	EXCEPT	C	B	A	NO OF POSN	PART NUMBER
---------	---------	--------	---	---	---	------------	-------------

6	4	.384	.300	3	4	4-103325-1
6		3.984	3.900	39	40	4-103325-0
6		3.884	3.800	38	39	3-103325-9
6		3.784	3.700	37	38	3-103325-8
6		3.684	3.600	36	37	3-103325-7
6		3.584	3.500	35	36	3-103325-6
6		3.484	3.400	34	35	3-103325-5
6		3.384	3.300	33	34	3-103325-4
6		3.284	3.200	32	33	3-103325-3
6		3.184	3.100	31	32	3-103325-2
6		3.084	3.000	30	31	3-103325-1
6		2.984	2.900	29	30	3-103325-0
6		2.884	2.800	28	29	2-103325-9
6		2.784	2.700	27	28	2-103325-8
6		2.684	2.600	26	27	2-103325-7
6		2.584	2.500	25	26	2-103325-6
6		2.484	2.400	24	25	2-103325-5
6		2.384	2.300	23	24	2-103325-4
6		2.284	2.200	22	23	2-103325-3
6		2.184	2.100	21	22	2-103325-2
6		2.084	2.000	20	21	2-103325-1
6		1.984	1.900	19	20	2-103325-0
6		1.884	1.800	18	19	1-103325-9
6		1.784	1.700	17	18	1-103325-8
6		1.684	1.600	16	17	1-103325-7
SUPERSEDED	6	1.584	1.500	15	16	1-103325-6
SUPERSEDED	6	1.484	1.400	14	15	1-103325-5
	6	1.384	1.300	13	14	1-103325-4
	6	1.284	1.200	12	13	1-103325-3
	6	1.184	1.100	11	12	1-103325-2
	6	1.084	1.000	10	11	1-103325-1
	6	.984	.900	9	10	1-103325-0
	6	.884	.800	8	9	103325-9
	6	.784	.700	7	8	103325-8
	6	.684	.600	6	7	103325-7
	6	.584	.500	5	6	103325-6
SUPERSEDED	6	.484	.400	4	5	103325-5
	6	.384	.300	3	4	103325-4
	6	.284	.200	2	3	103325-3
	6	.184	.100	1	2	103325-2
	6	.084	—	—	1	103325-1

PLATING	EXCEPT	C	B	A	NO OF POSN	PART NUMBER
---------	--------	---	---	---	------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL: HOUSING: PLATE REWORK: THERMOPLASTIC: COLOR: BLACK POSTS: COPPER ALLOY

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± .005 1. PLC ± .005 2. PLC ± .005 3. PLC ± .005 4. PLC ± .005 ANGLES ± .005

SEE TABLE

DWN: H. MOLL 22OCT87

CHK: THOMAS C. CLARK 23OCT87

APVD: THOMAS C. CLARK 23OCT87

NAME: HDR ASSY, MOD II, BREAKAWAY, SR, .100, RIGHT ANGLE, WITH .025 SQ POSTS

SIZE: A1

CAGE CODE: 00779

DRAWING NO: 103325

RESTRICTED TO: —

CUSTOMER DRAWING

SCALE: 4:1

SHEET: 1 OF 1

REV: J1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103325-6](#)