


- ① .000100 BRIGHT TIN—LEAD OVER .000050 NICKEL.
- ② POINT OF MEASUREMENT FOR PLATING THICKNESS.
- ③ THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- ④ ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- ⑤ .000100 BRIGHT TIN OVER .000050 NICKEL.
- ⑥ PRELIMINARY PART—NOT RELEASED FOR PRODUCTION.
- ⑦ .000100 MATTE TIN OVER .000050 NICKEL.
- ⑧ HIGH TEMPERATURE CONFIGURATION
- ⑨ STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
- ⑩ SUPERSEDED BY P/N 5-103639-2.
- ⑪ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- ⑫ 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF



RECOMMENDED HOLE LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.SHUEY	05MAR91		TE Connectivity																				
		CHK L.CASTAGNA	27MAR93																						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L.CASTAGNA	27MAR93		NAME																		
		0 PLC ± -		PRODUCT SPEC		HDR ASY,VERT,SNGL ROW 2.54[100] C/L 0.64[025] SQ PST, WTH PLZN<CHNG,AMPMODU MTE																			
		1 PLC ± -		108-25034																					
		2 PLC ± 0.13[.005]		APPLICATION SPEC																					
		3 PLC ± -		114-25026																					
4 PLC ± -		4 ANGLES ± -		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO															
MATERIAL		FINISH		WEIGHT		A2		-		C=103639		-													
HOUSING:		SEE TABLE																							
CUSTOMER DRAWING														SCALE		4:1		SHEET		1 OF 2		REV		AA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-103639-1](#)