

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


103639 , 103639

© COPYRIGHT 103639MM

ALL RIGHTS RESERVED.



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	Z	REVISED PER ECO-17-015890	31OCT2017	RS	MM
	AA	REVISED PER ECO-20-001323	17JUN2020	SM	JO




0.64±0.02
[.025±.001]

0.38 [.015] M
TYP AT POST TIPS



SECTION A-A



0.89±0.08
[0.035±.003] TYP

0.08 [.003] S

RECOMMENDED HOLE LAYOUT

- 1 .000100 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS. ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5 .000100 BRIGHT TIN OVER .000050 NICKEL.
- 6 PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 7 .000100 MATTE TIN OVER .000050 NICKEL.
- 8 HIGH TEMPERATURE CONFIGURATION
- 9 STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
- 10 SUPERSEDED BY P/N 5-103639-2.
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 12 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.SHUEY 05MAR91	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK L.CASTAGNA 27MAR93				
		APVD L.CASTAGNA 27MAR93	NAME			
		PRODUCT SPEC	HDR ASY,VERT,SNGL ROW			
		108-25034	2.54[.100] C/L 0.64[.025] SQ PST,			
		APPLICATION SPEC	WITH PLZN<CHNG,AMPMODU MTE			
MATERIAL		114-25026	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
HOUSING:		SEE TABLE	A2	-	103639	-
CUSTOMER DRAWING			SCALE	SHEET	REV	
			4:1	1 of 2	AA	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

11	OBSOLETE	8	1	64.01 [2.520]	65.91 [2.595]	24	25	2-103639-4	
	OBSOLETE	8	1	61.47 [2.420]	63.37 [2.495]	23	24	2-103639-3	
	OBSOLETE	8	1	58.93 [2.320]	60.83 [2.395]	22	23	2-103639-2	
	SUPERSEDED BY 7-103639-1		8	1	56.39 [2.220]	58.29 [2.295]	21	22	2-103639-1
11	OBSOLETE	8	1	53.85 [2.120]	55.75 [2.195]	20	21	2-103639-0	
		8	1	51.31 [2.020]	53.21 [2.095]	19	20	1-103639-9	
		8	1	48.77 [1.920]	50.67 [1.995]	18	19	1-103639-8	
		8	1	46.23 [1.820]	48.13 [1.895]	17	18	1-103639-7	
		8	1	43.69 [1.720]	45.59 [1.795]	16	17	1-103639-6	
		8	1	41.15 [1.620]	43.05 [1.695]	15	16	1-103639-5	
		8	1	38.61 [1.520]	40.51 [1.595]	14	15	1-103639-4	
		8	1	36.07 [1.420]	37.97 [1.495]	13	14	1-103639-3	
		8	1	33.53 [1.320]	35.43 [1.395]	12	13	1-103639-2	
		8	1	30.99 [1.220]	32.89 [1.295]	11	12	1-103639-1	
11	SUPERSEDED BY 6-103639-0		8	1	28.45 [1.120]	30.35 [1.195]	10	11	1-103639-0
		8	1	25.91 [1.020]	27.81 [1.095]	9	10	103639-9	
		8	1	23.37 [.920]	25.27 [0.995]	8	9	103639-8	
		8	1	20.83 [.820]	22.73 [.895]	7	8	103639-7	
		8	1	18.29 [.720]	20.19 [.795]	6	7	103639-6	
		8	1	15.75 [.620]	17.65 [.695]	5	6	103639-5	
		8	1	13.21 [.520]	15.11 [.595]	4	5	103639-4	
		8	1	10.67 [.420]	12.57 [.495]	3	4	103639-3	
		8	1	8.13 [.320]	10.03 [.395]	2	3	103639-2	
		8	1	5.59 [.220]	7.49 [.295]	1	2	103639-1	
		REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.SHUEY CHK L.CASTAGNA APVD L.CASTAGNA		05MAR93 27MAR93 27MAR93		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		HDR ASY,VERT,SNGL ROW 2.54[.100]C/L 0.64[.025]SQ PST, WTH PLZN<CHNG,AMPMODU MTE	
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-25034 APPLICATION SPEC 114-25026		SIZE A2	
MATERIAL		FINISH		CAGE CODE		DRAWING NO	
HOUSING:		SEE TABLE		WEIGHT		RESTRICTED TO	
				-		-	
CUSTOMER DRAWING				SCALE		SHEET	
				1:1		2 of 2	
				REV		AA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103639-4](#)