


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION






























ALL RIGHTS RESERVED.

© COPYRIGHT - By -

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	00		T2	REVISED PER ECO-11-005027	12MAR11	RK



- 1 CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- 2 USE WITH #22-#26 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- 3 THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- 4 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5 FOR STRIP ASSEMBLIES SEE PART NUMBER 103956
- 6 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 7 CONTACTS: .000100-.000200 BRIGHT TIN-LEAD OVER .000050 NICKEL
- 8 .000100-.000200 MATTE TIN OVER .000050 NICKEL
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE			2-104257-4	25	7-103645-4
			2-104257-3	24	7-103645-3
			2-104257-2	23	7-103645-2
			2-104257-1	22	7-103645-1
			2-104257-0	21	7-103645-0
OBSOLETE			1-104257-9	20	6-103645-9
			1-104257-8	19	6-103645-8
			1-104257-7	18	6-103645-7
OBSOLETE			1-104257-6	17	6-103645-6
			1-104257-5	16	6-103645-5
			1-104257-4	15	6-103645-4
OBSOLETE			1-104257-3	14	6-103645-3
			1-104257-2	13	6-103645-2
			2-104257-4	25	2-103645-4
			2-104257-3	24	2-103645-3
			2-104257-2	23	2-103645-2
			2-104257-1	22	2-103645-1
OBSOLETE			2-104257-0	21	2-103645-0
			1-104257-9	20	1-103645-9
			1-104257-8	19	1-103645-8
OBSOLETE			1-104257-7	18	1-103645-7
			1-104257-6	17	1-103645-6
			1-104257-5	16	1-103645-5
OBSOLETE			1-104257-4	15	1-103645-4
			1-104257-3	14	1-103645-3
			1-104257-2	13	1-103645-2
Y 1-103956-1			1-104257-1	12	1-103645-1
Y 1-103956-0			1-104257-0	11	1-103645-0
Y 103956-9			104257-9	10	103645-9
Y 103956-8			104257-8	9	103645-8
Y 103956-7			104257-7	8	103645-7
Y 103956-6			104257-6	7	103645-6
Y 103956-5			104257-5	6	103645-5
Y 103956-4			104257-4	5	103645-4
Y 103956-3			104257-3	4	103645-3
Y 103956-2			104257-2	3	103645-2
Y 103956-1			104257-1	2	103645-1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103645-3](#)