


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		P	EC 0G3C 0766 04	27DEC04	BSV	JLG
			P1	REVISED PER ECO-09-020932	26AUG09	KK	AEG



CONTACT IDENTIFICATION
LETTER "D" (LOCATED
IN THIS AREA)

HOUSING
(SEE TABLE
FOR PART NO.)

POSITION #1 INDICATOR

OBSOLETE	8	2-103653-4	25	7-103660-4
	8	2-103653-3	24	7-103660-3
	8	2-103653-2	23	7-103660-2
	8	2-103653-1	22	7-103660-1
	8	2-103653-0	21	7-103660-0
OBSOLETE	8	1-103653-9	20	6-103660-9
	8	1-103653-8	19	6-103660-8
	8	1-103653-7	18	6-103660-7
OBSOLETE	8	1-103653-6	17	6-103660-6
	8	1-103653-5	16	6-103660-5
OBSOLETE	8	1-103653-4	15	6-103660-4
	8	1-103653-3	14	6-103660-3
OBSOLETE	8	1-103653-2	13	6-103660-2
	7	2-103653-4	25	2-103660-4
OBSOLETE	7	2-103653-3	24	2-103660-3
	7	2-103653-2	23	2-103660-2
	7	2-103653-1	22	2-103660-1
OBSOLETE	7	2-103653-0	21	2-103660-0
	7	1-103653-9	20	1-103660-9
OBSOLETE	7	1-103653-8	19	1-103660-8
	7	1-103653-7	18	1-103660-7
SUPERSEDED	7	1-103653-6	17	1-103660-6
	7	1-103653-5	16	1-103660-5
SUPERSEDED	7	1-103653-4	15	1-103660-4
	7	1-103653-3	14	1-103660-3
SUPERSEDED	7	1-103653-2	13	1-103660-2
	7	1-103653-1	12	1-103660-1
SUPERSEDED BY 1-103945-1		1-103653-0	11	1-103660-0
SUPERSEDED BY 1-103945-0		103653-9	10	103660-9
SUPERSEDED BY 103945-9		103653-8	9	103660-8
SUPERSEDED BY 103945-8		103653-7	8	103660-7
SUPERSEDED BY 103945-7		103653-6	7	103660-6
SUPERSEDED BY 103945-6		103653-5	6	103660-5
SUPERSEDED BY 103945-5		103653-4	5	103660-4
SUPERSEDED BY 103945-4		103653-3	4	103660-3
SUPERSEDED BY 103945-3		103653-2	3	103660-2
SUPERSEDED BY 103945-2		103653-1	2	103660-1
SUPERSEDED BY 103945-1				

- CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- USE WITH #22-#26 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- POINT OF MEASUREMENT FOR PLATING THICKNESS
- FOR STRIP ASSEMBLIES SEE PART NUMBER 103945
- MATERIAL- HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR: BLACK PINS: PHOS. BRONZE
- FINISH- PINS: .000015 GOLD IN THE CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON THE TERMINATION AREA, OVER .000050 NICKEL.
- FINISH- PINS: .000015 GOLD IN THE CONTACT AREA, .000050-.000100 MATTE TIN ON THE TERMINATION AREA, OVER .000050 NICKEL.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH SEE TABLE

DWN R.BROWN 26JUL00
CHK K.WRIGHT 26JUL00
APVD K.WRIGHT 26JUL00

PRODUCT SPEC
108-25034
APPLICATION SPEC
114-25026
WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME
SHROUDED PIN ASSY, AMPMODU MTE, SINGLE ROW,
.100 CL, POLARIZED, WITH LATCH WINDOWS,
FOR #22-#26 AWG WIRE SIZE

SIZE A2
CAGE CODE 00779
DRAWING NO C=103660
RESTRICTED TO -

SCALE 4:1
SHEET 1 OF 1
REV P1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103660-3](#)