



1. .000100 BRIGHT TIN—LEAD OVER .000050 NICKEL.
2. POINT OF MEASUREMENT FOR PLATING THICKNESS.
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
4. ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
5. SELECT POST TAILS FORMED TO PROVIDE CONNECTOR HOLD DOWN UNTIL SOLDERED. CONFIGURATION ACCEPTS 0.69[.027]—2.03[.080] THICK PRINTED CIRCUIT BOARD. (SEE DETAIL Z).
6. .000100 BRIGHT TIN OVER .000050 NICKEL.
7. PRELIMINARY PART — NOT RELEASED FOR PRODUCTION.
8. .000100 MATTE TIN OVER .000050 NICKEL.
9. HIGH TEMPERATURE CONFIGURATION.
10. STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
11. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINIS
12. 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

<div>11</div>		<div>9</div>	<div>6</div>	23.37 [.920]	25.27 [.995]	8	9	3–103669–0
		<div>9</div>	<div>6</div>	8.13 [.320]	10.03 [.395]	2	3	2–103669–9
		<div>9</div>	<div>6</div>	15.75 [.620]	17.65 [.695]	5	6	2–103669–8
		<div>9</div>	<div>6</div>	13.21 [.520]	15.11 [.595]	4	5	2–103669–7
		<div>9</div>	<div>6</div>	10.67 [.420]	12.57 [.495]	3	4	2–103669–6
		<div>9</div>	<div>6</div>	5.59 [.220]	7.49 [.295]	1	2	2–103669–5
<div>11</div>	OBSOLETE	<div>9</div>	<div>1</div>	64.01 [2.520]	65.91 [2.595]	24	25	2–103669–4
<div>11</div>	OBSOLETE	<div>9</div>	<div>1</div>	61.47 [2.420]	63.37 [2.495]	23	24	2–103669–3
<div>11</div>	OBSOLETE	<div>9</div>	<div>1</div>	58.93 [2.320]	60.83 [2.395]	22	23	2–103669–2
<div>11</div>	OBSOLETE	<div>9</div>	<div>1</div>	56.39 [2.220]	58.29 [2.295]	21	22	2–103669–1
<div>11</div>	OBSOLETE	<div>9</div>	<div>1</div>	53.85 [2.120]	55.75 [2.195]	20	21	2–103669–0
<div>11</div>		<div>9</div>	<div>1</div>	51.31 [2.020]	53.21 [2.095]	19	20	1–103669–9
	OBSOLETE	<div>9</div>	<div>1</div>	48.77 [1.920]	50.67 [1.995]	18	19	1–103669–8
<div>11</div>	OBSOLETE	<div>9</div>	<div>1</div>	46.23 [1.820]	48.13 [1.895]	17	18	1–103669–7
<div>11</div>		<div>9</div>	<div>1</div>	43.69 [1.720]	45.59 [1.795]	16	17	1–103669–6
		<div>9</div>	<div>1</div>	41.15 [1.620]	43.05 [1.695]	15	16	1–103669–5
<div>11</div>	OBSOLETE	<div>9</div>	<div>1</div>	38.61 [1.520]	40.51 [1.595]	14	15	1–103669–4
<div>11</div>		<div>9</div>	<div>1</div>	36.07 [1.420]	37.97 [1.495]	13	14	1–103669–3
		<div>9</div>	<div>1</div>	33.53 [1.320]	35.43 [1.395]	12	13	1–103669–2
		<div>9</div>	<div>1</div>	30.99 [1.220]	32.89 [1.295]	11	12	1–103669–1
		<div>9</div>	<div>1</div>	28.45 [1.120]	30.35 [1.195]	10	11	1–103669–0
		<div>9</div>	<div>1</div>	25.91 [1.020]	27.81 [1.095]	9	10	103669–9
		<div>9</div>	<div>1</div>	23.37 [.920]	25.27 [.995]	8	9	103669–8
		<div>9</div>	<div>1</div>	20.83 [.820]	22.73 [.895]	7	8	103669–7
		<div>9</div>	<div>1</div>	18.29 [.720]	20.19 [.795]	6	7	103669–6
		<div>9</div>	<div>1</div>	15.75 [.620]	17.65 [.695]	5	6	103669–5
		<div>9</div>	<div>1</div>	13.21 [.520]	15.11 [.595]	4	5	103669–4
		<div>9</div>	<div>1</div>	10.67 [.420]	12.57 [.495]	3	4	103669–3
		<div>9</div>	<div>1</div>	8.13 [.320]	10.03 [.395]	2	3	103669–2
		<div>9</div>	<div>1</div>	5.59 [.220]	7.49 [.295]	1	2	103669–1

REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.
---------	---------	---	---	---	-------------------	----------

[illegible]

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

OBSOLETE

11

<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	64.01 [2.520]	65.91 [2.595]	24	25	7-103669-4
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	61.47 [2.420]	63.37 [2.495]	23	24	7-103669-3
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	58.93 [2.320]	60.83 [2.395]	22	23	7-103669-2
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	56.39 [2.220]	58.29 [2.295]	21	22	7-103669-1
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	53.85 [2.120]	55.75 [2.195]	20	21	7-103669-0
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	51.31 [2.020]	53.21 [2.095]	19	20	6-103669-9
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	48.77 [1.920]	50.67 [1.995]	18	19	6-103669-8
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	46.23 [1.820]	48.13 [1.895]	17	18	6-103669-7
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	43.69 [1.720]	45.59 [1.795]	16	17	6-103669-6
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	41.15 [1.620]	43.05 [1.695]	15	16	6-103669-5
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	38.61 [1.520]	40.51 [1.595]	14	15	6-103669-4
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	36.07 [1.420]	37.97 [1.495]	13	14	6-103669-3
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	33.53 [1.320]	35.43 [1.395]	12	13	6-103669-2
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	30.99 [1.220]	32.89 [1.295]	11	12	6-103669-1
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	28.45 [1.120]	30.35 [1.195]	10	11	6-103669-0
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	25.91 [1.020]	27.81 [1.095]	9	10	5-103669-9
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	23.37 [.920]	25.27 [.995]	8	9	5-103669-8
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	20.83 [.820]	22.73 [.895]	7	8	5-103669-7
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	18.29 [.720]	20.19 [.795]	6	7	5-103669-6
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	15.75 [.620]	17.65 [.695]	5	6	5-103669-5
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	13.21 [.520]	15.11 [.595]	4	5	5-103669-4
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	10.67 [.420]	12.57 [.495]	3	4	5-103669-3
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	8.13 [.320]	10.03 [.395]	2	3	5-103669-2
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	5.59 [.220]	7.49 [.295]	1	2	5-103669-1
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. SHUEY

3-5-91

CHK
M. RIDER

2-14-92

APVD
M. RIDER

2-14-92

NAME

DIMENSIONS:
INCHES

0 PLC

±

—

1 PLC

±

—

2 PLC

±

0.13[.005]

3 PLC

±

—

4 PLC

±

—

ANGLES

±

—

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

PRODUCT SPEC

APPLICATION SPEC

MATERIAL
HOUSING: LCP,
CONTACTS: BRASS

FINISH
SEE TABLE

WEIGHT

—

CUSTOMER DRAWING

STE

TE Connectivity

HDR ASSY, VERT, SINGLE ROW

2.54 [.100] C/L 0.64 [.025] SQ POST

WITH PLZN, AMPMODU MTE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A1

00779

C=103669

—

SCALE

4:1

SHEET

2

OF

2

REV

AC

4805 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-103669-2](#)