



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AF	REVISED PER ECO-16-006307	03AUG2016	NK	MM



1	POINT OF MEASUREMENT FOR PLATING THICKNESS.
2	ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
3	TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
4	.000381[.000015] GOLD ON THE CONTACT AREA, .00254[.000100]—.00508[.000200] MATTE TIN LEAD ON THE SOLDER TAIL, ALL OVER .00127[.000050] NICKEL.
5	PRELIMINARY PART—NOT RELEASED FOR PRODUCTION.
6	.000381[.000015] GOLD ON THE CONTACT AREA, .00254[.000100]—.00508[.000200] MATTE TIN ON THE SOLDER TAIL, ALL OVER .00127[.000050] NICKEL.
7	HIGH TEMPERATURE CONFIGURATION.
8	OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KATE HELM 21-12-89 CHK RANDY FEIXD 21-12-89 APVD RON FELIX 21-12-89		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .127 [0.005] 4 PLC ± - ANGLES ± -		NAME HDR ASSY,MOD II, BREAKAWAY, DBL ROW .100X.100 C/L VL, .025 SQ.POST, WITH SELECTIVE LOADING	
		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A2	CAGE CODE 00779
MATERIAL HOUSING:FLAME RETARDANT THERMOPLASTIC COLOR: BLACK POST: COPPER ALLOY		FINISH SEE TABLE		DRAWING NO C-103675	
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 2
				REV AF	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

OBSOLETE

7

8

6

3

NONE

12.29
[.484]

4

9

10

7-103675-0

7

8

6

NONE

7

25.40
[.884]

8

17

18

6-103675-6

7

8

6

14

14

42.77
[1.684]

16

32

34

6-103675-5

7

8

6

NONE

12

32.61
[1.284]

12

25

26

6-103675-4

7

8

6

1

NONE

19.91
[.784]

7

15

16

6-103675-3

7

8

6

13,14

14

50.39
[1.984]

19

37

40

6-103675-2

7

8

6

3

NONE

9.75
[.384]

3

7

8

6-103675-1

7

8

6

NONE

2

24.99
[.984]

9

19

20

6-103675-0

7

8

6

14

NONE

37.69
[1.484]

14

29

30

5-103675-9

7

8

6

2

NONE

42.77
[1.684]

16

33

34

5-103675-8

7

8

6

NONE

10

50.39
[1.984]

19

39

40

5-103675-7

7

8

6

NONE

13

32.61
[1.284]

12

25

26

5-103675-6

7

8

6

NONE

5

12.29
[.484]

4

9

10

5-103675-5

7

8

6

NONE

15

42.77
[1.684]

16

33

34

5-103675-3

7

8

6

11

NONE

50.39
[1.984]

19

39

40

5-103675-2

7

8

6

13

NONE

32.61
[1.284]

12

25

26

5-103675-1

REMARKS

PLATING

ROW N
POST NUMBER OMITTED

ROW M

B

A

NO OF ACTIVE POSN

NO OF POSN

ASSEMBLY PART NUMBER

OBSOLETE

4

2

2

12.29
[.484]

4

8

10

1-103675-9

4

9

NONE

25.40
[.884]

8

17

18

1-103675-8

4

4

NONE

19.91
[.784]

7

15

16

1-103675-7

4

NONE

7

25.40
[.884]

8

17

18

1-103675-6

4

14

14

42.77
[1.684]

16

32

34

1-103675-5

4

NONE

12

32.61
[1.284]

12

25

26

1-103675-4

4

1

NONE

19.91
[.784]

7

15

16

1-103675-3

4

13,14

14

50.39
[1.984]

19

37

40

1-103675-2

4

3

NONE

9.75
[.384]

3

7

8

1-103675-1

4

NONE

2

24.99
[.984]

9

19

20

1-103675-0

4

14

NONE

37.69
[1.484]

14

29

30

103675-9

4

2

NONE

42.77
[1.684]

16

33

34

103675-8

4

NONE

10

50.39
[1.984]

19

39

40

103675-7

4

NONE

13

32.61
[1.284]

12

25

26

103675-6

4

NONE

5

12.29
[.484]

4

9

10

103675-5

4

10

NONE

50.39
[1.984]

19

39

40

103675-4

4

NONE

15

42.77
[1.684]

16

33

34

103675-3

4

11

NONE

50.39
[1.984]

19

39

40

103675-2

4

13

NONE

32.61
[1.284]

12

25

26

103675-1

REMARKS

PLATING

ROW N
POST NUMBER OMITTED

ROW M

B

A

NO OF ACTIVE POSN

NO OF POSN

ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .127 [.005]

4 PLC ± -

ANGLES ± -

FINISH

MATERIAL

-

SEE TABLE

DWN KATE HELM 21-12-89

CHK RANDY FEIDT 21-12-89

APVD RON FELIX 21-12-89

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

HDR ASSY,MOD II,BREAKAWAY,DBL ROW
.100 X .100CL VERTICAL, .025 SQ. POST,
WITH SELECTIVE LOADING

A200779

C=103675

SCALE 4:1

SHEET 2 OF 2

REV AF

1471-9 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-103675-5](#)