

Passive Components



Passive Components



Introduction

Tyco Electronics is one of the major business units of Tyco International Ltd. (NYSE:TYC, LSE:TYI, BSX:TYC). Headquartered in Harrisburg, Pennsylvania, USA, Tyco Electronics is the world's largest passive electronic components manufacturer, and a world leader in cutting-edge wireless technologies, fibre optic active components, and complete power systems. The company has facilities located in 51 countries serving customers in the aerospace, automotive, computer, communications, consumer electronics, industrial and power industries.

Tyco Electronics provides advanced technology products from over thirty well-known and respected product brands, including Agastat, Alcoswitch, AMP, AMP NETCONNECT, Buchanan, CII, CoEv, Critchley, Elcon, Elo Touch Systems, HTS, M/A-COM, Madison Cable, OEG, Potter & Brumfield, Raychem, Schrack, Simel and TDI Batteries.

Tyco Electronics' product portfolio now includes a comprehensive range of passive components, including surface mount and leaded resistors, trimmers, potentiometers, PTC and NTC surface mount thermistors, as well as a wide range of inductive products covering wirewound, metal film surface mount, ceramic and ferrite bead.

A range of SMD Capacitors, including Multi Layer Ceramic (MLCC), Tantalum and Aluminium Electrolytic completes the Passive Components product portfolio.

The Holsworthy range of precision resistors meets the requirement for economically priced components for both industrial and military applications. In SMD and leaded packages, with tolerances down to 0.05% and TCRs as low as 5ppm, the Holsworthy



range from Tyco Electronics delivers the "Complete Precision Portfolio".

For all trimming solutions, the Citec brand is the ideal design partner where your circuit requires sealed or unsealed trimmers from just 2mm square. Multiturns for precision trimming are available with 11 or 12 turn setability. Further, Citec offers a prestigious range of potentiometers, from single and multiturn versions with cermet or carbon elements, through to switched options with shafts in either plastic or metal.

Sigma noise suppression and protection inductor chips from Tyco Electronics can help protect circuits in a variety of ways. The range offers solutions for high power, high speed, low frequency noise impedance as well as temperature responsive resistors in PTC and NTC. Sigma also encompasses a wide range of wound, multilayered and printed inductors in addition to noise reduction bead inductors and through-hole RF chokes.

CGS high power and high voltage resistors are rated up to 100W with voltage proof to 50kV and are available in a wide variety of package styles. High power and pulse resistors in the CGS range are capable of dissipating up to 25,000 Watts for applications such as regenerative braking and power supplies.

The Neohm range of commodity resistors are available with SMD and Leaded devices. This wide range of products compliments and supports the Passives range available from the Tyco Electronics portfolio.

Contents

Resistive Products	Page	Inductive Products (cont)	Page
Fixed - Surface Mount	3	Ferrite Beads	10
Fixed - Leaded	4-5	Power - Surface Mount - Unshielded	11
Trimmers - Surface Mount	6	Leaded - Unshielded	11
Trimmers - Leaded	7	Power - Surface Mount - Shielded	12
Potentiometers - Leaded	8		
Encoders - Leaded	9	Capacitive Products	
Thermistors and Varistors	9	Ceramic - Surface Mount	13
Inductive Products		Tantalum - Surface Mount	13
Moulded	10	Aluminium Electrolytic - Surface Mount	13
High Frequency	10	Colour Codes and E-Series Grid	14
3 11 17		Associated Products	15

2

Catalogue No. 1309350 August 2007

Dimensions are shown in mm for reference purposes only.

Specifications subject to change.

tycoelectronics.com passives.tycoelectronics.com



Resistive Products, Fixed - Surface Mount

Product Type	Commodity CRG / 3520	High Ohmic RH73	Fusible FCR	Trimmable TCR	Commodity MCN
	222				
Features	0201 to 2512 Package Sizes	0402 to 2512 Package Sizes	0805 and 1206 Package Sizes	0805 and 2512 Package Sizes	2, 4, or 8 x 0603 Resistors
	1R0 to 10M Value Range	10M to 100G Value Range	1R0 to 5IR Value Range	1R0 to 10M Value Range	10R to 1M Value Range
	Tolerances down to 1% and 5%	Tolerances down to 2%	5% Tolerance	Trimming Ratios up to 3 Times	±1%, ±2% ±5% Tolerances
	TCR ±200ppm/°C max.	TCR's down to 100ppm/°C	2.0W or 2.5W Fusing Power	TCR's down to 100ppm/°C	TCR ±200ppm/°C max.
	500 Volt Maximum Overload	Special Values Possible	30 Seconds Fusing Time	Up to 1W Dissipation	Concave or Convex Terminals
					UmQF

					MAF	
Product Type	Ultra Precision RN73	Precision CPF	Precision Thick Film CPG	Precision MRS	Precision SU	
					4 4 1 1 1	
Features	0402 to 1210 Package Sizes	0402 to 1206 Package Sizes	0603 to 1206 Package Sizes	4 x 0603 Resistors	0.125W to 0.50W	
	5R0 to 1M Value Range	5R1 to 1M Value Range	10R to 4M7 Value Range	10R to 330K Value Range	1R0 - 2M0 Value Range	
	0.01% Tolerance	Tolerances down to 0.1%	Tolerances down to 0.5%	Tolerances down to 0.1%	Tolerances down to 0.005%	
	TCR 10ppm/°C max.	TCR's down to 25ppm/°C	TCR's down to 50ppm/°C	TCR's down to 25ppm/°C	TCR's down to 10ppm/°C	
	0805-E96 Values in Distribution	E24 and E96 Value Grid	E24 and E96 Value Grid	1206 Real Estate	Available in E192 Value grid	

Product Type	Low Ohmic RL73	Low Ohmic TL / HL	Low Ohmic SL	Power Wirewound SP	Power SM
		20mQF	BILL BAR	ALL CARD	
Features	0402 to 2512 Package Sizes	0.25W to 2.0W Dissipation	0.5W& 3.0W Dissipation	0.75W to 3.5W @ 25°C Dissipation	1W to 5W Dissipation
	Values down to R10	R001 to 1R0 Value Range	R01 to R011 Value Range	R06 to 45K Value Range	R10 to 2M Value Range
	Tolerances down to 1%	1% Tolerance	1% - 5% Tolerance	Tolerances down to 0.1%	1% or 5% Tolerances
	TCR 100ppm/°C or 200ppm/°C	Down to TCR +50ppm/°C	Down to 4.7nH Inductance	TCR's down to 20ppm/°C	200ppm/°C Wire / 100ppm/°C Film
	2512 E12 Grid in Distribution	Non Inductive Foil Element	4 Package Sizes	Suited to Pulse Applications	True Pick and Place Body Style

Catalogue No. 1309350 August 2007

Dimensions are shown in mm for reference purposes only.

Specifications subject to change.

tycoelectronics.com passives.tycoelectronics.com



Resistive Products, Fixed - Leaded

Product Type	Metal Film Precision H4P / H4 / H8	Metal Film Semi Precision R	Standard Metal Film LR	Precision Wirewound UPW
		1 martine and the second secon		
Features	0.25W to 1.0W Dissipation	0.25W Dissipation	0.25W to 0.75W Dissipation	0.15W to 0.5W Dissipation
	1R0 to 10M Value Range	4R02 to 1M Value Range	R10 to 10M Value Range	R10 to 2M Value Range
	Tolerances down to 0.05%	0.1% to 1% Tolerance	1%, 2% or 5% Tolerance	Tolerances down to 0.005%
	TCR's down to 5ppm/°C	TCR's down to 15ppm/°C	TCR's down to 10ppm/°C	TCR's down to 1ppm/°C
	Released to BS/CECC	E96 Value Grid	Taped Ammo Pack to IEC286-1	Low Inductance

Product Type	Carbon Film CFR	Metal Oxide RSS / ROX	Fusible FRN / SQF / FKN	Metal Glaze RGP	High Voltage Thick Film HH / HJ
	e 8 B	and a second	5 m -	an a	
Features	0.25W to 2.0W Dissipation	0.5W to 7.0W Dissipation	1W to 10W Dissipation	0.25W to 4.0W Dissipation	0.5W to 6.0W Dissipation
	1R0 to 10M Value Range	1R0 to 200K Value Range	R10 to 150R Value Range	1M to 10G Value Range	100K to 50G Value Range
	2% or 5% Tolerance	±5% Tolerance	Axial or Radial Leaded	5% or 10% Tolerance	Tolerances down to 0.5%
	Small Body Sizes Available	Axial Leaded	5% Tolerance	±0.005%/V Voltage Coefficient	TCR's down to 25ppm/°C
	Taped Ammo Pack to IEC286-1	Ammo Packed or Reeled	TCR 300ppm/°C max.	TCR 350ppm/°C max.	Axial Leaded

Product Type	High Voltage Thick Film HB	High Voltage Thick Film HVR	High Power Thick Film BDS	High Power Thick Film MPC	Thin Film Power MPR
			the loss	THE REAL PROPERTY OF	
Features	Dissipation up to 2W @ 70°C	Up to 100 W Dissipation (in oil)	100W to 600W Dissipation	3W to 10W Dissipation	20W Dissipation (Heatsink)
	1K to 1G Value Range	2K to 1G Value Range	R20 to 1M Value Range	1R0 to 200K Value Range	R22 to 51K Value Range
	Tolerance down to 1%	Tolerances down to 1%	5% or 10% Tolerance	1% or 5% Tolerance	TO220 Package
	Up to 15kV Voltage Rating	Up to 50KV Voltage Rating	TCR 150ppm/°C max.	TCR ±100ppm/°C max.	1% (E24), 5% (E12) Tolerances
	Axial / Radial Options	Various Mounting Styles	Customised as Required	Radial Leads	TCR down to ±50ppm/°C

Catalogue No. 1309350 August 2007

4

Dimensions are shown in mm for reference purposes only.

Specifications subject to change.



Resistive Products, Fixed - Leaded

Product Type	Power Wirewound	Power Wirewound	Power Wirewound	Power Wirewound	Power Wirewound
	SBC / SBCHE	SQP / SQM / SQZ	C3A / C7 / C10 / C14	ER	ES
	the second secon	A last		1	
Features	3W to 40W Dissipation	2W to 25W Dissipation	3W to 14W Dissipation	3W to 14W Dissipation	0.5W to 10W Dissipation
	R10 to 22K Value Range	R10 to 150K Value Range	R10 to 100K Value Range	R01 to 100K Value Range	R10 to 3K3 Value Range
	10% or 5% Tolerance	5% Tolerance	10%, 5% or 2% Tolerance	Tolerances down to 0.5%	5% Tolerance
	Radial and Axial Styles	Radial and Axial Styles	Axial Leaded	Axial and Radial Types	Super Small Size available
	2000V Dielectric Strength	Wire or Power Oxide	3W and 7W Ammo Packed	Custom Designs as Required	Taped and Ammo Packed

Product Type	Power Wirewound HS / THS	Power Wirewound FC	Power Wirewound ME	Power Wirewound TG	Power Wirewound TT / TK
				2	
Features	5W to 300W Dissipation	2W to 8W Dissipation	Up to 500W Dissipation	Up to 293W Dissipation	10W to 1000W Dissipation
	R01 to 82K Value Range	R20 to 22K Value Range	R02 to 22K Value Range	R24 to 100K Value Range	R20 to 70K Value Range
	Tolerances down to 0.25%	5% or 10% Tolerance	5% or 10% Tolerance	5% or 10% Tolerance	5% or 10% Tolerance
	High Voltage Versions	Radial Leads	Fixed or Adjustable	Glass Bond Coated	Fixed or Adjustable
	Low Inductance Styles	Two Height Profiles	Range of Terminal Style	6000J Pulse Energy	Range of Mounting Styles

Product Type	Foil Low Ohmic SBL	Wire Shunt OS / OP	Zerohm Link ZR	Carbon Moulded CBT	Ceramic Composition CCR
					and a state of the
Features	4W and 5W Dissipation	Values from R003 to R150	Two Case Sizes	0.25W, 0.5W Dissipation	0.5, 1.0, 2.0W Power Dissipation
	R005 to R051 Value Range	2 Different Styles	< 2 milliohm Resistance	2R2 to 22M Value range	Up to 20kV Impulse Withstand
	1% or 5% Tolerance	Current Rating to 21A	Dielectric Strength - 500V	E24 - 5% E12 - 10% Tolerance	Tolerance 10%
	2KV Dielectric Strength	5% Tolerance as Standard	> 10G Insulation Resistance	Up to 750V Overload	Up to 400V Working Voltage
	Essentially Non Inductive	Custom Designs Available	Taped Ammo Pack to IEC286-1	Low Inductance	3R3 to 390K Value Range



Resistive Products, Trimmers - Surface Mount

Product Type	Open Frame 3121	Open Frame 3130	Open Frame 3135	Open Frame 3142	Open Frame 3150 / 3165
			00		
Features	Board Area - 2.2mm x 2.75mm		3mm Square Nominal	4mm Square Nominal	4mm Square Nominal
	Height 1.8mm	Height 1.85mm Max.	Height 1.2mm Max.	Height 2.4mm	Lightweight - 0.2 Grams
	200R to 1M Value Range	100R to 1M Value Range	100R to 1M Value Range	100R to 1M Value Range	100R to 1M Value Range
	25% Tolerance	Auto Adjust Version	Delta Terminals	Delta Terminals	In-line or Delta Terminals
	50V DC Operating Voltage	50V DC Operating Voltage	Integrated End Stop	50V DC Operating Voltage	Underside Adjust Version

Product Type	Semi Sealed 3103	Semi Sealed 3203	Semi Sealed 3204
	00	A C	
Features	Board Area - 3.6mm x 3.1mm	Board Area - 3.4mm x 3.4mm	Board Area - 4mm x 4.5mm
	Height < 1.8mm	Height < 2.1mm	Height 2.4mm
	500R to 1M Value Range	100R to 1M Value Range	100R to 1M Value Range
	0.05W Dissipation @ 50°C	0.05W Dissipation	0.1W Dissipation
	Sealed for Processing	Sealed for Processing	Sealed for Processing

Product Type	Sealed 3212	Sealed 3213	Sealed 3315	Multiturn 3240	Multiturn 3270
		10. 10	C IO		
Features	Board Area - 2.4mm x 2.8mm	Board Area - 3.4mm x 3.4mm	Board Area - 5mm x 5mm	4mm Square Nominal	6mm Square Nominal
	Height 1.7mm	Height 2.0mm	Height 2.5mm	Top and Side Adjust Styles	Top and Side Adjust Styles
	100R to 1M0 Value Range	10R to 1M0 Value Range	10R to 2M Value Range	10R to 2M Value Range	10R to 1M Value Range
	20% Tolerance	20% Tolerance	20% Tolerance	10% Tolerance	10% Tolerance
	O-ring Sealed	O-ring Sealed	O-ring Sealed	11 Turns	12 Turns

6

Catalogue No. 1309350 August 2007



Resistive Products, Trimmers - Leaded

Product Type	Economy CT6	Economy 416	Economy 409	Economy CB10	Economy CB15 / CT15
Features	6mm Single Turn 200R to 1M Value Range	6mm Single Turn 100R to 1M Value Range	10mm Single Turn 100R to 1M Value Range	Carbon Element 100R to 10M Value Range	Carbon Element 100R to 4M7 Value Range
	0.1W Dissipation	0.2W Dissipation	0.5W Dissipation	0.15W Log /0.25W Lin Dissipation	0.15W Log /0.25W Lin Dissipation
	Top and Side Adjust Versions	Top and Side Adjust Versions	100 Cycles Maximum	Long Life Version (>10,000 cycles)	Long Life (>10,000 cycles)
	Resin Moulded Technology	Dust and Splash Proof	Dust and Splash Proof	Enclosed Package	Plug in Shaft Available

Product Type	Professional 470	Professional 4265	Professional 4275	Professional 4295
			Ser and a second se	
Features	6mm Single Turn	6mm Single Turn Sealed	6mm Single Turn Sealed	10mm Single Turn Sealed
	10R to 1M Value Range	10R to 2M Value Range	10R to 2M Value Range	10R to 2M Value Range
	10% Tolerance	0.5W Dissipation	0.5W Dissipation	0.5W Dissipation
	0.5W Dissipation	20% Tolerance Standard	10% Tolerance Standard	TCR ±100ppm/°C
	Fully Sealed	Three Pin Layouts/Taped Versions	Three Pin Layouts/Taped Versions	Five Pin Layouts

Product Type	Multiturn 433	Multiturn 4270	Multiturn 4290
Features	19mm Multiturn Sealed	6mm Multiturn Sealed	10mm Multiturn Sealed
	10R to 2M Value Range	50R to 2M Value Range	50R to 2M Value Range
	0.75W Dissipation	0.25W Dissipation	0.5W Dissipation
	15 Electrical Turns	12 Electrical Turns	25 Electrical Turns
	Panel Mount Available	Wide Variety of Styles	Wide Variety of Styles





Resistive Products, Potentiometers - Leaded

Product Type	Economy PC610	Economy 31 / 23	Economy 51 / 54 / 56	Economy 17P	Economy CP16
		C. C			
Features	9mm Square Pluggable	20mm/16mm Round Body	16mm Package	16mm Square all Plastic Body	16mm Square Package
	Polymer Element	Printed Carbon Element	Polymer Element	Polymer Thick Film Element	Polymer Thick Film Element
	500R to 500K Value Range	1K to 1M Value Range (Linear)	470R to 2M2 Value Range	1K to 1M Value Range (Lin)	100R to 4M7 Value Range
	0.05W Dissipation	0.25W Log/0.4W Lin Dissipation	0.25W Dissipation	0.25W Dissipation	0.1W Log/0.2W Lin Dissipation
	Non Linear Laws Available	Non Linear Laws Available	Non Linear Laws Available	Non Linear Laws Available	Non Linear Laws Available
	10,000 Operations minimum	Dual Gang & Switched Styles	Switched Version	Multigangs, Switches Available	Switches Available

Product Type	Professional CS9	Professional TW	Professional 5930 / 5940	Professional LC	Professional MC
Features	9mm Square Body	265° Travel	10 Turn Multiturn	13mm Round Body	19mm Round Body
	Polymer Element	Wirewound Element	Wirewound Element	Cermet Element	Cermet Element
	5K to 250K Value Range	5R to 22K Value Range	200R to 100K Value Range	100R to 2M2 Value Range	100R to 2M2 Value Range
	0.05W Dissipation	1 Watt @ 40°C	2W Dissipation	1W Dissipation	2W Dissipation
	Linear or Logarithmic Laws	TCR - 100 ppm	<0.25% Linearity	O-ring Spindle Sealed	O-ring Spindle Sealed
	Multigangs, Switches Available	5000 Operations	Range of Dials Available	25,000 Operations minimum	25,000 Operations minimum

Product Type	Economy RW	Rheostats BFA
Features	40mm Enclosed Body Wirewound Element 10R to 100K Value Range 1W (RW1), 3W (RW3) Dissipation Linear Laws Only Excellent Linearity	Wirewound Variable Load Up to 811W Dissipation Current up to 10 Amps 5 Case Sizes Operates up to 400°C Protective Case





Passive Components

Encoders - Leaded

Product Type	Contact Encoder DP(S) 9	Contact Encoder DP(S) 12	Contact Encoder DP(S) 15
		e de la compañía de	
Features	9mm Square	12mm Square	12mm Square
	Switch / Detent Options	Switch / Detent Options	Switch / Detent Options
	Vertical / Horizontal Mounting	Vertical / Horizontal Mounting	Vertical / Horizontal Mounting
	Various Shaft Configurations	Various Shaft Configurations	Various Shaft Configurations
	12 / 24 Pulses	12 / 24 Pulses	12 / 24 Pulse



Encoders - Leaded, with Illuminated Shaft

Product Type	Contact Encoder with LED DPSL 12				
Features	Integrated Colour LED's (Yellow / Blue / Red / Orange / Green)				
	Switch / Detent Options				
	Vertical / Horizontal Mounting				
	Various Shaft Configurations				
	12 / 24 Pulses - 5V 0.5mA Rating				



Resistive Products, Thermistors and Varistors

Product Type	Temperature Sense 8158	Temperature Sense NTC	Temperature Sense LT73	PTC Thermistor LT
Features	0402 to 1206 Package Sizes	0603 and 0805 Case Size	0805 and 1206 Package Styles	Axial Leaded
	40R to 500K Value Range	100R to 150K Value Range	510R to 6K2 Value Range	0.16W or 0.25W
	Tolerances down to 5%	5% or 10% Tolerance	5% Tolerance	Wide Temperature Range
	ß Values - 2800 to 4350 (NTC)	ß Values -2700 to 4100	TCR 3900ppm/°C max (PTC)	Values from 10R to 10K
	ß Value Tolerances down to 1%	5% Tolerance on B Value	Operating Temp40°C to 150°C	Insulated Package Style

tycoelectronics.com passives.tycoelectronics.com



Inductive Products, Moulded

Product Type	Moulded 3610	Moulded 3611	Moulded 3612	Moulded 3613	Moulded 3615
		OUT OUT	AL AL	EST ST.	ta front
Features	0805, 1008, 1210, 1812 Packages	Board Area 13mm x 5mm			
	10µH to 1mH Value Range	0.1µH to 1mH Value Range			
	Temp.Range -25°C to 100°C	High Current (3.5A)			
	Moulded Package	Moulded Package	Moulded Package	Moulded Package	Moulded Package
	Dip and Wave Solderable	Dip and Wave Solderable			

Inductive Products, High Frequency

Product Type	High Frequency 3640	High Frequency 3650	High Frequency 3651 / 52 / 53	High Frequency 3670	High Frequency 3680
					276
Features	0402 to 1206 Package Sizes	0603 to 1008 Package Sizes	0805 & 1008 Low Profile (3651)	0603 to 1206 Package Sizes	0402, 0603, 0805 Package Sizes
	1µH to 100mH Value (E12 Grid)	1.8nH to 4.7µH Value Range	0603 High Current (3652)	Low DC Resistance	1nH to 470nH Value Range
	DC Current 1200mA	DC Current up to 1Amp	0805 & 1008 High Q (3653)	Low Q Factor	DC Current 0.3 Amps
	Tolerances down to ±0.2µH	Tolerances down to 2%	Tolerances Down to 2%	High Reliability	Tolerances down to ±0.3 nH
	High Self Resonant Frequency	-40°C to 125°C Temp. Range	Up to 2.4A IDC	Range of Tolerances	E12 Value Grid

Inductive Products, Ferrite Beads

Product Ty	уре	BMB A & B Series	BMB R Series	BMB L Series	BMB P & S Series	BMB W Series	
		0402 to 1812 Packara Sizes 0603 to 1206 P					
Features		0402 to 1812 Package Sizes	0603 to 1206 Package Sizes	0603 to 0805 Package Sizes	0603 to 1812 Package Sizes	0603 Size	
		10R to 2K7 Impedance	26R to 600R Impedance	30R to 1K5 Impedance	10R to 600R Impedance	120R to 1K0 Impedance	
		General Purpose Applications	Low Frequency Applications	High Current	High Current	Minimal Electromagnetic Interference	
		High Frequency Applications	Prevents Signal Ringing	Signal Line Applications	Noise Filtering Applications	Minimises Stray Capacitance	
		DC Current to 0.6A	DC Current to 0.4A	DC Current to 1A	DC Current to 6A	DC Current to 0.2A	



Inductive Products, Power, Surface Mount - Unshielded

Product Type	Power Chokes 3621	Power Chokes 3622	Power Chokes 3623	Power Chokes 3624	Power Chokes 3625		
Features	Board Area from 3mm x 2.8mm	Board Area from 6.6mm x 4.5mm	Board Area from 22mm x 15mm	Board Area from 3.2mm x 1.6mm	Board Area from 6mm x 6mm		
	Values 1µH to 15,000µH	Values 1µH to 10,000 µH	Values 0.8µH to 1,000µH	Values 0.12µH to 3,300µH	Values 1.5µH to 1,000µH		
Current up to 9.5 Amps Current		Current up to 10 Amps	Current up to 16 Amps	Current up to 9 Amps	Current up to 7.2 Amps		
	Only 1.5mm Height	Less than 3mm Height	Less than 7mm Height	Less than 2mm Height	Less than 3mm Height		
	12 Package Styles	4 Package Sizes	2 Package Sizes	8 Package Sizes	3 Package Sizes		

Product Type	Power Chokes 3626
Features	Board Area from 7.5mm x 7.5mm Values 10µH to 5,000µH
	Current up to 4 Amps
	Less than 4mm Height
	2 Package Sizes



Inductive Products, Leaded - Unshielded

Product Type	Insulated SC 10 / 20 / 30	Leaded Axial SC	Leaded Radial SC	Moulded MSC
			60.0	
Features	0402 to 1812 and Arrays	4 Package Slzes	4 Package Slzes	2 Case Sizes
	5R to 2K ohms impedance	Suited to Power Circuits	Suited to Power Circuits	0.1µH to 10mH Value (E12 Grid)
	DC Current up to 6 Amps	Wide Value Range	Wide Value Range	DC Current up to 1.79 Amps
	HS Signal Line, Digital Sound,	E12 Series Values	E12 Series Values	5% or 10% Tolerance
	High Current, High Loss, etc	DC Current to 1.7A	DC Current to 5.6A	Dielectric Strength up to 1KV



Inductive Products, Power, Surface Mount - Shielded

Product Type	Shielded Power Chokes 3630	Shielded Power Chokes 3631	Shielded Power Chokes 3632	Shielded Power Chokes 3633	Shielded Power Chokes 3634
Features		Board Area from 12.5mm x 12.5mm		Board Area from 3.3mm x 3.5mm	Board Area from 3.8mm x 3.8mm
	Values 1µH to 10,000µH	Values 1.1µH to 1,500µH	Values 1.5µH to 15,000µH	Values 1µH to 220µH	Values 0.9µH to 1,000µH
	Current up to 4.5 Amps	Current up to 10.2 Amps	Current up to 5.6 Amps	Current up to 3.5 Amps	Current up to 4.6 Amps
	Less than 3mm Height	From 4mm Height	From 6mm Height	From less than 1mm Height	From less than 1.2mm Height
	6 Package Sizes	6 Package Sizes	2 Package Sizes	7 Package Sizes	9 Package Sizes

	Product Type	Shielded Power Chokes 3635	Shielded Power Chokes 3636	Shielded Power Chokes 3637	Shielded Power Chokes 3638	Shielded Power Chokes 3639
A DAMAGE AND A DAMAG				0		
ſ	Features	Board Area from 6.6mm x 6.6mm	Board Area 7.8mm x 7.5mm	Board Area from 7.5mm x 7.5mm	Board Area from 6mm x 6mm	Board Area from 8mm x 8mm
		Values .054µH to 7.4µH	Values 1.2µH to 5,600µH	Values 10µH to 1,500µH	Values 1µH to 1,000µH	Values 0.8µH to 330µH
		Current up to 38 Amps	Current up to 2.6 Amps	Current up to 4.6 Amps	Current up to 3.8 Amps	Current up to 7.8 Amps
		From 4.5mm Height	Less than 2.5mm Height	From 4mm Height	From less than 3mm Height	From less than 3mm Height
		2 Package Sizes	1 Package Size	3 Package Sizes	3 Package Sizes	5 Package Sizes



12

Dimensions are shown in mm for reference purposes only.

Specifications subject to change.



Capacitive Products, Ceramic - Surface Mount

		TYC
Ultra Stable	Semi Stable and High K	General Purpose, High K
		High Volumetric Efficiency Non Polar Construction
	v v	0402 - 1206 Sizes
		20% Tolerance Available
)	Ultra Stable Low ESR eing of Capacitance 11 to 1206 Sizes noces down to ±1%	Low ESR High Volumetric Efficiency eing of Capacitance Extended Voltage Ratings 11 to 1206 Sizes 0402 to 1206 Sizes

Capacitive Products, Tantalum - Surface Mount

Product Type	Standard TYTS	Extended Range TYTM	0805 Case Size TYTP	Low ESR TYTR
Features	Full Value Range	Super Compact Size	Super Compact Size	Suited to High Frequency
	A, B, C & D Case Sizes	A, B, C & D Case Sizes	Suited to High Density PCB's	B, C & D Case Sizes
	4V to 50V Ratings	2.5V to 50V Ratings	2.5V to 25V Ratings	6V to 35V Ratings
	10% / 20% Tolerance	10% or 20% Tolerance	10% or 20% Tolerance	10% or 20% Tolerance
	RoHS Compliant	RoHS Compliant	RoHS Compliant	RoHS Compliant

Capacitive Products, Aluminium Electrolytic - Surface Mount

Product Type	85°C TYEV	105°C TYEH	Long Life TYEL	Low Impedance TYEE	Organic Conductive Polymer TYOH	
Features	-40°C to +85°C	-40°C to +105°C	-40°C to +105°C	-55°C to +105°C	-55°C to +105°C	
	4.0V to 100V DC	6.3V to 100V DC	6.3V to 50V DC	6.3V to 50V DC	2.5V to 25V DC	
2000 Hours Load Life Up to 3000 Hours Load Life		3000 Hours Load Life	1000 Hours Load Life	2000 Hours Load Life		
	0.1 to 6800µF Capacitance Range	0.1 to 6800µF Capacitance Range	0.1 to 1000µF Capacitance Range	1.0 to 220µF Capacitance Range	22 to 2700µF Capacitance Range	
	7 Case Sizes	7 Case Sizes	6 Case Sizes	4 Case Sizes	7 Case Styles	



Colour Code in Accordance with IEC 62



E Series Value Grid

E Se	eries in	accor	dance	with	EC 63																		
E6	E12	E24	E96	E6	E12	E24	E96	E6	E12	E24	E96	E6	E12	E24	E96	E6	E12	E24	E96	E6	E12	E24	E96
100	100	100	100				147	220	220	220	215				316	470	470	470	464	680	680	680	681
			102	150	150	150	150				221	330	330	330	324				475				698
			105				154				226				332				487				715
			107			160	158				232				340				499				732
		110	110				162			240	237				348			510	511			750	750
			113				165				243			360	357				523				768
			115				169				249				365				536				787
	120	120	118				174				255				374				549		820	820	806
			121		180	180	178				261		390	390	383		560	560	562				825
			124				182		270	270	267				392				576				845
			127				187				274				402				590				866
		130	130				191				280				412				604				887
			133				196				287				422			620	619			910	909
			137			200	200				294			430	432				634				931
			140				205			300	301				442				649				953
			143				210				309				453				665				976



Associated Products



Alcoswitch Switches



Schrack PCB Relays



Amp Connectors



Power Resistors



Microdot Connectors and Cables



Contacts

 Austria
 - Vienna

 Phone:
 +43-1-905-60-0

 Fax:
 +43-1-905-60-1333

 Product
 Information Center:

 Phone:
 +43-1-905-60-1249

 Fax:
 +43-1-905-60-1251

Belgium - Kessel-Lo Phone: +32-16-352-300 Fax: +32-16-352-352

Bulgaria - Sofia Phone: +359-2-971-2152 Fax: +359-2-971-2153

Czech Republic and Slovakia

 Czech Republic- Kurim

 Phone:
 +420-541-162-111

 Fax:
 +420-541-162-223

 Product
 Information Center:

 Phone:
 +420-541-162-113

 Fax:
 +420-541-162-113

 Fax:
 +420-541-162-132

Denmark - Glostrup Phone: +45-43-48-04-00 Fax: +45-43-44-14-14

Egypt - Cairo Phone: +202-419-2334 Fax: +202-417-7647

Estonia- Tartu Phone: +372-5138-274 Fax: +372-7400-779

Finland - Helsinki Phone: +358-95-12-34-20 Fax: +358-95-12-34-250

France - Cergy-Pontoise Cedex Phone: +33-1-3420-8888 Fax: +33-1-3420-8600 Product Information Center: Phone: +33-1-3420-8686 Fax: +33-1-3420-8623

France Export Divisions – Cergy-Pontoise Cedex Phone: +33-1-3420-8804 Fax: +33-1-3420-8699

 Germany
 - Bensheim

 Phone:
 +49-6251-133-0

 Fax:
 +49-6251-133-1600

 Product
 Information Center:

 Phone:
 +49-6251-133-1999

 Fax:
 +49-6251-133-1988

Greece - Athens Phone: +30-210-9370-396/397 Fax: +30-210-9370-655

 Hungary
 - Budapest

 Phone:
 +36-1-289-1000

 Fax:
 +36-1-289-1010

 Product
 Information Center:

 Phone:
 +36-1-289-1016

 Fax:
 +36-1-289-1017

Ireland - Dublin Phone: +353-1-866-5612 Fax: +353-1-866-5714

Israel - Petach-Tikva Phone: +972-3-929-0999 Fax: +972-3-919-1088

 Italy - Collegno (Torino)

 Phone: +39-011-4012-111

 Fax: +39-011-4031-116

 Product Information Center:

 Phone: +39-011-4012-428

 Fax: +39-011-4028-7428

Lithuania and Latvia Lithuania - Vilnius Phone: +370-5-213-1402 Fax: +370-5-213-1403 Product Information Center: Phone: +370-5-211-3016 Fax: +370-5-213-1403

 Netherlands
 - 's-Hertogenbosch

 Phone:
 +31-73-6246-246

 Fax:
 +31-73-6212-365

 Product
 Information Center:

 Phone:
 +31-73-6246-999

 Fax:
 +31-73-6246-999

 Fax:
 +31-73-6246-998

Norway - Nesbru Phone: +47-66-77-88-50 Fax: +47-66-77-88-55

 Poland
 - Warsaw

 Phone:
 +48-22-4576-700

 Fax:
 +48-22-4576-720

 Product
 Information Center:

 Phone:
 +48-22-4576-704

 Fax:
 +48-22-4576-720

Romania - Bucharest Phone: +40-21-311-3479/3596 Fax: +40-21-312-0574

 Russia - Moscow

 Phone: +7-495-790-7902

 Fax: +7-495-721-1893

 Product Information Center:

 Phone: +7-495-790-7902-404

 Fax: +7-495-790-7902-404

RussiaSt.PetersburgPhone:+7-812-718-8192Fax:+7-812-718-8193

Slovenia - Ljubljana Phone: +386-1561-3270 Fax: +386-1561-3240

South Africa - Port Elizabeth Phone: +27-41-503-4500 Fax: +27-41-581-0440

Spain - Barcelona Phone: +34-93-291-0330 Fax: +34-93-201-7879

Sweden - Upplands Väsby Phone: +46-8-50-72-50-00 Fax: +46-8-50-72-50-01

Switzerland - Steinach Phone: +41-71-447-0447 Fax: +41-71-447-0444

Turkey - Istanbul Phone: +90-212-281-8181/2/3 +90-212-282-5130/5430 Fax: +90-212-281-8184

Ukraine - Kiev

Phone: +380-44-206-2265 Fax: +380-44-206-2264 Product Information Center: Phone: +380-44-206-2265 Fax: +380-44-206-2264

United Kingdom -

 Stanmore, Middlesex

 Phone:
 +44-8706-080208

 Fax:
 +44-208-954-6234

 Product Information Center:
 Freephone (UK only):

 0800-267-666
 Phone:

 Phone:
 +44-8706-080208

 Fax:
 +44-8706-080208

 Fax:
 +44-208-420-8095

tycoelectronics.com passives.tycoelectronics.com



Catalogue No: 1309350. Revise August 2007 TE Logo and Tyco Electronics are trademarks

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity: CRGV0805F374K