



LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			K	REVISED PER ECO-14-000066	30JUN2014	NK	MM



RECOMMENDED HOLE LAYOUT

- | | | | | |
|---------------|--|---------------|------|-----|
| 1 | TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD. | | | |
| 2 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING. | | | |
| 3 | POINT OF MEASUREMENT FOR PLATING THICKNESS. | | | |
| 4 | RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION. | | | |
| 5 | <table border="1"><tr><td>$\varnothing$</td><td>.020</td><td>(M)</td></tr></table> FOR KINKED TAILS. | $\varnothing$ | .020 | (M) |
| $\varnothing$ | .020 | (M) | | |
| 6 | OBsolete PARTS: OBsolete CIS STREAMLINING PER D.RENAUD/D.SINISI | | | |

		3.984	3.900	39	40	2-104344-7
		3.484	3.400	34	35	2-104344-6
		2.984	2.900	29	30	2-104344-5
		2.584	2.500	25	26	2-104344-4
		2.484	2.400	24	25	2-104344-3
		2.384	2.300	23	24	2-104344-2
		2.284	2.200	22	23	2-104344-1
		2.184	2.100	21	22	2-104344-0
		2.084	2.000	20	21	1-104344-9
6	SUPERCEDED	1.984	1.900	19	20	1-104344-8
		1.884	1.800	18	19	1-104344-7
		1.784	1.700	17	18	1-104344-6
		1.684	1.600	16	17	1-104344-5
		1.584	1.500	15	16	1-104344-4
6	OBSOLETE	1.484	1.400	14	15	1-104344-3
		1.384	1.300	13	14	1-104344-2
6	OBSOLETE	1.284	1.200	12	13	1-104344-1
6	SUPERCEDED	1.184	1.100	11	12	1-104344-0
6	OBSOLETE	1.084	1.000	10	11	104344-9
		.984	.900	9	10	104344-8
		.884	.800	8	9	104344-7
		.784	.700	7	8	104344-6
		.684	.600	6	7	104344-5
		.584	.500	5	6	104344-4
		.484	.400	4	5	104344-3
		.384	.300	3	4	104344-2
		.284	.200	2	3	104344-1
		C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL		08FE8B8		 TE Connectivity	
		CHK R FEIDT		08FE8B8			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R FEIDT		NAME	
		0 PLC ± -		PRODUCT SPEC		HEADER ASSY, MOD II,BREAKAWAY, SINGLE ROW,.100 CL, VERT, .025 SQ POSTS, WITH RETENTION FEATURE	
		1 PLC ± -		—			
		2 PLC ± -		APPLICATION SPEC			
		3 PLC ± .005		—			
4 PLC ± -		ANGLES ± -		WEIGHT		—	
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC COLOR-BLACK		FINISH POSTS: .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL		SIZE		CAGE CODE	
POSTS: COPPER ALLOY				A2		00779	
				DRAWING NO		C-104344	
				RESTRICTED TO		—	
CUSTOMER DRAWING						SCALE 4:1	
						SHEET 1 of 1	
						REV K	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104344-6](#)