






RECOMMENDED HOLE LAYOUT

8	OBSOLETE	7	6	1,2,39,40	1,2,39,40	3.984	3.900	39	80	7-104355-0	
		7	6	1,2,29,30	1,2,29,30	2.984	2.900	29	60	6-104355-9	
		7	6	1,2,24,25	1,2,24,25	2.484	2.400	24	50	6-104355-8	
		7	6	1,2,19,20	1,2,19,20	1.984	1.900	19	40	6-104355-7	
		7	6	1,2,16,17	1,2,16,17	1.684	1.600	16	34	6-104355-6	
		7	6	1,2,14,15	1,2,14,15	1.484	1.400	14	30	6-104355-5	
		7	6	1,2,13,14	1,2,13,14	1.384	1.300	13	28	6-104355-4	
		7	6	1,2,12,13	1,2,12,13	1.284	1.200	12	26	6-104355-3	
		7	6	1,2,11,12	1,2,11,12	1.184	1.100	11	24	6-104355-2	
		7	6	1,2,10,11	1,2,10,11	1.084	1.000	10	22	6-104355-1	
		7	6	1,2,9,10	1,2,9,10	.984	.900	9	20	6-104355-0	
		7	6	1,2,8,9	1,2,8,9	.884	.800	8	18	5-104355-9	
		7	6	1,2,7,8	1,2,7,8	.784	.700	7	16	5-104355-8	
		7	6	1,2,6,7	1,2,6,7	.684	.600	6	14	5-104355-7	
		7	6	1,2,5,6	1,2,5,6	.584	.500	5	12	5-104355-6	
8	OBSOLETE	7	6	1,2,4,5	1,2,4,5	.484	.400	4	10	5-104355-5	
		7	6	1,2,3,4	1,2,3,4	.384	.300	3	8	5-104355-4	
		7	6	1,2,3	1,2,3	.284	.200	2	6	5-104355-3	
8	OBSOLETE	7	6	1,2	1,2	.184	.100	1	4	5-104355-2	
		OBSOLETE	4	1,2,39,40	1,2,39,40	3.984	3.900	39	80	2-104355-0	
		OBSOLETE	4	1,2,29,30	1,2,29,30	2.984	2.900	29	60	1-104355-9	
		OBSOLETE	4	1,2,24,25	1,2,24,25	2.484	2.400	24	50	1-104355-8	
		8	OBSOLETE	4	1,2,19,20	1,2,19,20	1.984	1.900	19	40	1-104355-7
				4	1,2,16,17	1,2,16,17	1.684	1.600	16	34	1-104355-6
				4	1,2,14,15	1,2,14,15	1.484	1.400	14	30	1-104355-5
				4	1,2,13,14	1,2,13,14	1.384	1.300	13	28	1-104355-4
				4	1,2,12,13	1,2,12,13	1.284	1.200	12	26	1-104355-3
				4	1,2,11,12	1,2,11,12	1.184	1.100	11	24	1-104355-2
				4	1,2,10,11	1,2,10,11	1.084	1.000	10	22	1-104355-1
		8	OBSOLETE	4	1,2,9,10	1,2,9,10	.984	.900	9	20	1-104355-0
				4	1,2,8,9	1,2,8,9	.884	.800	8	18	104355-9
				4	1,2,7,8	1,2,7,8	.784	.700	7	16	104355-8
				4	1,2,6,7	1,2,6,7	.684	.600	6	14	104355-7
4	1,2,5,6			1,2,5,6	.584	.500	5	12	104355-6		
4	1,2,4,5			1,2,4,5	.484	.400	4	10	104355-5		
4	1,2,3,4			1,2,3,4	.384	.300	3	8	104355-4		
OBSOLETE	OBSOLETE	5	1,2,3	1,2,3	.284	.200	2	6	104355-3		
		4	1,2	1,2	.184	.100	1	4	104355-2		
		4	1	1	.084	-	-	2	104355-1		
	REMARKS	PLATING	ROW N	ROW M	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER		
			HOLD-DOWN POST CONFIG LOCATION								

THIS DRAWING IS A CONTROLLED DOCUMENT.						DIN M. PASTAL		04FEB88				TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		QWK R. FEIDT		09FEB88		NAME		HEADER ASSEMBLY, MOD II, BREAKAWAY, RIGHT ANGLE, DOUBLE ROW, .100X.100			
		APRD R FLICKER		09FEB88		PRODUCT SPEC							
		—				APPLICATION SPEC							
		—											
MATERIAL	HOUSING POST: COPPER ALLOY	SEE TABLE		WEIGHT	—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO —			
							A1	00779	C=104355				
							SCALE		4:1	SHEET	1 OF 1	REV	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104355-5](#)