

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

11

27.79	20.32	15	24.89	34	8-104666-3
12.55	5.08	4	9.65	10	8-104666-2
22.71	15.24	12	19.81	26	8-104666-1
21.44	13.97	11	18.54	24	8-104666-0
16.36	8.89	7	13.46	16	7-104666-9
49.38	46.99	33	46.48	68	7-104666-8
44.30	36.83	29	41.40	60	7-104666-7
69.70	62.23	49	66.80	100	7-104666-6
57.00	49.53	39	54.10	80	7-104666-5
37.95	30.48	24	35.05	50	7-104666-4
31.60	24.13	19	28.70	40	7-104666-3
25.25	17.78	14	22.35	30	7-104666-2
18.90	11.43	9	16.00	20	7-104666-1

7

27.79	20.32	15	24.89	34	9 6-104666-3
12.55	5.08	4	9.65	10	9 6-104666-2
22.71	15.24	12	19.81	26	9 6-104666-1
21.44	13.97	11	18.54	24	9 6-104666-0
16.36	8.89	7	13.46	16	9 5-104666-9
49.38	46.99	33	46.48	68	9 5-104666-8
44.30	36.83	29	41.40	60	9 5-104666-7
69.70	62.23	49	66.80	100	9 5-104666-6
57.00	49.53	39	54.10	80	9 5-104666-5
37.95	30.48	24	35.05	50	9 5-104666-4
31.60	24.13	19	28.70	40	9 5-104666-3
25.25	17.78	14	22.35	30	9 5-104666-2
18.90	11.43	9	16.00	20	9 5-104666-1

FINISH

DIM_G

DIM_C

B SPACES

DIM_A

NO OF POSN

PART NUMBER

10

27.79	20.32	15	24.89	34	3-104666-3
12.55	5.08	4	9.65	10	3-104666-2
22.71	15.24	12	19.81	26	3-104666-1
21.44	13.97	11	18.54	24	3-104666-0
16.36	8.89	7	13.46	16	2-104666-9
49.38	46.99	33	46.48	68	2-104666-8
44.30	36.83	29	41.40	60	2-104666-7
69.70	62.23	49	66.80	100	2-104666-6
57.00	49.53	39	54.10	80	2-104666-5
37.95	30.48	24	35.05	50	2-104666-4
31.60	24.13	19	28.70	40	2-104666-3
25.25	17.78	14	22.35	30	2-104666-2
18.90	11.43	9	16.00	20	2-104666-1

1

27.79	20.32	15	24.89	34	1-104666-3
12.55	5.08	4	9.65	10	1-104666-2
22.71	15.24	12	19.81	26	1-104666-1
21.44	13.97	11	18.54	24	1-104666-0
16.36	8.89	7	13.46	16	104666-9
49.38	46.99	33	46.48	68	104666-8
44.30	36.83	29	41.40	60	104666-7
69.70	62.23	49	66.80	100	104666-6
57.00	49.53	39	54.10	80	104666-5
37.95	30.48	24	35.05	50	104666-4
31.60	24.13	19	28.70	40	104666-3
25.25	17.78	14	22.35	30	104666-2
18.90	11.43	9	16.00	20	104666-1

FINISH

DIM_G

DIM_C

B SPACES

DIM_A

NO OF POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC±0.3

1 PLC±0.13

2 PLC±0.13

3 PLC±0.13

4 PLC±0.13

ANGLES±0.5°

FINISH-

SEE TABLE

DWN22NOV2017G. RAMESH

CHK22NOV2017J. OLSON

APVD22NOV2017J. OLSON

PRODUCT SPEC108-1093

APPLICATION SPEC114-25031

WEIGHT-

CUSTOMER DRAWING

TEConnectivity

NAMEHEADER ASSEMBLY, VERTICAL, DOUBLE ROW, W/SIDE & END LATCHES, AMPMODU System 50

SIZEA200779

CAGE CODEC

DRAWING NO104666

RESTRICTED TO

SCALE4:1

SHEET2 OF 2

REVAC

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104666-6](#)