








- 1 MATERIAL:
RECEPTACLE CONTACTS- PHOSPHOR BRONZE
RECEPTACLE HOUSING AND TERMINATING COVERS- THERMOPLASTIC,
COLOR: BLACK.
- 2 PLATING:
RECEPTACLE CONTACTS- 0.00076 [.000030] MINIMUM GOLD PLATE IN CONTACT AREA,
0.00127 [.000050] MINIMUM BRIGHT TIN-LEAD PLATE IN TERMINATION AREA,
ALL OVER 0.00127 [.000050] MINIMUM NICKEL.
- 3 RECOMMENDED WIRE:
28 AWG- 0.91 [.036] MAX O.D. PVC OR POLYETHYLENE INSULATION.
- 4 SHORT-LONG CONTACT SEQUENCE MUST ALTERNATE BUT MAY BEGIN WITH EITHER
A SHORT OR LONG CONTACT.
- 5 PLATING:
RECEPTACLE CONTACTS- 0.00076 [.000030] MINIMUM GOLD PLATE IN CONTACT AREA,
0.00127 [.000050] MINIMUM MATTE TIN PLATE IN TERMINATION AREA,
ALL OVER 0.00127 [.000050] MINIMUM NICKEL.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

		71.83 [2.828]	63.91 [2.516]	62.23 [2.450]	49	100	6-104892-0
	OBsolete	65.48 [2.578]	57.56 [2.266]	55.88 [2.200]	44	90	5-104892-9
		59.13 [2.328]	51.21 [2.016]	49.53 [1.950]	39	80	5-104892-8
		52.78 [2.078]	44.86 [1.766]	43.18 [1.700]	34	70	5-104892-7
	OBsolete	46.43 [1.828]	38.51 [1.516]	36.83 [1.450]	29	60	5-104892-6
		40.08 [1.578]	32.16 [1.266]	30.48 [1.200]	24	50	5-104892-5
		33.73 [1.328]	25.81 [1.016]	24.13 [.950]	19	40	5-104892-4
		27.38 [1.078]	19.46 [.766]	17.78 [.700]	14	30	5-104892-3
		21.03 [.828]	13.11 [.516]	11.43 [.450]	9	20	5-104892-2
		14.68 [.578]	6.76 [.266]	5.08 [.200]	4	10	5-104892-1
	OBsolete	71.83 [2.828]	63.91 [2.516]	62.23 [2.450]	49	100	1-104892-0
	OBsolete	65.48 [2.578]	57.56 [2.266]	55.88 [2.200]	44	90	104892-9
		59.13 [2.328]	51.21 [2.016]	49.53 [1.950]	39	80	104892-8
		52.78 [2.078]	44.86 [1.766]	43.18 [1.700]	34	70	104892-7
	OBsolete	46.43 [1.828]	38.51 [1.516]	36.83 [1.450]	29	60	104892-6
		40.08 [1.578]	32.16 [1.266]	30.48 [1.200]	24	50	104892-5
		33.73 [1.328]	25.81 [1.016]	24.13 [.950]	19	40	104892-4
		27.38 [1.078]	19.46 [.766]	17.78 [.700]	14	30	104892-3
		21.03 [.828]	13.11 [.516]	11.43 [.450]	9	20	104892-2
	OBsolete	14.68 [.578]	6.76 [.266]	5.08 [.200]	4	10	104892-1
		D	C	B	A	NO. OF POSN	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG J.HERRINGTON 6-18-93 CHK P.SREMCICH 6-24-93		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.36 [015] 3 PLC ± — 4 PLC ± — ANGLES ± —		— NAME AMPMODU 50/50 GRID CABLE CONN. ASSY WITH LATCH	
		APVD PRODUCT SPEC 108-1443 APPLICATION SPEC 114-7010		SIZE A1	
MATERIAL 		FINISH 		CODE CODE 00779	
		WEIGHT —		DRAWING NO 104892	
		CUSTOMER DRAWING		RESTRICTED TO —	
				SCALE 10:1	
				SHEET 1 OF 1	
				REV G.3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104892-3](#)