

THIS DRAWING IS UNPUBLISHED.
VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG

© COPYRIGHT - By -

RELEASED FOR PUBLICATION
FREI FÜR VERÖFFENTLICHUNG

ALL RIGHTS RESERVED.
ALLE RECHTE VORBEHALTEN

MATED WITH
PASSEND ZU:
BG6

REVISIONS
ÄNDERUNGEN

P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
	C11	ECR-17-009069	12FEB2018	SG	MKO

Screw version
Thermo

1

2

M3x10

77.5

83.5

21.2

34

Crimp version

1

3

M3x10

77.5

83.5

spring clamp version

4

1

M3x10

77.5

83.5

assembly directions

Sti

Bu

19.5 x

x distance for a safe contact max: max: 21 mm

Contact arrangement

view from termination side

Printing 1-16 Thermo

1+ 2+ 3+ 4+ 5+ 6+ 7+ 8+

● ● ● ● ● ● ● ●

● ● ● ● ● ● ● ●

9- 10- 11- 12- 13- 14- 15- 16-

Printing 17-32 Screw

17 18 19 20 21 22 23 24

● ● ● ● ● ● ● ●

● ● ● ● ● ● ● ●

25 26 27 28 29 30 31 32

Printing 1-16 Screw

1 2 3 4 5 6 7 8

● ● ● ● ● ● ● ●

● ● ● ● ● ● ● ●

9 10 11 12 13 14 15 16

Printing 8+4+4 Screw/Thermo

1 2 3 4 5+ 6+ 7+ 8+

● ● ● ● ● ● ● ●

● ● ● ● ● ● ● ●

9 10 11 12 13- 14- 15- 16-

Panel cut-out for contact insert

when used without housing

70.5

27

20

36

77.5

85.5

NOTES:

1

SUITABLE CRIMP CONTACTS: SERIES HE/HA

OUTER DIMENSIONS OF INSULATION: MAX. Ø3,2 MM

2

SUITABLE HOOD SIZE 6, 10: SERIES HB; HD;HIP;EMV

SUITABLE INSERTION AND EXTRACTION TOOL:

SCREWDRIVER 0,5x3 DIN 5264

3

Strip lenght: Screw conection 10mm

Spring clamp conection 10mm Crimp conection 7.5mm

4

STANDARDS:

DIN EN 61984; DIN EN 60664-1

5

PACKAGING:

5 SETS IN A CARTON, PRE-MOUNTED

6

SPECIAL PACKAGING: Krauss-Maffei

PACKAGING UNIT: 200 PIECES

OBSELETE

OBSELETE

OBSELETE

SUPERSEDED BY T204-0163101-000

OBSELETE

OBSELETE

0-19-41-89-57-97-112-92-31-91-71-1

6555555555555555

HE.16.Sti.S.B 1-16:KM

HE.16.Sti.S.B 17-32-AU

HE.16.Sti.S.-T.B 8+4+4

HE.16.Sti.S.B 1-16-AU

HE.16.Sti.S.C.B 17-32

HE.16.Sti.S.C.B 1-16

HE.16.Sti.S.C.B 17-32

HE.16.Sti.C

HE.16.Sti.S.B 17-32

HE.16.Sti.S.-T.B 1-16

HE.16.Sti.S.B 1-16

cover spring clamp version

cover crimp version

cover screw version

pin insert

DESCRIPTION

MATERIAL

COLOR

ITEM NO. POS.

NOTES

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT.

DIMENSIONS:
MASSEINHEITEN:
mm

MATERIAL

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
ALL GEMEINTOLERANZEN

0 PLC +

1 PLC +

2 PLC +

3 PLC +

4 PLC +

ANGLES / WINKEL ± -

FINISH / OBERFLÄCHE / FARBE

-

DWN 08.02.99

CHK 08.02.00

APVD

PRODUCT SPEC
PRODUKTSPEZ.

APPLICATION SPEC
VERARBEITUNGSSPEZ.

WEIGHT
GEWICHT

CUSTOMER DRAWING / KUNDENZEICHNUNG

TE Connectivity

Male insert
HE.16.STIs/C

SIZE A2

CAGE CODE 00779

DRAWING NO
ZEICHNUNGS-NR.
C=1103638

RESTRICTED TO
NUR FÜR

SCALE
MASSSTAB 1:1

SHEET
BLATT 1

REV C11

1471-9 (1/15)

1103638

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1103638-1](#)