





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		B6	REVISED PER ECR ECR-13-011405	17JUL13	GRZ DZ

- 1
- CONTINUOUS STRIP ON REELS (NO SPLICES) WITH TERMINALS LOCATED ON .220±.003 CENTERS.
- 2
- SLOT ACCEPTS 0.64-0.81mm [#22-#20] AWG COPPER MAGNET WIRE. SINGLE OR DOUBLE WIRE OF THE SAME SIZE AND TYPE.
- 3
- PREPRODUCTION - FASR REQUIRED
- 4
- SPECIAL CAVITY ANVIL LOCATION REQUIRED 4.83±0.07[.190±.003] REF APPLICATION SPEC 114-2046, SEC. 3.2 NOTE 7 REVISION T OR LATER.



OBSOLETE	REVERSE	1217973-2
	STANDARD	3 1217973-1
	REELING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN jr ruth 15JUL03		 TE Connectivity								
DIMENSIONS: INCHES			CHK KURT A. RANDOLPH 15JUL03										
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL, SPLICE, MAG-MATE								
			0 PLC ± -										
			1 PLC ± -										
			2 PLC ± .010										
			3 PLC ± -		SIZE A2								
			4 PLC ± -					CAGE CODE 00779					
			ANGLES ± -								DRAWING NO C=1217973		
MATERIAL H04 PHOS BRONZE			WEIGHT -		SCALE 10:1								
FINISH (B6) .000080 MIN TIN OVER .000020 MIN NICKEL			CUSTOMER DRAWING					SHEET 1 of 1					
											REV B6		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1217973-2](#)