









LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			D2	PROD. SPEC INFO ADDED	01OCT2010	PKS	MP
			D3	ECR-19-010275	02JUL2019	KD	FL
			D4	ECR-20-001157	13APR2020	KD	FL

PERSPECTIVE VIEW
FOR REF. ONLY
SCALE 1:1



PANEL CUT OFF DIMENSIONS
SCALE 1:1



- 1 TYPICAL CAVITY SUITABLE FOR:
FASTIN-FASTON TAB CONTACTS 6.3 mm SRS:
P/N: 293041, 0.3-1.0 mm2 WIRE RANGE
60294, 0.3-0.8 mm2 WIRE RANGE
160691, 0.3-0.8 mm2 WIRE RANGE
AMPLIVAR CONTACTS:
P/N: 141051, 0.1-0.5 mm2 WIRE RANGE
142411, 0.3-1.6 mm2 WIRE RANGE
MAX. INSULATION DIA. 2.8 mm,
MAX. INSULATION CRIMP WIDTH 3.3 mm.
- 2 PA UNFILLED, UL 94-V2, NATURE COLOUR
ACCORDING TO IEC 60335-1 NORM.
- 3 PA66 UNFILLED, UL 94-V2, NATURE COLOUR
- 4 TRADEMARK AND PART NUMBER
OPTIONAL POSITION.
- 5 CIRCUIT IDENTIFICATION NUMBERS, 1 TO 5.
- 6 POLARIZATION KEYS DIMENTIONS AND POSITIONS
ARE ACCORDING TO "RAST 5" NORM
RAST CODE 05-B, 05-D.
- 7 PRELIMINARY - NO RELEASED FOR PRODUCTION
- 8 PA66 UNFILLED, UL94-V0,
GWPE7 750°C NO FLAME ACCORDING TO IEC-60335-1

	NATURAL	SEE NOTE 2	9-1241857-5
	NATURAL	SEE NOTE 8	1-1241857-5
	NATURAL	SEE NOTE 3	0-1241857-5
NOTE	COLOUR	MATERIAL	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		06 JUN 2005 DWN H. YAALI CHK - G. TURCO APVD -		 Tyco Electronics AMP Italia S.R.L. C.so F.lli Cervi, 15 COLLEGNO (TO)	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.3 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±1°		NAME 5POS. FASTIN-FASTON TAB HOUSING RAST 5, PANEL MOUNT VERSION. -	
MATERIAL SEE TABLE		FINISH WEIGHT -		SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-1241857	RESTRICTED TO
				SCALE 3:1	SHEET OF REV D4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9-1241857-5](#)