

LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
AJ	16				B	REVISED PER 0514-0485-02	170CT03	KW
					C	REVISED PER 0514-0184-04.	15DEC04	JL

- 1

ZINC PER QQ-Z-363.
- 2

POLYMETHYLPENTENE PER ASTM-D-1238.
- 3

PHOSPHOR BRONZE PER QQ-B-750.
- 4

BRASS PER ASTM-B-453.
- 5



BRASS PER ASTM-B-16.
- 6

NICKEL PLATE PER QQ-N-290,
3.81 μ m [.000150] MINIMUM THICK.
- 7

TIN PLATE PER ASTM-B-545,
3.81 μ m [.000150] MINIMUM THICK.
- 8

GOLD PLATE PER MIL-G-45204,
0.76 μ m [.000030] MINIMUM THICK.
- 9

POLYPHTHALAMIDE, PPA, GENERAL PURPOSE.
10. SEE INSTRUCTION SHEET 2769.



OBSOLETE	9	1274084-2
	2	1274084-1
DIELECTRIC MATERIAL		PART NUMBER

				PART NO			
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.20 [.008] 3 PLC DEC ± - ANGLES ± - MATERIAL SEE NOTES 1 THRU 5 & 9		DR 7-10-98 J. LIPPETT		AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME JACK, RIGHT ANGLE, PCB 75 OHM, SERIES BNC			
		CHK 7-10-98 J. LIPPETT					
		APPD 7-10-98 J. LIPPETT					
		APPD 7-10-98 J. LIPPETT					
		PRODUCT SPEC 108-12078					
FINISH SEE NOTES 6 THRU 8		APPLICATION SPEC -		SIZE D	CAGE CODE 00779	DRAWING NO 1274084	
		WEIGHT -		SCALE 4:1		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1274084-1](#)