




DETAIL A
SCALE 20:1





LOC		DIST		REVISIONS						
GE		00		P	LTR	DESCRIPTION	DATE	DWN	APVD	
				D		REVISED PER EC OK40-0405-02	17APR2002	AH	TW	
				D1		REVISED PER EC OK40-0248-03	02SEP2003	AH	TW	
				E		REVISED PER OK40-0074-04	23MAR2004	AG	TW	
				F		REVISED PER ECR 05-003800	17NOV2005	DLD	JLT	

1 MATERIAL: 0.30 THICK COPPER ALLOY, PREPLATED WITH 0.0008 MINIMUM THICK MATTE TIN (ELV COMPLIANT).



4. QUALIFICATION OF THE CRIMP APPLICATION TOOLING SHALL BE CONTROLLED BY THE REQUIREMENTS ESTABLISHED UNDER USCAR 21.

5. LOOSE END SPLICING TO BE USED.



3	1-1326031-1 REELED FOR AMP APPLICATORS							12 AWG	1-1326031-2
	1.35	6.8	4.30	5.89	4.7	2.7	5.25	12 AWG	1-1326031-1
3	1326031-5 REELED FOR AMP APPLICATORS							14 AWG	1-1326031-0
	1326031-4 REELED FOR AMP APPLICATORS							16 AWG	1326031-9
	1326031-3 REELED FOR AMP APPLICATORS							18 AWG	1326031-8
	1326031-2 REELED FOR AMP APPLICATORS							20 AWG	1326031-7
	1326031-1 REELED FOR AMP APPLICATORS							22 AWG	1326031-6
2	1.35	6.5	4.30	5.62	3.9	1.70	3.88	14 AWG	1326031-5
	1.10	5.6	3.80	4.54	3.9	1.70	3.88	16 AWG	1326031-4
	1.10	5.6	3.80	4.54	3.3	1.30	2.76	18 AWG	1326031-3
	0.90	5.0	3.40	4.11	3.3	1.30	2.76	20 AWG	1326031-2
	0.90	5.0	3.40	4.11	2.5	0.90	2.11	22 AWG	1326031-1
REELING	N	L	ØK	J	H	ØF	E	WIRE SIZE	PART NO.

THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHALL BE CONTACTED FOR THE LATEST REVISION.		DWN D. STRAUSSER 28APR99	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK D. BROWN 28APR99	NAME AMP	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.3 1 PLC ±0.10 3 PLC ±. 4 PLC ±. ANGLES ±°		APVD D. BROWN 28APR99	PRODUCT SPEC SAE/USCAR-2 8/97	
MATERIAL		114-13013	APPLICATION SPEC	
FINISH		114-13013	WEIGHT	
CUSTOMER DRAWING		10779	SIZE A	
SCALE 10:1		00779	DRAWING NO 1326031	
SHEET 1 OF 1		00779	REV F	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1326031-1](#)