

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

JAN ,2006.

© COPYRIGHT 2006 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

E

B

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REVISED PER ECO-11-005033	01APR11	RK	HMR

NOTES:

1

PACK IN ACCORDANCE WITH AMP SPEC 107-3275

2

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275

3

Au PLATING

4

ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:DC - 4 GHz

NOMINAL IMPEDANCE:50 Ohm

INSULATION RESISTANCE:1000 MOhm

WORKING VOLTAGE:250 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:750 Volts RMS Max

CONTACT RESISTANCE:CENTRE CONTACT:6.00 mOhm Max

OUTER CONTACT:1.00 mOhm Max

5

MECHANICAL CHARACTERISTICS

MOUNT NUT RECOMMENDED TORQUE:0.75N

DURABILITY:500 Cycles Min

6

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:-65 to +165 DegC

1

2

3

NO.10-32UNF

6.00 A/F HEX

4.30 A/F

1.00

11.50

12.30

15.40

Ø0.50

Ø3.69

5

4

Ø7.30

NO.10-32UNEF

6.00 A/F HEX

1.60

		1	1	BRASS	3	LOCKWASHER	5
		1	1	BRASS	3	HEX NUT	4
		1	1	PTFE		INSULATION	3
		1	1	BRASS	3	CONTACT	2
		1	1	BRASS	3	BODY	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		2	1				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0

PLC

±

-

1

PLC

±

-

2

PLC

±

-

3

PLC

±

-

4

PLC

±

-

ANGLES

±

-

FINISH

-

DWN
J.SANDWELL
12JAN06

CHK
S.PARLOW
12JAN06

APVD
F.WHEELER-KING
12JAN06

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME

SMB BULKHEAD SOCKET REAR MOUNT 50 OHM

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1337479

-

SCALE
NTS

SHEET
1 OF 1

REV
C1

1470-19

(3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1337479-0](#)