








LOC		DIST		REVISIONS					
-		-		DESCRIPTION			DATE	DWN	APVD
		P	LTR						
			F	REV PER ECO 14-003443			3-21-14	CT	DH
</									

- 1 HOUSING: LCP, UL94V0, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE.
- 2 FINISH: 1.27µm GOLD IN CONTACT AREA 1.27µm MIN. TIN-LEAD ON PCB TAIL OVER 3.81µm MIN. NICKEL OVER ALL.
- 3 FINISH: 1.27µm GOLD IN CONTACT AREA 1.27µm MIN. TIN ON PCB TAIL OVER 3.81µm MIN. NICKEL OVER ALL.
- 4 PLATED THROUGH HOLE PER TE SPEC. 114-13056, FIGURE 4.
- 5 ADDITIONAL CONNECTOR-SIDE KEEP-OUT AREA REQUIRED IF CONNECTOR-SIDE EXTRACTION TOOL IS TO BE USED.
- 6 PLASTIC ALIGNMENT PIN MUST BE REMOVED FLUSH TO HOUSING BODY PRIOR TO INSERTION INTO RTM LAYOUT

3	1410186-2
2	1410186-1
PLATING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	30SEP2003	TE Connectivity	
		CHK	30SEP2003		
		APVD	30SEP2003	NAME	
				CONNECTOR ASSEMBLY, BACKPLANE	
				VERTICAL RECEPTACLE, HALF, LEFT END,	
				20.3mm, MultiGig RT 2	
				SIZE	
				A100779C=1410186	
				RESTRICTED TO	
				-	
				SCALE	
				8:1	
				SHEET	
				1 OF 2	
				REV	
				F	

REAR TRANSITION MODULE APPLICATION



RTM PC BOARD LAYOUT
(CONNECTOR SIDE)
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN <u>SIPF</u> 30SEP2003		 TE Connectivity	
		CMP <u>CONSOLI</u> 30SEP2003			
DIMENSIONS:		APVD 30SEP2003		NAME	
mm	TOLERANCES, UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC		CONNECTOR ASSEMBLY, BACKPLANE	
	0 PLOC ±.05	108-2072		VERTICAL RECEPTACLE, HALF, LEFT END,	
	2 PLOC ±.05.13	APPLICATION SPEC		20.3mm, MultiGig RT 2	
	4 PLOC ±.05	WEIGHT		SIZE CASE CODE DRAWING NO	
	ANGLES ±.1°	114-13056		A100779C-1410186	
MATERIAL	FINISH	CUSTOMER DRAWING		RESTRICTED TO	
-	SEE TABLE			SCALE 8:1 SHEET 2 OF 2 REV F	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1410186-1](#)