



# Introducing RW-175

Highly flame-resistant, high-temperature, chemical-resistant RW-175 tubing provides tough, semirigid, very-thin-wall insulation and strain relief of multipin connectors, solder joints and other delicate electrical connections and terminations. It is well-suited for applications that require dense packing of components or visual inspection of covered components. It is especially suitable for applications requiring outstanding abrasion and cut-through resistance and superior chemical and solvent resistance. Its high temperature performance meets or exceeds military and industrial standards. RW-175 meets NASA outgassing requirements making it suitable for use in space applications such as satellites.

## KEY FEATURES

- 2:1 shrink ratio for all standard sizes
- Tough, semirigid, very-thin-wall insulation
- High flame-resistance, meeting the requirements of AMS-DTL-23053, Test C, with UL and CSA VW-1 flammability rating
- High temperature performance that meets or exceeds military and industrial standards
- Protection from most industrial solvents, fuels, and chemicals
- Available in several "microtubing" sizes for applications requiring recovered I.D.'s as small as .007" (0.178mm)
- Meets NASA outgassing requirements
- Offers improved clarity (clear version) and increased resistance to crazing when compared to previously offered solutions

## APPLICATIONS

- Appliances
- Military and commercial aircraft
- Satellites
- Commercial electronics and communication
- Industrial equipment

## ELECTRICAL

- Provides excellent electrical insulation
- Not recommended for use as a primary insulator at temperatures exceeding 135°C [275°F]

## MECHANICAL

- Tough modified polyvinylidene fluoride material provides outstanding abrasion and cut-through resistance
- Excellent for strain relief when installed on delicate electrical connections and terminations

## TEMPERATURE RATING

- Full recovery temperature: 175°C [347°F]
- Operating Temperature range: -55°C to 175°C [-67°F to 347°F]

## STANDARDS AND SPECIFICATIONS

- RW-3029/2
- RW-175 Microtubing SCD
- SAE-AMS-DTL-23053/8
- UL 224 VW-1
- CSA C22.2 No. 198.1-98 VW-1

## ORDERING INFORMATION


- Color: Clear (-X) (standard); Black (-O) (nonstandard)
- Standard packaging (-STK): 1.2m [4 ft.] lengths  
Optional packaging (-SP): Spool, varying lengths (consult TE for details)
- Ordering description: Specify product name, size, and color; for example, RW-175-3/16-X.

**SAMPLES NOW AVAILABLE**

[te.com/products/RW-175](http://te.com/products/RW-175)



RW-175 DIMENSIONS



| Size  | Minimum Expanded I.D. (D) |       | Maximum Recovered I.D. (d) |       | Nominal Recovered Jacket Wall (W) |            |
|-------|---------------------------|-------|----------------------------|-------|-----------------------------------|------------|
|       | in.                       | mm.   | in.                        | mm.   | in.                               | mm.        |
| 3/64  | .046                      | 1.17  | .023                       | .58   | .010 ± .002                       | .25 ± .051 |
| 1/16  | .063                      | 1.60  | .031                       | .79   | .010 ± .002                       | .25 ± .051 |
| 3/32  | .093                      | 2.36  | .046                       | 1.17  | .010 ± .002                       | .25 ± .051 |
| 1/8   | .125                      | 3.18  | .062                       | 1.58  | .010 ± .002                       | .25 ± .051 |
| 3/16  | .187                      | 4.75  | .093                       | 2.36  | .010 ± .002                       | .25 ± .051 |
| 1/4   | .250                      | 6.35  | .125                       | 3.18  | .013 ± .002                       | .33 ± .051 |
| 3/8   | .375                      | 9.53  | .187                       | 4.75  | .013 ± .002                       | .33 ± .051 |
| 1/2   | .500                      | 12.70 | .250                       | 6.35  | .013 ± .002                       | .33 ± .051 |
| 3/4   | .750                      | 19.05 | .375                       | 9.53  | .017 ± .003                       | .43 ± .076 |
| 1     | 1.000                     | 25.40 | .500                       | 12.70 | .019 ± .003                       | .48 ± .076 |
| 1-1/2 | 1.500                     | 38.10 | .750                       | 19.05 | .020 ± .003                       | .51 ± .076 |
| 2     | 2.000                     | 50.80 | 1.000                      | 25.40 | .020 ± .003                       | .51 ± .076 |

RW-175 ORDERING DESCRIPTION

Example 1:

**RW-175-3/8-X-STK**

- 1.2m [4 ft.] Length
- Color is Clear
- Size
- Semirigid, Very Thin Wall Product

Example 2:

**RW-175-3/4-0-SP**

- Spool Packaging
- Color is Black
- Size
- Semirigid, Very Thin Wall Product

[te.com/products/RW-175](https://te.com/products/RW-175)



## PRODUCT OFFERING

| Material Description | Material Number |
|----------------------|-----------------|
| RW-175-3/64-X-STK    | CV3299-000      |
| RW-175-3/64-X-SP     | CV3270-000      |
| RW-175-3/64-O-STK    | CV3331-000      |
| RW-175-3/64-O-SP     | CV3269-000      |
| RW-175-1/16-X-STK    | CV3300-000      |
| RW-175-1/16-X-SP     | CV3257-000      |
| RW-175-1/16-O-STK    | CV3322-000      |
| RW-175-1/16-O-SP     | CV3256-000      |
| RW-175-3/32-X-STK    | CV3301-000      |
| RW-175-3/32-X-SP     | CV3267-000      |
| RW-175-3/32-O-STK    | CV3329-000      |
| RW-175-3/32-O-SP     | CV3266-000      |
| RW-175-1/8-X-STK     | CV3302-000      |
| RW-175-1/8-X-SP      | CV3262-000      |
| RW-175-1/8-O-STK     | CV3325-000      |
| RW-175-1/8-O-SP      | CV3261-000      |
| RW-175-3/16-X-STK    | CV3303-000      |
| RW-175-3/16-X-SP     | CV3265-000      |
| RW-175-3/16-O-STK    | CV3328-000      |
| RW-175-3/16-O-SP     | CV3264-000      |
| RW-175-1/4-X-STK     | CV3304-000      |
| RW-175-1/4-X-SP      | CV3260-000      |
| RW-175-1/4-O-STK     | CV3324-000      |
| RW-175-1/4-O-SP      | CV3259-000      |
| RW-175-3/8-X-STK     | CV3305-000      |

| Material Description | Material Number |
|----------------------|-----------------|
| RW-175-3/8-X-SP      | CV3272-000      |
| RW-175-3/8-O-STK     | CV3332-000      |
| RW-175-3/8-O-SP      | CV3271-000      |
| RW-175-1/2-X-STK     | CV3306-000      |
| RW-175-1/2-X-SP      | CV3258-000      |
| RW-175-1/2-O-STK     | CV3323-000      |
| RW-175-3/4-X-STK     | CV3307-000      |
| RW-175-3/4-X-SP      | CV3268-000      |
| RW-175-3/4-O-STK     | CV3330-000      |
| RW-175-1-X-STK       | CV3308-000      |
| RW-175-1-X-SP        | CV3263-000      |
| RW-175-1-O-STK       | CV3326-000      |
| RW-175-1-1/2-X-STK   | CV3309-000      |
| RW-175-1-1/2-O-STK   | CV3327-000      |
| RW-175-2-X-STK       | CV3310-000      |
| RW-175-030-X-SP†     | CV3281-000      |
| RW-175-NO.1-X-SP†    | CV3293-000      |
| RW-175-NO.2-X-SP†    | CV3294-000      |
| RW-175-NO.13-X-SP†   | CV3291-000      |
| RW-175-NO.14-X-SP†   | CV3292-000      |
| RW-175-NO.33-X-SP†   | CV3296-000      |
| RW-175-NO.33-O-SP†   | CV3295-000      |
| RW-175-NO.65-X-SP†   | CV3298-000      |
| RW-175-NO.65-O-SP†   | CV3297-000      |

† RW-175 microtubing is available in 0.014-0.045 in. (.356-1.143 mm) dia. Consult TE for complete details.

## SAMPLE INVENTORY

|                    |
|--------------------|
| RW-175-3/64-X-STK  |
| RW-175-1/16-X-STK  |
| RW-175-3/32-X-STK  |
| RW-175-1/8-X-STK   |
| RW-175-3/16-X-STK  |
| RW-175-1/4-X-STK   |
| RW-175-3/8-X-STK   |
| RW-175-1/2-X-STK   |
| RW-175-3/4-X-STK   |
| RW-175-1-X-STK     |
| RW-175-1-1/2-X-STK |
| RW-175-NO.1-X-SP   |
| RW-175-NO.33-X-SP  |

[te.com/products/RW-175](http://te.com/products/RW-175)



## PROPERTY REQUIREMENTS

| Property                                                                                                                                                                                                                                                                                                                                                                           | Unit                                                                  | Requirement                                                                                                 | Test Method                                                                                                                |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|
| <b>PHYSICAL</b>                                                                                                                                                                                                                                                                                                                                                                    |                                                                       |                                                                                                             |                                                                                                                            |
| Dimensions                                                                                                                                                                                                                                                                                                                                                                         | Inch (mm)                                                             | Table 1                                                                                                     | RW-3029/2, Section 4.3.1                                                                                                   |
| Longitudinal Change                                                                                                                                                                                                                                                                                                                                                                | Percent                                                               | +0, -10 maximum                                                                                             | ASTM D 2671                                                                                                                |
| Tensile Strength                                                                                                                                                                                                                                                                                                                                                                   | psi (MPa)                                                             | 5000 minimum (34.5)                                                                                         | RW-3029/2, Section 4.3.2                                                                                                   |
| Ultimate Elongation                                                                                                                                                                                                                                                                                                                                                                | Percent                                                               | 150 minimum                                                                                                 | ASTM D 2671                                                                                                                |
| Secant Modulus (expanded)                                                                                                                                                                                                                                                                                                                                                          | psi (MPa)                                                             | 1 x 10 <sup>5</sup> minimum (690)                                                                           | ASTM D 2671                                                                                                                |
| Specific Gravity                                                                                                                                                                                                                                                                                                                                                                   |                                                                       | 1.8 maximum                                                                                                 | ASTM D 2671                                                                                                                |
| Low Temperature Flexibility<br>4 hours at -55°C ± 2°C (-67 ± 4°F)                                                                                                                                                                                                                                                                                                                  |                                                                       | No cracking                                                                                                 | RW-3029/2, Section 4.3.3                                                                                                   |
| Heat Shock<br>4 hours at 300 ± 5°C (572 ± 9°F)                                                                                                                                                                                                                                                                                                                                     |                                                                       | No dripping, flowing or cracking                                                                            | RW-3029/2, Section 4.3.4                                                                                                   |
| Heat Resistance<br>168 hours at 250 ± 5°C (482 ± 9°F)<br>Followed by test for:<br>Ultimate elongation                                                                                                                                                                                                                                                                              |                                                                       |                                                                                                             | RW-3029/2, Section 4.3.5                                                                                                   |
| Vacuum Outgasing<br>TML (Total Mass Loss)                                                                                                                                                                                                                                                                                                                                          | Percent                                                               | 50 minimum                                                                                                  | ASTM D 2671                                                                                                                |
| VCM (Volatile Condensible Material)                                                                                                                                                                                                                                                                                                                                                | Percent                                                               | 0.1 maximum                                                                                                 | ASTM E 595                                                                                                                 |
| <b>ELECTRICAL</b>                                                                                                                                                                                                                                                                                                                                                                  |                                                                       |                                                                                                             |                                                                                                                            |
| Dielectric Strength<br>Sizes 3/64 through 12<br>Sizes 3/4 through 2                                                                                                                                                                                                                                                                                                                | V/mil (kV/mm)                                                         | 800 minimum (31,500)<br>600 minimum (2,600)                                                                 | ASTM D 2671                                                                                                                |
| Volume Resistivity                                                                                                                                                                                                                                                                                                                                                                 | Ohm-cm                                                                | 1 X 10 <sup>13</sup> minimum                                                                                | ASTM D 2671                                                                                                                |
| <b>CHEMICAL</b>                                                                                                                                                                                                                                                                                                                                                                    |                                                                       |                                                                                                             |                                                                                                                            |
| Corrosive Effect Copper Mirror<br>16 hours at 150°C                                                                                                                                                                                                                                                                                                                                |                                                                       | Noncorrosive                                                                                                | RW-3029/2, Section 4.3.6.1<br>ASTM D 2671, Proc. A                                                                         |
| Copper Contact<br>168 hours at 175 ± 3°C (347 ± 5°F)<br>Followed by test for:<br>Ultimate Elongation                                                                                                                                                                                                                                                                               | Percent                                                               | No pitting or blackening of copper<br><br>100 minimum                                                       | RW-3029/2, Section 4.3.6.2<br>ASTM D 2671, Proc. B<br><br>RW-3029/2, Section 4.3.2                                         |
| Flammability<br>Average Time of Burning                                                                                                                                                                                                                                                                                                                                            | Seconds                                                               | 15 maximum                                                                                                  | ASTM D 2671, Proc. A                                                                                                       |
| Fungus Resistance<br>Followed by tests for:<br>Tensile Strength<br>Ultimate Elongation                                                                                                                                                                                                                                                                                             | psi (Mpa)<br>Percent                                                  | 5000 minimum (34.5)<br>150 minimum                                                                          | ISO 846, Method B<br><br>RW-3029/2, Section 4.3.2<br>ASTM D 2671                                                           |
| Dielectric Strength<br>Sizes 3/64 through 1/2<br>Sizes 3/4 through 2                                                                                                                                                                                                                                                                                                               | Volts/mil (volts/mm)                                                  | 800 minimum (31,500)<br>600 minimum (23,600)                                                                | ASTM D 2671                                                                                                                |
| Water Absorption<br>24 hours at 23 ± 3°C (73 ± 5°F)                                                                                                                                                                                                                                                                                                                                | Percent                                                               | 0.5 maximum                                                                                                 | ASTM D 2671                                                                                                                |
| Fluid Resistance<br>24 hours at 23 ± 3°C (73 ± 5°F)<br>JP-4 Fuel (MIL-T-5624)<br>SKYDROL 500 Hydraulic Fluid (MIL-H-5606)<br>Aviation Gasoline 100/130 (MIL-G-5572)<br>Salt Water (5% salt)<br>Anti-icing Fluid (MIL-A-8243)<br>Lubricating Oil (MIL-L-7808)<br>Followed by tests for:<br>Dielectric Strength<br>Sizes 3/64 through 1/2<br>Sizes 3/4 through 2<br>Tensile Strength | Volts/mil (Volts/mm)<br><br><br><br><br><br><br><br><br><br>psi (MPa) | <br><br><br><br><br><br><br><br><br><br>700 minimum (27,600)<br>500 minimum (19,700)<br>5000 minimum (34.5) | RW-3029/2, Section 4.3.7<br><br><br><br><br><br><br><br><br><br>ASTM D 2671<br><br>RW-3029/2, Section 4.3.2<br>ASTM D 2671 |

While TE has made every reasonable effort to ensure the accuracy of the information in this flyer, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this flyer are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[RW-175-1/8-X-STK](#)