




REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
S10		REVISED PER ECO-09-009758	23APR2009	DLD	DCM
S11		REVISED PER ECO-09-028550	29DEC2009	DLD	DCM
S12		REVISED PER ECO-20-012739	18SEP2020	AP	CM




KEYING OPTION "A"
1438082-1



SHOWN WITH CAM LEVER AND SPACER
IN LOADED POSITION WITH
OPTIONAL WIRESHIELD




KEYING OPTION "B"
1438082-2




- MATERIAL:
HARNESS - 35% GLASS FILLED PA66, BLACK
ALT MAT'L: HARNESS - 30% GLASS FILLED sPS, BLACK
SPACER - 40% GLASS FILLED PPS+PA66, RED
ALT MAT'L: 30% GLASS FILLED sPS, RED
ALT MAT'L: 35% GLASS FILLED PA66, RED
COVER - 35% GLASS FILLED PA66, BLACK
ALT MAT'L: COVER - 30% GLASS FILLED LCP, BLACK
CAM LEVER - 35% GLASS FILLED NYLON, GRAY
GROMMET - SILICONE, BROWN
PERIMETER SEAL - SILICONE, GREEN

2. CAM LEVER AND SPACER ARE SHIPPED IN PRE-LATCH POSITION.
 SEE PINOUT CHART ON SHEETS 2, 3 AND 4 FOR CLOSED CIRCUIT CONFIGURATIONS.
 CAVITIES WITH A NUMERIC SYMBOL INDICATES CLOSED TERMINAL LOCATIONS.
BLANK CAVITIES INDICATE OPEN TERMINAL HOLE LOCATIONS.



SCALE 1:1



SECTION B-B

SEE PINOUT CHARTS
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN R. VESTAL	01AUG2003	TE Connectivity	
DIMENSIONS:		CHK D. STRAUSSER	01AUG2003		
mm		APVD D. STRAUSSER	01AUG2003	NAME 46 WAY PCM CONNECTOR HARNESS ASSEMBLY	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE A100779	
		0 PLC ±.3 1 PLC ±0.3 2 PLC ±0.10 3 PLC ±. 4 PLC ±. ANGLES ±°		CAGE CODE C=1438082	
MATERIAL SEE TABLE		FINISH SEE TABLE		RESTRICTED TO SHEET 1 OF 5	
		WEIGHT		SCALE 4:1	
		CUSTOMER DRAWING		REV S12	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1438082-3](#)