






PART NUMBER:
1438136-1
SHOWN WITH SPACER
IN SEATED POSTION



REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
G45		REVISED PER ECO-13-011449	16JUL2013	DLD	DCM
G46		REVISED PER ECO-14-007153	19MAY2014	DLD	DCM
G47		REVISED PER ECO-14-014965	09OCT2013	DLD	DCM
G48		REVISED PER ECO-20-012739	05OCT2020	AP	CM

1. PRINT FORD PART NUMBER (SEE ATTACHED CHARTS) AND TRACEABILITY CODE (YY = 2 DIGIT YEAR, JJJ = JULIAN DATE, HH = 2 DIGIT MILITARY HOUR) IN THIS LOCATION AT ASSEMBLY. SEE SHEETS 3, 4 AND 5 (-*) PART NUMBERS.


2. APPLICABLE MOLEX (1.5) POWER TERMINAL PART NUMBERS:
33012-0002 TIN 0.50-1.50mm²

3. CAM LEVER AND SPACER ARE SHIPPED IN THEIR PRE-ASSEMBLED POSITIONS.



4. REFERENCE TE INSTRUCTION SHEET 408-8893.

△ COMPANY LOGO.



△ OBSOLETE PART.



SECTION A-A
SPACER AND LEVER
IN PRE-SEATED POSITION
(DELIVERY POSITION)



SHOWN WITH CAM
LEVER AND SPACER
IN LOADED POSTION



MIN. FEED THRU CONDITION
WITH 1mm CLEARANCE ALL AROUND
SHOWN WITH SPACER IN SEATED POSTION




APPLICABLE COMPONENTS (FOR REFERENCE ONLY)

DESCRIPTION	NOMINAL TERMINAL SIZE	COLOR/ PLATING	FORD COMPONENT PART NUMBER	SUPPLIER PART NUMBER	MATERIAL/SPECIFICATION NUMBER	SAE WIRE SIZE
TERMINAL - FEMALE (Ag)	0.64 (CAT. 0)	SILVER	7S4T-14474-AA	1393366-2	COPPER ALLOY/SILVER PLATE	20AWG
						18AWG
TERMINAL - FEMALE (Ag)	0.64 (CAT. 0)	SILVER	7S4T-14474-BA	1393367-2	COPPER ALLOY/SILVER PLATE	22AWG
						20AWG
TERMINAL - FEMALE (Sn)	0.64 (CAT. 0)	TIN	1L2T-14474-AA	1393366-1	COPPER ALLOY/TIN PLATE	20AWG
						18AWG
TERMINAL - FEMALE (Sn)	0.64 (CAT. 0)	TIN	1L2T-14474-BA	1393367-1	COPPER ALLOY/TIN PLATE	22AWG
						20AWG
TERMINAL - FEMALE (Au)	0.64 (CAT. 0)	GOLD	1L2T-14474-CA	1393365-1	COPPER ALLOY/GOLD PLATE	20AWG
						18AWG
TERMINAL - FEMALE (Au)	0.64 (CAT. 0)	GOLD	1L2T-14474-DA	1393364-1	COPPER ALLOY/GOLD PLATE	22AWG


SEE SHEETS 3 THRU 7
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL	15APR2005	TE TE Connectivity	
		CHK T. VALASEK	15APR2005		
DIMENSIONS:		APVD T. VALASEK	15APR2005	NAME	
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		0 PLC ±.3		APPLICATION SPEC	
		1 PLC ±0.10			
		2 PLC ±.1			
		3 PLC ±.1			
		4 PLC ±.1			
		ANGLES ±1°			
		FINISH			
MATERIAL				WEIGHT	
				CUSTOMER DRAWING	
				SCALE 2:1	
				SHEET 1 OF 11	
				REV. G48	


REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-




KEYING OPTION "A"




KEYING OPTION "B"




KEYING OPTION "C"



KEYING OPTION "D"



KEYING OPTION "E"



KEYING OPTION "F"

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL	15APR2005	TE Connectivity	
DIMENSIONS:		CHK'd T. VALASEK	15APR2005		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T. VALASEK	15APR2005	NAME	
	0 PLC	±		PRODUCT SPEC	
	1 PLC	±0.3		APPLICATION SPEC	
	2 PLC	±0.10		WEIGHT	
MATERIAL	3 PLC	±		CUSTOMER DRAWING	
	4 PLC	±		SCALE 2:1 SHEET 2 OF 11 REV 648	
	ANGLES	±1°			
	FINISH				

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LYR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

KEYING OPTION A

				65	64	63	62					56								42	40	39				33	32			27	26	25	24	23	22	21	20	19	18				13				8	7	6				2	1	9-1438136-6	5L3T-14A464-DA-054							
				65	64	63	62					56								43	42	40	39			33						24			21	20	18			13			8				3	2	1	8-1438136-8	5L3T-14A464-DA-053												
				65	64	63	62					56					49	48		43	42	40	39			33	31	30		27				23	21		18			13			8			5	4	3	2	1	8-1438136-3	5L3T-14A464-DA-052											
				65								56					50	49	48		44	43	42	40	39		33	31	30				24			20				13			8				3	2	1	8-1438136-2	5L3T-14A464-DA-051												
					64	63	62					57	56	55			50				43			39	38		32				27	26	25			22			14	13		9	8			3				8-1438136-1	5L3T-14A464-DA-050												
					64	63	62					57	56	55			50				43			39	38		32			29	28	27	26	25			22			14	13		9	8			3			7-1438136-8	5L3T-14A464-DA-049												
				65	64	63	62					57	56							42	40	39			33	32					26	25	24	23	22	21	20	19	18			13			8	7	6			2	1	7-1438136-7	5L3T-14A464-DA-048										
				65	64	63	62					56						49	48		43	42	40	39			33	31	30						23	21		18			13			8			5	4	3	2	1	7-1438136-5	5L3T-14A464-DA-047										
				65								56					50			44	43	42	40	39			33						24			20				13			8				3	2	1	7-1438136-4	5L3T-14A464-DA-046												
					65	64	63	62				56								43	42	40	39			33				27		24			21	20	18			13			8				3	2	1	7-1438136-3	5L3T-14A464-DA-045												
	68	67		65	64							56	55				50			44	43	42	41	40	39	38		33	31	30		27		24			20			15	14	13		11	10	9	8				2	1	7-1438136-2	5L3T-14A464-DA-044									
70	68	67	66	65	64	63			60	59			55	54			51	50			44	43	42	40		38	37		34		32	31	30	29		27			24	23		21	20	19	18		16	15	14			11	10	9			5	4	3	2	1	7-1438136-1	5L3T-14A464-DA-043
					64	63	62					57	56	55			50				43	42			39	38			32				27		25			22	21	20	19	18			14			9	8	7		5			1	6-1438136-9	5L3T-14A464-DA-042						
	68	67		65	64							56					50			44	43	42	40	39			33	31	30		27		24	23			20	18			13			8				4	2	1	6-1438136-8	5L3T-14A464-DA-041											
	68	67			64	63	62					56					50			44	43	42	40	39			33	31	30		27		24	23			21	20	18			13			8	7	6					6-1438136-7	5L3T-14A464-DA-040										
	68	67		64	63	62											50	49	48		44	43	42	40			33	31	30		27		24	23		21	20	18					7	6			4	3			6-1438136-6	5L3T-14A464-DA-039											
	68	67	66	65	64	62		60	59			56	55				51	50			44	43	42	41	40	39	38		34		32	31	30		27		24	23		20	19			15	14	13		11	10	9	8	7		5	4	3	2	1	6-1438136-5	5L3T-14A464-DA-038			
	68	67	66	65	64	62		60	59			56	55				51	50			44	43	42	41	40	39	38		34		32	31	30		27		24	23			20	19			15	14	13		11	10	9	8	7		5	4	2	1	6-1438136-4	5L3T-14A464-DA-037			
70	68	67	66	65	64	63		60	59			55	54				51	50			44	43	42	40	39	38	37		34		32	31	30	29		27		24	23		21	20	19		16	15	14			11	10	9			5	4	3	2	1	6-1438136-3	5L3T-14A464-DA-036		
					64	63	62					57	56	55			50				43				39	38			32				27	26	25			22	21	20	19	18			14	13		9	8	7	6	5	4	3			6-1438136-2	5L3T-14A464-DA-035					
				64	63	62						57	56	55			50				43				39	38			32			27	26	25		23	22	21	20	19	18			14	13		9	8	7	6	5	4			6-1438136-1	5L3T-14A464-DA-034							
	68	67		65	64							56	55							44		42	40	39	38			33	31	30		27		24	23			20	18			15	14	13		11	10	9	8	7		5	4		2	1	5-1438136-9	5L3T-14A464-DA-033					
	68	67															50			44	43	42	40				33				27		24			20	18										7				2		5-1438136-8	5L3T-14A464-DA-032									
	68	67			63	62											50			44	43	42	40				33				27		24			21	20	18					7					2		5-1438136-7	5L3T-14A464-DA-031												
				64	63	62						56										42	40	39				33						24	23			21	20	18			13			8	7						5-1438136-6	5L3T-14A464-DA-030									
	68	67	66	65	64			60	59				55				51	50			44	43	42	40		38			34		32	31	30		27		24	23			20	19			15	14			11	10	9			5	4		2	1	5-1438136-5	5L3T-14A464-DA-029			
	68	67		64									50							44	43	42	40	39				33	31	30		27		24	23			20	18			13			8	7	6					4-1438136-9	5L3T-14A464-DA-028										
70	68			63								56	55	54						44	42	40	39	38	37			33	32	31	30	29		27		25	24		22	21		19			15	14			10			5	4		2	1	4-1438136-3	5L3T-14A464-DA-027					
70	68			63								56	55	54						44	42	40	39	38	37			33	32	31	30	29		27		24		22	21		19			15	14			10				4	2	1	4-1438136-2	5L3T-14A464-DA-026							
				64	63							56	55				50				43	42	41	40	39	38				32	31	30		27		25			22	21	20	19			14				5				1	4-1438136-1	5L3T-14A464-DA-025								
	68	67		64								56					50				44	43	42	40	39				33	31	30		27	26	25		23	22		20	19	18			13			8	7	6	5	4	3	2	1	4-1438136-0	5L3T-14A464-DA-024						
	68	67		64	63	62						56					50				44	43	42	40	39			33	31	30		27		24	23			21	20	18			13			8	7	6				2		3-1438136-9	5L3T-14A464-DA-023								
	68	67		64	63	62											50	49	48		44	43	42	40				33	31	30		27		24	23			21	20	18					7	6						3-1438136-8	5L3T-14A464-DA-022										
	68	67		64		62						56					50				44	43	42	40	39			33	31	30		27		24	23			20	18			13			8	7	6				2		3-1438136-7	5L3T-14A464-DA-021									
	68	67		64								56					50				44	43	42	40	39			33	31	30		27		24	23			20	19	18			13			8	7</																

KEYING OPTION B

CAVITIES WITH A NUMERIC SYMBOL INDICATES CLOSED TERMINAL LOCATIONS

BLANK CAVITIES INDICATES OPEN TERMINAL HOLE LOCATIONS

TERMINAL HOLE POSITION

5L3T-14A464-E* PIN-OUT CHART

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R. VESTAL

CHK
T. VALASEK

APVD
T. VALASEK

15APR2005

15APR2005

15APR2005

DIMENSIONS:

mm

0 PLC ±.3

1 PLC ±0.10

2 PLC ±.1

3 PLC ±.1

4 PLC ±.1

ANGLES ±1°

FINISH

MATERIAL

-

-

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

NAME

70-WAY HARNESS ASSEMBLY

SIZE

CAGE CODE

DRAWING NO

A100779

RESTRICTED TO

-

TE Connectivity

SCALE

2:1

SHEET

5

OF

11

REV

648

CAVITIES WITH A NUMERIC SYMBOL INDICATES CLOSED TERMINAL LOCATIONS
BLANK CAVITIES INDICATES OPEN TERMINAL HOLE LOCATIONS

ASSEMBLY PART NUMBER	FORD PART NUMBER

4805 (3/13)

A

4805 (3/13)4805 (3/13)

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.


REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET I	-	-	-


KEYING OPTION F

[illegible]

KEYING OPTION E

[illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. VESTAL 15APR2005 CHK T. VALASEK 15APR2005 APPR T. VALASEK 15APR2005		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±.0 1 PLC ±.0 2 PLC ±.010 3 PLC ±. 4 PLC ±. ANGLES ±.°		PRODUCT SPEC - APPLICATION SPEC -	
MATERIAL		WEIGHT		SIZE CAGE CODE DRAWING NO A100779C1438136	
FINISH		CUSTOMER DRAWING		RESTRICTED TO - SCALE 2:1 SHEET 9 OF 11 REV 648	



1. GENERAL TOLERANCE:
 ± 0.3 ALL ONE PLACE DIMENSIONS
 ± 0.10 ALL TWO PLACE DIMENSIONS
 $\pm 1^{\circ}00'$ ALL ANGULAR DIMENSIONS

3 SEALING SURFACE, NO WITNESS LINES OF DAMAGE PERMITTED.

4. ALL UNMARKED RADII TO BE 0.5 MAX., UNLESS OTHERWISE SPECIFIED

5 VENT HOLE SIZE AND LOCATION IS OPTIONAL.

6 THIS AREA TO REMAIN CLEAR FOR THE HARNESS ASSEMBLY.

 TERMINAL POSITION IDENTIFICATION.










8. MATES WITH TYCO ELECTRONICS PART# 1438136-*



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: R. VESTAL 15APR2005 CHK: J. VALASEK 15APR2005 APP'D: J. VALASEK 15APR2005		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.3 2 PLC ±0.10 3 PLC ±. 4 PLC ±. ANGLES ±1°		NAME 70-WAY HARNESS ASSEMBLY	
		PRODUCT SPEC - APPLICATION SPEC -		SIZE CAGE CODE DRAWING NO A100779C1438136	
MATERIAL - - -		FINISH - - -		RESTRICTED TO - CUSTOMER DRAWING SCALE: 2:1 SHEET 10 OF 11 REF: 648	

HEADER INTERFACE KEYING OPTIONS

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN. R. VESTAL 15APR2005	TE Connectivity
DIMENSIONS:		CHK. T. VALASEK 15APR2005	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD. T. VALASEK 15APR2005	NAME
	0 PLC ±0.3	PRODUCT SPEC	70-WAY HARNESS ASSEMBLY
	1 PLC ±0.10	APPLICATION SPEC	
MATERIAL	FINISH	WEIGHT	SIZE CAGE CODE DRAWING NO. RESTRICTED TO
-	-	-	A100779C=1438136
CUSTOMER DRAWING		SCALE 2:1	SHEET 11 OF 11 REV. 648

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1438136-4](#)