





THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISED PER ECR-16-011494	20JUN2017	NK	CX
	D3	ECO-19-006934	13MAY2019	AP	WS



- 1 MATERIAL: CONTACTS - BRASS
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
HOLDDOWNS: - PHOSPHOR BRONZE.
- 2 PLATING: CONTACTS - 0.38 μ m MINIMUM GOLD ON MATING END,
2.54 μ m MINIMUM TIN LEAD ON SOLDER TAILS, BOTH OVER
1.27 μ m MINIMUM NICKEL.
HOLDDOWNS: 2.54 μ m MINIMUM TIN-LEAD OVER 1.27 μ m MINIMUM
NICKEL.
- 4 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 5 KAPTON VACUUM PICK UP BUTTON.
- 6 PLATING: CONTACTS - 0.38 μ m MINIMUM GOLD ON MATING END,
2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS, BOTH OVER
1.27 μ m MINIMUM NICKEL.
HOLDDOWNS: 2.54 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM
NICKEL.



		33.00	40.41	40.00	12	3-1445087-2
		30.00	37.41	37.00	11	3-1445087-1
		27.00	34.41	34.00	10	3-1445087-0
		24.00	31.41	31.00	9	2-1445087-9
		21.00	28.41	28.00	8	2-1445087-8
		18.00	25.41	25.00	7	2-1445087-7
		15.00	22.41	22.00	6	2-1445087-6
		12.00	19.41	19.00	5	2-1445087-5
		9.00	16.41	16.00	4	2-1445087-4
		6.00	13.41	13.00	3	2-1445087-3
SUPERCEDED BY 1445087-2		3.00	10.41	10.00	2	2-1445087-2
SUPERCEDED BY 3-1445087-2		33.00	40.41	40.00	12	1-1445087-2
SUPERCEDED BY 3-1445087-1		30.00	37.41	37.00	11	1-1445087-1
SUPERCEDED BY 3-1445087-0		27.00	34.41	34.00	10	1-1445087-0
SUPERSEDED BY 2-1445087-9		24.00	31.41	31.00	9	1445087-9
SUPERSEDED BY 2-1445087-8		21.00	28.41	28.00	8	1445087-8
SUPERSEDED BY 2-1445087-7		18.00	25.41	25.00	7	1445087-7
SUPERSEDED BY 2-1445087-6		15.00	22.41	22.00	6	1445087-6
SUPERSEDED BY 2-1445087-5		12.00	19.41	19.00	5	1445087-5
SUPERSEDED BY 2-1445087-4		9.00	16.41	16.00	4	1445087-4
SUPERSEDED BY 2-1445087-3		6.00	13.41	13.00	3	1445087-3
SUPERSEDED BY 2-1445087-2		3.00	10.41	10.00	2	1445087-2
	FINISH	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 09OCT2000		 TE Connectivity	
		CHR K. WHITAKER 20-FEB-2001 APVD C. JONES 20-FEB-2001			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		NAME VERTICAL SURFACE MOUNT HEADER ASSY, 15 MIC GOLD CONTACTS,SURFACE MOUNT, HOLDDOWNS, SGL ROW,MICRO MATE-N-LOK™	
		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000			
MATERIAL  SEE TABLE		WEIGHT -		SIZE CAGE CODE DRAWING NO A200779 C-1445087	
		CUSTOMER DRAWING		RESTRICTED TO - SCALE 5:1 SHEET OF 1 REV D3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1445087-8](#)