


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REVISED PER ECR-16-011506	23JUN2017	NK	CX
	C2	ECO-19-006934	13MAY2019	AP	WS




	MATERIAL:	CONTACTS - BRASS
		HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
		HOLD-DOWNS: - PHOSPHOR BRONZE.

△ PLATING: CONTACTS - 0.76μm MINIMUM GOLD ON MATING END,
2.54μm MINIMUM TIN LEAD ON SOLDER TAILS, BOTH OVER
1.27μm MINIMUM NICKEL.
HOLD DOWNS: 2.54μm MINIMUM MATTE TIN OVER 1.27μm MINIMUM
NICKEL.


△4 RECOMMENDED PC BOARD THICKNESS OF 1.57.

5 KAPTON VACUUM PICK UP BUTTON.

6	PLATING: CONTACTS - 0.76μm MINIMUM GOLD ON MATING END, 2.54μm MINIMUM MATTE TIN ON SOLDER TAILS, BOTH OVER 1.27μm MINIMUM NICKEL. HOLDDOWNS: 2.54μm MINIMUM MATTE TIN OVER 1.27μm MINIMUM NICKEL.
---	--




 0.15
 INCLUDES CONTACT TAILS
 AND HOUSING STANDOFFS



		33.00	37.43	40.00	12	3-1445095-2
		30.00	34.43	37.00	11	3-1445095-1
		27.00	31.43	34.00	10	3-1445095-0
		24.00	28.43	31.00	9	2-1445095-9
		21.00	25.43	28.00	8	2-1445095-8
		18.00	22.43	25.00	7	2-1445095-7
		15.00	19.43	22.00	6	2-1445095-6
		12.00	16.43	19.00	5	2-1445095-5
		9.00	13.43	16.00	4	2-1445095-4
		6.00	10.43	13.00	3	2-1445095-3
		3.00	7.43	10.00	2	2-1445095-2
2		33.00	37.43	40.00	12	1-1445095-2
1		30.00	34.43	37.00	11	1-1445095-1
0		27.00	31.43	34.00	10	1-1445095-0
9		24.00	28.43	31.00	9	1-1445095-9
8		21.00	25.43	28.00	8	1-1445095-8
7		18.00	22.43	25.00	7	1-1445095-7
6		15.00	19.43	22.00	6	1-1445095-6
5		12.00	16.43	19.00	5	1-1445095-5
4		9.00	13.43	16.00	4	1-1445095-4
3		6.00	10.43	13.00	3	1-1445095-3
2		3.00	7.43	10.00	2	1-1445095-2
	FINISH	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

SUPERSEDED BY 3-1445095-2
SUPERSEDED BY 3-1445095-1
SUPERSEDED BY 3-1445095-0
SUPERSEDED BY 2-1445095-9
SUPERSEDED BY 2-1445095-8
SUPERSEDED BY 2-1445095-7
SUPERSEDED BY 2-1445095-6
SUPERSEDED BY 2-1445095-5
SUPERSEDED BY 2-1445095-4
SUPERSEDED BY 2-1445095-3
SUPERSEDED BY 2-1445095-2

PCB LAYOUT COMPONENT SIDE 

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 09OCT2000		TE Connectivity	
DIMENSIONS:		CHK K. WHITAKER 20-FEB-2001			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES 20-FEB-2001			
mm		NAME			
		VERTICAL SURF MOUNT HEADER ASSY, 30 MIC GOLD CONTACTS, THRU HOLE HOLDDOWNS, SGL ROW, MICRO MATE-N-LOK™			
0 PLC ±. 1 PLC ±. 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000 WEIGHT -		SIZE CAGE CODE DRAWING NO RESTRICTED TO A200779 C-1445095 -	
MATERIAL		CUSTOMER DRAWING		SCALE 5:1 SHEET OF REV C2	
 SEE TABLE					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1445095-7](#)