

D

C

B



A

D



C

B

A



PART NUMBER	4 CONTACT POINTS	SPRING	CRIMP AREA
144969-4	Sn 0.8 to 2 μ m	Au 0.4 to 0.8 μ m	Sn 0.8 to 3.3 μ m
144969-3	Au 0.4 to 0.8 μ m	Sn 0.8 to 3.3 μ m	Sn 0.8 to 3.3 μ m
144969-2	Au 0.4 to 0.8 μ m	Au 0.4 to 0.8 μ m	Sn 0.8 to 3.3 μ m
144969-1	Sn 0.8 to 2 μ m PRETINNED	Sn 0.8 to 2 μ m PRETINNED	Sn 0.8 to 2 μ m PRETINNED



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. ROSI CHK X. ROUILLARD APVD J. DAHER		04 JUN2012 04 JUN2012 04 JUN2012		 TE Connectivity							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CLIP MQS A SERTIR (0.2-0.6 SQ mm) MQS RECEPTACLE WITH BARRIER CRIMP VERSION									
		 ±0.2											
MATERIAL		ANGLES FINISH ±2°											
VOIR TABLEAU		VOIR TABLEAU		WEIGHT 0.2g		SIZE A2		CAGE CODE 00779		DRAWING NO C=144969		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 10:1				SHEET 1 OF 1		REV E			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[144969-1](#)