

REV. 2

DCO 141326


COIL: @ 25°C  
 RESISTANCE \_\_\_\_\_ 1350 OHMS ± 10%  
 NOMINAL VOLTAGE \_\_\_\_\_ 26.5 VDC  
 MUST OPERATE \_\_\_\_\_ 13.5 VDC  
 \_\_\_\_\_  
 MUST RELEASE \_\_\_\_\_ 8.1 VDC MAX, 1.5 VDC MIN.

ENVIRONMENT:

VIBRATION \_\_\_\_\_ 10 \_\_\_\_\_ CPS TO \_\_\_\_\_ 3000 \_\_\_\_\_ CPS @ \_\_\_\_\_ 30 \_\_\_\_\_ g's  
 SHOCK \_\_\_\_\_ 75 \_\_\_\_\_ g's \_\_\_\_\_ 6 \_\_\_\_\_ MS. DURATION  
 TEMPERATURE \_\_\_\_\_ -65 \_\_\_\_\_ °C TO \_\_\_\_\_ +125 \_\_\_\_\_ °C

NOTES: \_\_\_\_\_ OPERATE & RELEASE 4 MS MAX.  
 \_\_\_\_\_ BOUNCE 2 MS MAX.  
 \_\_\_\_\_  
 \_\_\_\_\_

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: \_\_\_\_\_ LOW LEVEL TO  
 \_\_\_\_\_ 2 AMPS 28 VDC RESISTIVE  
 \_\_\_\_\_ 50,000 OPERATIONS

DR. \_\_\_\_\_ R.B. 11/21/96 CK. *GgH* 9/20/99



COMMUNICATIONS  
 INSTRUMENTS, INC.

CUST. \_\_\_\_\_ OPL  
 CUST. NO. \_\_\_\_\_ M39016/13-057L REV. \_\_\_\_\_

\*3SBC\* RELAY

3SBC1503A2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M39016/13-057L](#)